

**APC Smart-UPS 3000VA LCD 230V**

**Part Number: SMT3000I**



**Output**

Output Power Capacity	2700 Watts / 3000 VA
Max Configurable Power	2700 Watts / 3000 VA
Nominal Output Voltage	230V
Output Voltage Note	Configurable for 220 : 230 or 240 nominal output voltage
Efficiency at Full Load	98%
Output Voltage Distortion	Less than 5% at full load
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal, 57 - 63 Hz for 60 Hz nominal
Waveform Type	Sine wave
Output Connections	(8) IEC 320 C13 (1) IEC 320 C19 (2) IEC Jumpers



**Input**

Nominal Input Voltage	230V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	IEC-320 C20 Schuko CEE 7 / EU1-16P British BS1363A

Input voltage range for main operations 160 - 285V

Input voltage adjustable range for mains operation 151 - 302V

#### Batteries & Runtime


Battery Type Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Typical recharge time 3 hour(s)

Replacement Battery [RBC55](#)

RBC™ Quantity 1

#### Runtime Graph




*Hover over the line on the graph above to view the runtime at any desired load*

Curve fit to measured runtime data. All measurements taken with new, fully charged batteries, at typical environmental conditions, with no electrical input and balanced resistive load (PF = 1.0) output.

[View Enlarged Graph](#)

[View Runtime Chart](#)

# Energy Use/Efficiency



*Hover over the line on the graph above to view the efficiency at any desired load*

Curve fit to measured efficiency data. All measurements taken in normal operating mode, at typical environmental conditions, with nominal electrical input and balanced resistive load (PF = 1.0) output.

[View Enlarged Chart](#)

## Communications & Management

Interface Port(s)	SmartSlot,USB
Available SmartSlot™ Interface Quantity	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Yes

## Surge Protection and Filtering

Surge energy rating	365 Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Physical

Maximum Height	435.00 mm
Maximum Width	197.00 mm
Maximum Depth	544.00 mm
Net Weight	52.50 KG

Shipping Weight	63.70 KG
Shipping Height	699.00 mm
Shipping Width	381.00 mm
Shipping Depth	762.00 mm
Color	Black
Units per Pallet	3.00

#### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	53.00 dBA
Online Thermal Dissipation	375.00 BTU/hr

#### Conformance

Regulatory Approvals	C-tick,CE,EN 50091-1,EN 50091-2,VDE
Standard Warranty	3 years repair or replace (excluding battery) and 2 year for battery,optional on-site warranties available,optional extended warranties available
Environmental Compliance	RoHS 7b Exemption,China RoHS,REACH: Contains No SVHCs

\*\*The time to recharge to 90% of full battery capacity following a discharge to shutdown using a load rated for 1/2 the full load rating of the UPS.