Honeywell Sensing and Control



23AC2



Actual product appearance may vary.

Features

Automatically cuts power when

service door or drawer is opened

• Choice of momentary, maintained or pull-to-cheat actuation

Versatile mounting bracket for side

- or end mountingCurrent rating ranges from 5 A to 25
- A

Available with one or two SPDT switches

- UL recognized versions available
- Choice of termination

Potential Applications

AC Series Door Switch, Single Pole Double Throw Circuitry, 15 A at 250 Vac, Rod Actuator, Silver Contacts,

Appliances

Screw Termination

- Vending machines
- Office equipment
- Computer/business
- equipment
- Test instruments
- Medical/dental equipmentCommunications equipment
- HVAC equipment

Description

MICRO SWITCH[™] AC Series Door Switches are used for simple or precision on/ off application needs. They enable circuit testing with POWER ON by manually pulling a rod actuator to the maintained-ON position. Closing the door resets the switch.

Product Specifications	
Switch Type	Door 38,1 mm H x 12,7 mm W x 38,1 mm L [1.5 in H x 0.5 in W x 1.5 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	Single Pole Double Throw (SPDT)
Actuator	Rod
Termination	Screw
Operating Temperature Range	-18 °C to 82 °C [-65 °F to 180 °F]
Voltage	250 Vac
Contact Type	Silver
Operating Position (O.P.)	5,16 mm [0.203 in] min.
Free Position (F.P.)	9,53 mm [0.375 in] max.

Housing Material	Stainless Steel Bracket, Polyester Rod
Weight	41,73 g [.092 lb]
Package Height	46 mm [1.81 in]
Package Width	12,7 mm [.50 in]
Package Length	50,0 mm [1.97 in]
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	AC

