

#### **Smart-UPS** APC Smart-UPS 3000VA RM 5U 120V Shipboard



APC Smart-UPS, 2250 Watts / 3000 VA,Input 120V / Output 120V, Interface Port DB-9 RS-232, SmartSlot, Rack Height 5 U

**Includes**: CD with software, Rack Mounting support rails, Smart UPS signalling RS-232 cable, User Manual



**Standard Lead Time**: Usually Ships within 4 Weeks

#### **Smart-UPS Features & Benefits**

Availability	
Boost and Trim Automatic Voltage Regulation (AVR)	Gives higher application availability by correcting low and high voltage conditions without using the battery.
Intelligent Battery Management	Maximizes battery performance, life, and reliability through intelligent, precision charging.
Power conditioning	Protects connected loads from surges, spikes, lightning, and other power disturbances.
Temperature- compensated battery charging	Prolongs battery life by regulating the charge voltage according to battery temperature.
Automatic restart of loads after UPS shutdown	Automatically starts up the connected equipment upon the return of utility power.
Automatic self-test	Periodic battery self-test ensures early detection of a battery that needs to be replaced.
Cold-start capable Disconnected battery notification	Provides temporary battery power when the utility power is out. Warns when a battery is not available to provide backup power.
Generator Compatible	Ensures clean, uninterrupted power to protected equipment when generator power is used.
Manageability	
Network manageable	Provides remote management of the UPS over the network.
SmartSlot	Customize UPS capabilities with management cards.
Audible Alarms	Actively let you know if the unit is on battery, if the battery is low or if there is an overload condition.
LED status indicators	Quickly understand unit and power status with visual indicators.
Serial Connectivity	Provides management of the UPS via a serial port.
USB Connectivity	Provides management of the UPS via a USB port (not available on all models).
Disconnected battery notification	Warns when a battery is not available to provide backup power.
InfraStruXure Manager Compatible Serviceability	Enables centralized management via the APC InfraStruXure® Manager.
User-replaceable batteries	Increases availability by allowing a trained user to perform upgrades and replacements of the batteries reducing Mean Time to Repair (MTTR)
Hot-swappable batteries	Ensures clean, uninterrupted power to protected equipment while batteries are being replaced
Predictive failure notification	Provides early-warning fault analysis ensuring proactive component replacement.
Resettable circuit breakers	Enables a quick recovery from overload events.
Adaptability	
Adjustable voltage-	Maximizes useful battery life by widening the input voltage window or

transfer points Adjustable voltage sensitivity Field-replaceable power distribution panel	tightening the output voltage regulation. Provides the ability to adapt the UPS for optimal performance in specific power environments or generator applications. Ensures compatibility with equipment that has different plug types.
Safety	
Safety-agency approved	Ensures the product has been tested and approved to work safely with the connected service provider equipment and within the specified environment. UL, FCC, CE, C-Tick approvals.

- Compare Models
  Ratings and Reviews

# Output

Output Power Capacity	2250 Watts / 3000 VA	
Max Configurable Power	2250 Watts / 3000 VA	
Nominal Output Voltage	120V	
Output Voltage Distortion	Less than 5% at full load	
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal,57 - 63 Hz for 60 Hz nominal	
Crest Factor	up to 5 : 1	
Waveform Type	Sine wave	
Output Connections	(6) NEMA 5-15R	
Waveform Type	Sine wave	

# Input

Nominal Input Voltage	120V	
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)	
Input Connections	NEMA L5-30P	(S)
Cord Length	1.83 meters	
Input voltage range for main operations	92 - 147V	
Input voltage adjustable range for mains operation	86 - 154V	

#### **Batteries & Runtime**

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	3 hour(s)
Replacement Battery	<u>RBC11</u>
RBC <sup>™</sup> Quantity	1
Typical Backup Time at Half Load	19.2 minutes (1125 Watts)
Typical Backup Time at Full Load	5.7 minutes (2250 Watts)
Runtime Chart	Smart-UPS

## **Communications & Management**

Interface Port(s)	DB-9 RS-232,SmartSlot
Available SmartSlot <sup>TM</sup> Interface Quantity	1
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : and Overload Indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Optional

## **Surge Protection and Filtering**

Surge energy rating	480 Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Physical

Maximum Height	222.00 mm
Maximum Width	483.00 mm
Maximum Depth	451.00 mm
Rack Height	5U
Net Weight	58.64 KG
Shipping Weight	65.91 KG
Shipping Height	337.00 mm
Shipping Width	622.00 mm
Shipping Depth	610.00 mm
Color	Beige

#### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0%
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	53.00 dBA
Online Thermal Dissipation	375.00 BTU/hr

#### Conformance

Regulatory Approvals	CSA,FCC Part 15 Class A,UL 1778
Standard Warranty	2 years repair or replace, optional on-site warranties available, optional extended warranties available

\*\*The time to recharge to 90% of full battery capacity following a discharge to shutdown using a load rated for 1/2 the full load rating of the UPS.