

Honeywell Sensing and Control

1LS1-L



Enclosed Switches Series LS: Side Rotary with 1.5" Fixed Length Lever; Steel Roller; 1NC 1NO DPDT Snap Action, Double Break; 0.5 in - 14NPT conduit; Compact/Non-Plug-in

Actual product appearance may vary.

Features

- Mode of operation is field adjustable
- NEMA 1, 3, 4, 6, and 13
- Wide choice of heads and actuators
- Variety of operating characteristics
- Captive screws
- UL and CSA approved parts available

Potential Applications

- Machine tools
- Conveyors
- Material handling
- Metal fabrication equipment
- Lift trucks

Description

MICRO SWITCHTM compact LS and plug-in 200LS limit switches have a long record of successful performance in industrial applications. The MICRO SWITCHTM LS fits in many places too small for any other fully adjustable limit switch. The MICRO SWITCHTM 200LS switches are the original plug-in concept for reducing downtime by making changeover simple and fast.

Product Specifications	
Availability	Global
Operating Force (O.F.)	0.51 N m max. [4.5 in lb max.]
Full Overtravel Force	8.13 N m max. [6 in lb max.]
Release Force (R.F.)	0.08 N m min. [0.75 in lb min.]
Pretravel (P.T.)	20° max.
Overtravel (O.T.)	30° min.
Differential Travel (D.T.)	12° max.
Product Type	MICRO SWITCH™ Compact Limit Switches
Actuator	Side Rotary
Lever Style	1.5 in Fixed Length Lever with front mounted Steel Roller (.75 in dia. x .25 in wide)

Circuitry	1NC 1NO SPDT Snap Action,
	Double-Break
Ampere Rating	10 A Ind./0.8 A Res./0.4 Res.
Supply Voltage	125 Vac. 250 Vac. 480 Vac/125 Vdc/250 Vdc
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14NPT conduit
Housing Type	Compact / Non Plug-In
Series Name	LS
Sealing	NEMA 1, 3, 4, 6, 13
Approvals	UL Recognized, CSA Certified
CSA File #	LR57325
UL File #	E12252
Operating Temperature Range	-29 °C to 71 °C [-20 °F to 160 °F]
Comment	UL Recognized, CSA Certified
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial

