

# Super Contact Cleaner 801B



- Protects gold for life
- Improves conductivity
- Safe on plastics

Use when requiring a contact cleaner with lubrication that offers long-term protection from oxidation. Reduces contact scrubbing and reduces connection wear and abrasion failures. Protects, lubricates and deoxidizes IC's, connectors, jacks, relays, contacts, switches, plugs, batteries, controls, potentiometers and more.

Also available in micro tip pen format.

#### **Available Sizes**

Catalog Number	Sizes Available	Description	
801B-100ML	100ml (4 oz)	Liquid	
801B-125G	125g (4.5 oz)	Aerosol	
<u>801B-P</u>	10ml (0.34 oz)	Felt pen	





# **Material Safety Data Sheet**

# **Section 1: Product Identification**

MSDS Code: 801B - aerosol Name: Super Contact Cleaner (With PPE)

Related Part Numbers: 801B-125G
Use: Cleans and protects connector ends.

# Section 2: Hazardous Ingredients

CAS#	Chemical Name	Percentage by weight	ACGIH TWA	Osha Pel	Osha Stel
64742-88-7	Petroleum naphtha	70 - 85	100ppm	N/e	N/e
811-97-2	1,1,1,2 - tetrafluoroethane	20 - 25	1000ppm	N/e	N/e
64741-44-2	Petroleum seal oil	2 - 6	5 mg/m³	N/e	N/e
2455-71-2	Poly phenyl ether	2 - 4	N/e	N/e	N/e

#### **Section 3: Hazards Identification**

WHMIS Codes: A, B5, D2B

NFPA Ratings: Health 2 Flammability 3 Reactivity 0

HMIS Ratings: Health 2 Flammability 3 Reactivity 0

**Eyes:** Vapors cause eye irritation.

Skin: May cause defatting, drying and cracking of the skin.

Inhalation: Product is irritating to the nose, throat, and respiratory tract. May cause central nervous system

depression, headache, dizziness, cardiac arrhythmia, nausea, and vomiting

**Ingestion:** Harmful if swallowed.

Chronic: This product may sensitize heart muscle causing cardiac arrhythmia, in rare cases.

#### **Section 4: First Aid Measure**

Eyes: Remove contact lenses. Flush with water or saline for 20 minutes. Get medical aid.

Skin: Wash skin with large quantities of soap and water. Get medical aid if symptoms persist.

Inhalation: Immediately remove from exposure to fresh air. If not breathing, give artificial respiration. If

breathing is difficult, give oxygen. Get medical aid.

**Ingestion:** Do not induce vomiting. If conscious, give 1-2 glasses of water. Get medical aid.



### Section 5: Fire Fighting Measures

Autoignition Temperature 240°C Flash Point: 42°C **LEL / UEL**: 1/5

Extinguishing Media: Use water spray, dry chemical, carbon dioxide, or chemical foam.

Will burn if involved in a fire. Containers may explode in the heat of a fire. Highly

General Information: flammable vapors are heavier than air and may accumulate in low areas. Flash back

along vapor trail is possible.

#### Section 6: Accidental Release Measures

Spill Procedure: Remove all sources of ignition. Provide adequate ventilation. Wear appropriate personal

protection. Sprinkle absorbent compound onto spill, then sweep into a plastic or metal container. Wipe up further residue with paper towel and place in container. Wash spill area with soap and

water

#### Section 7: Handling and Storage

Handling: Wash thoroughly after handling. Avoid contact with eyes, skin, and clothing. Do not ingest or inhale. Do

not expose container to heat or flame.

Keep away from sources of ignition. Store in a cool, dry, well-ventilated area, away from incompatible Storage:

#### Section 8: Exposure Controls

Routes of entry: Eyes, ingestion, inhalation, and skin.

Ventilation: Use adequate general or local exhaust ventilation to keep airborne concentrations below

exposure limits.

**Personal Protection:** Wear appropriate protective eyeglasses or chemical safety goggles. Wear appropriate

protective clothing to prevent skin contact. Use a NIOSH approved respirator when

necessary.

#### Section 9: Physical and Chemical Properties

**Physical** Aerosol Distinctive Solubility Evaporation Odor: Insoluble Moderate

State: in water: Rate:

**Boiling** 156°C Specific Vapor 42 PSI Vapor 0.81 4.7 :Ha N/a

Point: Gravity: Pressure: @21°C Density: (Air=1)

# Section 10: Stability and Reactivity

Stability: Stable at normal temperatures and pressures.

Conditions to

avoid:

Temperatures over 40°C, ignition sources, and incompatible substances.

Alkali and alkaline earth metals, powdered aluminum, zinc, magnesium, and beryllium, Incompatibilities:

strong oxidizers, lewis or mineral acids.

Polymerization: Will not occur.

Decomposition: Halogens, halogen acids, possibly carbonyl halides, carbon monoxide, carbon dioxide.

> **PAGE 2 / 4** MSDS Code: 801B - Aerosol



#### Section 15: Regulatory Information

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the MSDS contains all of the information required by the Controlled Products Regulations.

SARA (Superfund Amendments and Reauthorization Act of 1986, USA, 40 CFR 372.4)

None of the chemicals in this product have a reportable quantity.

EPCRA (Emergency Planning and Right to Know Act, USA, 40 CFR 372.45

This product does not contain any chemicals subject to the reporting requirements of section 313 Title III of the SARA of 1986 and 40 CFR part 372.

TSCA (Toxic Substances Control Act of 1976, USA)

All substances are TSCA listed.

CAA (Clean Air Act, USA)

This product does not contain any class 1-ozone depletors.

This product does not contain any class 2-ozone depletors.

This product does not contain any chemicals listed as hazardous air pollutants.

California Proposition 65 (Chemicals know to cause cancer or reproductive toxicity, May 1, 1997 revision, USA)

This product does not contain any chemicals listed.

#### **Health Canada**

Labeling and containers used in this product are listed in compliance with Consumer Chemicals and Container regulations.

#### **Environment Canada**

Chemicals in this product are listed on the Domestic Substances List in the Canadian Environmental Protection Act

This product does not contain any ozone depleting substances.

#### **Industry and Science Canada**

Labeling, product identity, net quantity declaration, minimum printing type size heights, and packaging of this product is in compliance with the Consumer Packaging and Labeling Act and Regulations. This product is not slack filled in accordance to chapter 4 prohibitions.

**RoHS** (The restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2004).

This product is RoHS compliant.

#### **Section 16: Other Information**

**Definitions:** N/a = not applicable, n/e = not established

**Disclaimer:** This material safety data sheet is provided as an information resource only. M.G. Chemicals believes the

information contained herein is accurate and compiled from reliable sources. It is the responsibility of the user to verify its validity. The buyer assumes all responsibility of using and handling the product in

accordance with federal, state, and local regulations.