

SLI Series units act as a defensive barrier between your equipment and



corrupted power, thereby eliminating premature hardware failure, data loss and error, storage loss and system/keyboard

Under voltage

lockup. SLI Series units are most effective against five power problems.



Over voltage

Power

SLI Series Features

- 120 VAC, 50/60 Hz (Auto-sensing)
 Operation
- Advanced Battery Management Technology Doubles Battery Service Life
- Extended Battery Modules (EBMs) Increase Run Time Capacity
- Buck and Double Boost Voltage Regulation
- ◆ Load Segment Control
- Network Transient Protector Isolates Networks, Modems and Cables from Surges and Spikes
- Hot-swappable Batteries
 Simplify Service
- X-Slot Option Cards Extend Power Management Capabilities

Advanced Power Management

SLI Series STABILINE Uninterruptible Power Supplies provide advanced power management for PCs, workstations and servers.

All SLI Series units incorporate load segment capabilities (separate receptacle groups) which enable scheduled shutdowns and load shedding as well as maximum run time for each critical device. To preserve battery power for more critical equipment connected to the UPS, shut down and power up load segments are user-defined. Feature rich communications and UPS power management software provide extensive control and monitoring.

All feature advanced battery management technology, which doubles battery service life, critical to maximizing system availability. Lead-acid batteries subjected to constant trickle charging (utilized by most all other UPSs on the market today) reach the end of their useful life in less than half the time of batteries charged using SLI Series advanced battery management. Utilizing a proprietary three-stage charging technique, SLI Series units minimize recharge time and provide for up to 60 days notification when batteries are approaching the end of their useful life.

Hot-swappable Batteries

When alarm notification indicates the end of battery life is near, batteries can easily be hot-swapped without powering down the connected load(s). User friendly design allows batteries to be exchanged through the front of the unit.

Extended Battery Modules

Increasing battery backup time is as simple as plugging in an extended battery module. Hot-swap capability with all extended battery modules (EBMs) allow for expanded run time or EBM replacement while keeping your critical load up and running.

		Model SLI1000	Model SLI1500	Model SLI2200	
—	Nominal Voltage	120 VAC			
INPUT	Voltage Range	77 · 152 VAC			
<u> </u>	Frequency Range	46 · 65 Hz			
Z	Noise Filtering	MOVs and Line Filter for Normal and Common-mode Noise			
_	· ·				
	VA Rating	1000 VA	1440 VA	1920 VA	
	Power	700 Watts	1050 Watts	1600 Watts	
	Frequency		50/60 Hz, Auto-sensing		
5	Voltage		120 VAC		
<u></u>	Voltage Regulation		-10% to +6% of Nominal		
⊨	On Utility On Battery		±5% RMS		
OUTPUT	Overload (Normal Operation)	110% Overload, Shutdown After 3 Minutes; 150% Overload, Shutdown 10 Cycles			
	Voltage Wave Shape (Battery Mode)	Sine Wave			
	Transfer Time Line Fails/Recovers		2-4 ms Typical		
	Output Protection		Short Circuit Protection		
	·				
BATTERY	DC Voltage	24 VDC	48 VDC	48 VDC	
	Type	(2) 121/ 041	Sealed, Lead-acid, Maintenance-free, Valve-regula		
	Number (Internal) Number (External Battery Module)	(2) 12V, 9AH (8) 12V, 9AH	(4) 12V, 7AH (8) 12V, 9AH	(4) 12V, 12AH (8) 12V, 9AH	
ш	Recharge Time to 90%		attery; < 3 Hours; External Battery; No More than		
	Run Time (Internal Batteries) †	litternal b	attery, < 3 flours, External Battery, No More than	To x discharge fillie	
4	Full Load/Half Load in Minutes	5/14	6/17	5/14	
<u> </u>	Battery Replacement		appable Internal Batteries and External Battery Mo		
	Monitoring		nitoring for Earlier Failure Detection and Warning; A		
	Special	Frequency Auto Tracking, DC Cold Start, Optional Extended Battery Modules, Load Segment Control, Network Transient Protection; Input/Output RJ45 (accomodates RJ11 Jacks) for Modem/Fax and Other Telecommunications Equipment; UL 497A Tested			
	Diagnostics		Full System Self-test on Power-up		
NS	User Interface		Front Panel Control		
	Computer Interface	Power Management Software CD-ROM and 6-Foot Communications Cable Supplied			
0	X-Slot Interface	RS-232 Single Serial Card (Standard); Other Options Available - Consult Factory			
	Audible	On Battery, Low Battery, Overload, UPS Fault 0°C to 40°C (32°F to 104°F)			
SPECIFICATIONS	Temperature Operating Storage	0°C to 25°C (32°F to 77°F)			
	<u> </u>	-25°C to 55°C (-13°F to 131°F)			
	Humidity	0.95% Non-condensing			
	Altitude Operating	10,000 Feet (3,000 Meters) Without Derating			
\circ	Transit	50,000 Feet (15,000 Meters Above Sea Level)			
<u> </u>	Audible Noise	Less than 40 dBA Normal Mode, Less than 55 dBA Battery Mode with Typical Load			
	Surge Suppression	ANSI/IEEE C62.41 Category B (Formerly IEEE 587), IEC61000-4-5			
	EMC Compliance		FCC Part 15, ICES-003		
7	Input Connection	5-15P, 6-Foot Line Cor		5-20P, 6 Foot Line Cord	
RAL	Output Receptacles	(6) 5-15R	(6) 5-15R	(6) 5-15R, (2) 5-20R	
GENER	Load Segments	(2) Receptacle Group		(3) Receptacle Groups	
	Weight UPS EBM	34 lbs (16 kg)	51 lbs (23 kg) 60 lbs (27 kg)	68 lbs (31 kg)	
	Dimensions HxWxD UPS Inches	9.45 x 6.38 x 15.79		9.84 x 8.07 x 19.41	
G	Millimeters	240 x 162 x 401	250 x 162 x 467	250 x 205 x 493	
	EBM Inches	2 10 X 102 X 101	9.84 x 6.38 x 18.66	200 X 200 X 170	
	Millimeters		250 x 162 x 474		
	Agency		UL, cUL		
	Warranty		2 Years		
OPTIONAL EBM's		Model	Model	Model	
	Run Time Internal battery plus	SLI24V-EBM	SLI48V-EBM	SLI48V-EBM	
	number of optional EBM's up to four.	Full Load/Half Load in Minutes		Full Load/Half Load in Minutes	
	min .				
	1 EBM [4]	25/60	33/79	25/60	
	2 EBM V	55/170	63/146	55/170	
	3 EBM V	83/199	92/174	81/198	
	4 EBM U	109/228	120/201	106/224	

Specifications subject to change without notice. † Backup times are for reference only. Actual duration may vary depending on temperature, battery condition and type of load.



