62.5/125, Multimode Fiber Cable, Dual LC / Dual LC, 1.0m

Features for this product

- Used to connect communications equipment that utilize ST, SC and LC fiber interfaces
- · Rugged Polyurethane jacket protects against cuts, abrasions and chemicals
- · Cable meets Military requirements for crush and impact resistance
- · Multiple off the shelf lengths provide design flexibility
- Impact Resistance: EIA/TIA-455-25, (Military Req.) Crush Resistance: EIA/TIA-455-41, (Military Req.)



L-com's Military Grade fiber optic patch cables are built with specialized Military Tactical fiber cable that features impact and crush resistance characteristics which comply with Military requirements. Additionally, these robust assemblies are rated for operating temperatures of -40° to +75° Celsius. Three versions are available including Duplex ST, SC and LC styles. Our ST connectorized assemblies feature rust resistant stainless steel bodies and extra high force springs to ensure tight mating even when exposed to shock and vibration often encountered in the field under combat conditions. These assemblies are excellent for use in military vehicles and with field deployed communications equipment.

Details for this Fiber Optic product

L-com Item # FODLCMIL-01


Manufacturer L-com

UPC # 822335045217

RoHS Status Not Compliant At This Time







TE-

Dual SC Connectors

Dual LC Connectors

SC (2)

LC (2)

-95

FODSCMIL-XX

FODLCMIL-XX

LC (2)

SC (2)

Item # Description

Variable Length 62.5/125 Multimode Fiber Coil Cables

L-com's exclusive coil fiber cables provide flexibility for all your additions and changes. These unique cables feature a coiled cable construction, which supports variable lengths when equipment is moved or added. Our quality-constructed cables are great for securing fiber to the desktop applications as well as server and equipment rack usage. These assemblies feature SC, ST, LC and MTRJ connectors along with an extremely abrasion resistant polyurethane jacket that stands up to oxidation and oil better than a standard PVC cable.

Dual ST to Dual ST Coil Cable, Multimode Fiber with Polyurethane Jacket

FODST-C-03	MM Coil Fiber Cable, Dual ST / Dual ST, 3.0n	n Extended Length
FODST-C-05	MM Coil Fiber Cable, Dual ST / Dual ST, 5.0n	n Extended Length
FODST-C-07	MM Coil Fiber Cable, Dual ST / Dual ST, 7.0n	n Extended Lenath

Dual SC to Dual SC Coil Cable, Multimode Fiber with Polyurethane Jacket

FODSC-C-03	MM Coil Fiber Cable, Dual SC / Dual SC, 3.0m Extended Length
FODSC-C-05	MM Coil Fiber Cable, Dual SC / Dual SC, 5.0m Extended Length
FODSC-C-07	MM Coil Fiber Cable, Dual SC / Dual SC, 7.0m Extended Length

Dual LC to Dual LC Coil Cable, Multimode Fiber with Polyurethane Jacket

FODLC-C-03	MM Coil Fiber Cable, Dual LC / Dual LC, 3.0m Extended Length
FODLC-C-05	MM Coil Fiber Cable, Dual LC / Dual LC, 5.0m Extended Length
FODLC-C-07	MM Coil Fiber Cable, Dual LC / Dual LC, 7.0m Extended Length

MT-RJ to MT-RJ Coil Cable, Multimode Fiber with Polyurethane Jacket

FODMTRJ-C-03 MM Coil Fiber Cable, MT-RJ / MT-RJ, 3.0m Extended Length FODMTRJ-C-05 MM Coil Fiber Cable, MT-RJ / MT-RJ, 5.0m Extended Length FODMTRJ-C-07 MM Coil Fiber Cable, MT-RJ / MT-RJ, 7.0m Extended Length

IP66/67 Harsh Environment Multimode Duplex LC Cable Assemblies

L-com's IP66/67 rated Duplex LC cable assemblies are perfect for Industrial networks and harsh environments where protection from moisture, chemicals, corrosive gases and liquids is essential. These rugged Multimode assemblies feature robust outdoor rated cable, which stands up to hostile environments. Each assembly is 100% functionally tested and is covered by a one year manufacturer warranty. Accessories sold separately include a bulkhead style adapter where one side is designed for standard LC fiber cable connection and the other will accept the industrial LC connector.

FODLC-IND-01	MM IP67 Fiber Cable, Dual LC / Dual LC, 1.0m
FODLC-IND-03	MM IP67 Fiber Cable, Dual LC / Dual LC, 3.0m
FODLC-IND-05	MM IP67 Fiber Cable, Dual LC / Dual LC, 5.0m
FODLC-IND-10	MM IP67 Fiber Cable, Dual LC / Dual LC, 10.0m

Item # Description

10 Gigabit Laser Optimized Multimode Fiber Optic Cables, 50/125 with OFNR Jackets

These revolutionary new fiber optic cables are constructed from the highest quality silica and are 100% factory tested. Connector options include SC and LC styles. Typically 10 Gigabit applications are run on 9/125 Single mode fibers, which require costly laser transceivers. By utilizing these fiber optic cables, users are able to implement high speed, low cost Multimode transceivers or VCSEL's (Vertical Cavity Surface Emitting Lasers) resulting in greater overall system cost savings. Custom lengths, connector combinations and polishes are available. Contact us today for details.

LC to LC Duplex 10 Gigabit Laser Optimized Multimode Fiber Optic Cables, 50/125 with OFNR Jacket

FODLC-10G-01 MM 10 Gig Fiber Cable, Dual LC / Dual LC, 1.0m FODLC-10G-02 MM 10 Gig Fiber Cable, Dual LC / Dual LC, 2.0m FODLC-10G-03 MM 10 Gig Fiber Cable, Dual LC / Dual LC, 3.0m FODLC-10G-04 MM 10 Gig Fiber Cable, Dual LC / Dual LC, 4.0m FODLC-10G-05 MM 10 Gig Fiber Cable, Dual LC / Dual LC, 5.0m

SC to SC Duplex 10 Gigabit Laser Optimized Multimode Fiber Optic Cables, 50/125 with OFNR Jacket

FODSC-10G-01 MM 10 Gig Fiber Cable, Dual SC / Dual SC, 1.0m FODSC-10G-02 MM 10 Gig Fiber Cable, Dual SC / Dual SC, 2.0m FODSC-10G-03 MM 10 Gig Fiber Cable, Dual SC / Dual SC, 3.0m FODSC-10G-04 MM 10 Gig Fiber Cable, Dual SC / Dual SC, 4.0m FODSC-10G-05 MM 10 Gig Fiber Cable, Dual SC / Dual SC, 5.0m

Military Grade 62.5/125 Fiber Optic Patch Cables

L-com's Military Grade fiber optic patch cables are built with specialized Military Tactical fiber cable that features impact and crush resistance characteristics which comply with Military requirements. Additionally, these robust assemblies are rated for operating temperatures of -40° to +75° Celsius. Three versions are available including Duplex ST, SC and LC styles. Our ST assemblies feature rust resistant stainless steel bodies and extra high force springs to ensure tight mating even when exposed to shock and vibration often encountered in the field under combat conditions.

ST to ST Duplex Military Grade Multimode Fiber Optic Cables, 62.5/125 with Polyurethane Jacket

FODSTMIL-01 MM Military Grade Fiber Cable, Dual ST / Dual ST, 1.0m FODSTMIL-02 MM Military Grade Fiber Cable, Dual ST / Dual ST, 2.0m FODSTMIL-03 MM Military Grade Fiber Cable, Dual ST / Dual ST, 3.0m FODSTMIL-05 MM Military Grade Fiber Cable, Dual ST / Dual ST, 5.0m FODSTMIL-10 MM Military Grade Fiber Cable, Dual ST / Dual ST, 10.0m

SC to SC Duplex Military Grade Multimode Fiber Optic Cables, 62.5/125 with Polyurethane Jacket

MM Military Grade Fiber Cable, Dual SC / Dual SC, 1.0m FODSCMIL-01 FODSCMIL-02 MM Military Grade Fiber Cable, Dual SC / Dual SC, 2.0m FODSCMIL-03 MM Military Grade Fiber Cable, Dual SC / Dual SC, 3.0m FODSCMIL-05 MM Military Grade Fiber Cable, Dual SC / Dual SC, 5.0m FODSCMIL-10 MM Military Grade Fiber Cable, Dual SC / Dual SC, 10.0m

LC to LC Duplex Military Grade Multimode Fiber Optic Cables, 62.5/125 with Polyurethane Jacket

FODLCMIL-01	MM Military Grade Fiber Cable, Dual LC / Dual LC, 1.0m
FODLCMIL-02	MM Military Grade Fiber Cable, Dual LC / Dual LC, 2.0m
FODLCMIL-03	MM Military Grade Fiber Cable, Dual LC / Dual LC, 3.0m
FODLCMIL-05	MM Military Grade Fiber Cable, Dual LC / Dual LC, 5.0m
FODLCMIL-10	MM Military Grade Fiber Cable, Dual LC / Dual LC, 10.0n