


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/6/10	D.GRIFFIN

DESCRIPTION	MATERIAL	PLATING
BODY 1	BRASS	NICKEL
BODY 2	BRASS	NICKEL
DIELECTRIC	TEFLON	-
CENTER PIN 1	BRASS	GOLD
CENTER PIN 2	BRASS	GOLD
RETAINING RING	BRASS	NICKEL
GASKET	RUBBER	-
PRESS FIT GROUND RING	BRASS	NICKEL
SHELL	BRASS	NICKEL
STAMP WASHER	BRASS	NICKEL



**NOTES:**

**ELECTRICAL:**

IMPEDANCE: 50 OHMS  
 DIELECTRIC WITHSTAND VOLTAGE: 2500 VOLTS PEAK  
 FREQUENCY RANGE: DC ~ 11 GHz  
 INSERTION LOSS: .15 dB MAX.  
 VOLTAGE RATING: 1500 V PEAK

**MISCELLANEOUS:**

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC PS-0031.

ALL DIMENSIONS ARE FOR REFERENCE ONLY

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS D. CASTRO CHECKED BY K. BURGNER APPROVED BY K. BURGNER	DATE 4/6/10 4/6/10 4/6/10	<b>L-com</b> Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY <b>COAXIAL</b>
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b> DWG. NO. AXA-NMNF90
SCALE: NONE		CAD FILE: AXA-NMNF90.SLDRW	SHEET 1 OF 1