



**10W to 12W Interchangeable Plug Series
PSC12R Adapter Series Meets EISA and Energy Star Requirements**



Features

- Double Insulated
- Field Changeable AC Plugs
- Efficiency Level V Compliance
- Class B EMI
- Less Than 0.3W No-Load Current
- Over-Voltage Protection

Applications

- Wireless Communications
- Networking
- Portable Equipment
- Peripherals

Safety Approvals

- cUL/UL
- CCC
- SAA
- Ecodesign ErP Directive 2009/125/EC
- CE
- ENERGY STAR
- C-Tick

Mechanical Characteristics

- Length: 71.7mm (2.82in)
- Width: 45mm (1.77in)
- Height: 32.39mm (1.27in)
- Weight: 75g (2.65oz)

Output Specifications

Model	DC Output Voltage	Load		Efficiency Level
		Min.	Max.	
PSC12R-050	5V	0A	2.0A	V
PSC12R-090	9V	0A	1.11A	V
PSC12R-120	12V	0A	1.0A	V

Interchangeable Clips Sold Separately

Input:

AC Input Voltage Rating
100 to 240V AC

AC Input Voltage Range
90 to 264V AC

AC Input Frequency
47 to 63Hz

Input Current
0.5A (RMS) maximum at 120V AC
0.25A (RMS) maximum at 240V AC

Leakage Current
0.25mA maximum at 264V AC

Inrush Current
30A for 120V AC at maximum load
60A for 240V AC at maximum load

Input Power Saving
0.3W maximum at no load

Output:

Efficiency
Meets requirements for ENERGY STAR EPS2.0 level V efficiency and Ecodesign ErP Directive 2009/125/EC level 2 annex 1b

Ripple (Vp-p)
5V 200mV
9V 180mV
12V 240mV

Hold-up Time
10mS minimum at maximum load

Short-Circuit Protection
Output can be shorted permanently without damage

Over-Current Protection
Short circuit protection – auto-restart

Environmental:
Temperature
Operation 0 to +40°C
Non-operation -40 to +85°C

Humidity
Non-Condensing 10 to 90%

Emissions
FCC Class B
EN55022 Class B

Immunity
EN61000-4-2 Level 3
EN61000-4-3 Level 2
EN61000-4-4 Level 2
EN61000-4-5 Level 2
EN61000-4-6 Level 3
EN61000-4-11
EN61000-3-2 Harmonic
EN61000-3-3 Flicker

Dielectric Withstand (Hi-pot) Test
Primary to Secondary: 3000V AC 1 min., 10mA

DC Output Connector
2.1 x 5.5mm center positive standard

Mating Connector
Kycon KLD-0202-A or Equivalent

AC Input Clips (sold separately)
RPA: US RPI: India
RPB: Brazil RPK: UK
RPC: China RPN: Argentina
RPE: Europe RPS: Australia
RPH: Korea

Dimension Diagram Unit: mm

