Products > LEDs > Thru-Hole > Round > 3mm > Mechanical Features > Short Lens



Features / Options

- ► State-of-the-Art, High Brightness Chip Technology
- ► Choice of Colors and Lens Finishes
- ► Lead Frame / Lens Casting Reliability
- ► Easy-to-Solder Leads, Tin Finish
- ► Available Bulk or on Tape and Reel
- ► Lead Trimming and Forming Available
- ► Custom Shapes, Easily Tooled, Low Minimum


Applications / Uses

- ► Board or Panel Indication or Illumination
- ► Annunciator and Control Panels
- ► Telecom Switches and Central Station Equipment
- ► Large Panel Indicators

Part Number:	Brightness	Dice Material	Emitted Color	Peak Wavelength	Epoxy Lens	Operating Typ Vf (V)	Intensity Typ, mcd @ 20 mA	View Angle 2x Theta	Sample	
SSL-LX3044AC	STANDARD	GaAsP	Amber	605	Clear	2.1	80	30		_
SSL-LX3044AD	STANDARD	GaAsP	Amber	605	Diffused	2.1	15	60		_
SSL-LX3044GC	STANDARD	GaP	Green	565	Clear	2.1	100	30		_
SSL-LX3044GD	STANDARD	GaP	Green	565	Diffused	2.1	40	60		_
SSL-LX3044HC	STANDARD	GaP	Red	700	Clear	2.0	25	30		_
SSL-LX3044HD	STANDARD	GaP	Red	700	Diffused	2.0	6	60		_
SSL-LX3044IC	STANDARD	GaAsP	Red	635	Clear	2.0	125	30		_
SSL-LX3044ID	STANDARD	GaAsP	Red	635	Diffused	2.0	30	60		_
SSL-LX3044OD	STANDARD	GaP	Orange	630	Diffused	2.0	30	60		
SSL-LX3044PGC	STANDARD	GaP	Green	555	Clear	2.1	15	30		_

UNCONTROLLED DOCUMENT

Ø3.20 [Ø0.126] — Ø2.90 [Ø0.114]



PART NUMBER SSL-LX3044GC

F F

REV.	E.C.N. NUMBER AND REVISION COMMENTS	DATE
Α	REMOVED FLAT EDGE FROM FLANGE,	4.28,92
В	CHG'D WAVELENGTH TO 565nm.	6.10.92
C	CHG'D CURRENT SPECS.	10.26.92
D	UPDATED SPECS.	11.18.94
Ε	UPDATED MEW ANGLE.	2.20,95
F	E.C.N. #10BRDR, & REDRAWN IN 3D.	5 .8. 01

	ELECTRO-OPTICAL CH	ARACTERI	ISTICS TA=25°C	;	$I_f = 20mA$	
	PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
B	PEAK WAVELENGTH		565		nm	
	FORWARD VOLTAGE		2.2	2.6	V_f	
	reverse voltage	5.0			V_{r}	I _r =100μΑ
	AXIAL INTENSITY		100		mcd	$I_f = 20 \text{mA}$
E	VIEWING ANGLE		30		2x theta	
	EMITTED COLOR:	GREEN				
	EPOXY LENS FINISH:	WATER	CLEAR			

☐ LIMITS OF SAFE OPERATION AT 25°C

	PARAMETER	MAX	UNITS
C	PEAK FORWARD CURRENT*	150	mA
	STEADY CURRENT	25	mA
	POWER DISSIPATION	105	mW
	DERATE FROM 25°C	– 1 . Б	mW/°C
	OPERATING, STORAGE TEMP.	- 40 TO + 85	.c
	SOLDERING TEMP.	+ 260	.c
	2.0mm FROM BODY		3 SEC. MAX

^{*} t<10µS

UNCONTROLLED DOCUMENT

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECINAL PRECISION ARE: X=±1 (±0.039), XX=±0.5 (±0.020), XXX=±0.25 (±0.010), XXXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= +DECINAL PRECISION MAX.= +0.00 (±0.000), XXX=±0.25 (±0.010), XXXX=±0.127 (±0.005).

F SSL-LX3044GC

T-3mm (T-1) 565nm GREEN LED, WATER CLEAR LENS.

CONFIDENTIAL INFORMATION

THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX NO. EXCEPT AS SPECTROALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OF IN PART FROM DISOLOGISURE AND DISSEMINATION TO ALL THIRD PARTIES.

RELABILITY NOTE

OUR MANY YEARS OF EXPERENCE DATA ACCUMULATION INDICATE THAT

SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE.

PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.

× ₽	LUMEN

DRAWN BY: CHECKED BY: APPROVED BY: DATE: 5.30.90
PAGE: 1 OF 1
BC SCALE: N/A