



APC Smart-UPS RT 192V Battery Pack

Part Number: SURT192XLBP



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Options](#) [Ratings and Reviews](#)

Batteries & Runtime

Battery Volt-Amp-Hour Capacity	1920
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Replacement Battery (Service center technician only)	APCRBC140
Battery mounting	Stand alone battery stack
Battery manufacturer	--
Expected Battery Life (years)	3 - 5
Included Battery Modules	4
RBC Quantity	2
Replacement battery cartridge note	Replace all batteries in operation together (UPS internal and external batteries) all-at-once
Battery blocks per string	16

Physical

Net Weight	200.00 lbs. (90.91 kg)
Maximum Height	5.10 inches (130 mm)
Maximum Width	17.00 inches (432 mm)
Maximum Depth	26.00 inches (660 mm)

Shipping Weight	223.00 lbs. (101.36 kg)
Shipping Width	23.63 inches (600 mm)
Shipping Height	16.25 inches (413 mm)
Shipping Depth	39.38 inches (1000 mm)
Rack Height	3U
Color	Black
Units per Pallet	4.00

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Standard warranty	2 years repair or replace, optional on-site warranties available, optional extended warranties available
-------------------	--

Sustainable Offer Status

EOLI	Available in Documentation tab
Other Environmental Compliance	China RoHS

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.