

Products


LED Indicators

CML IT offers panel mount indicators manufactured with LED, Neon or Incandescent light sources. These indicators are available in a number of different lens and termination styles, with voltages of 2V ~ 250V available off-the-shelf.

	<p> Part Number: 5110F3-5V Serial Number: 5110 Mounting hole (inch): 5/32" Mounting hole (metric): 3.97mm Indicator type: Mounting type: Bezel type: Bezel material: Bezel color: Bezel size: Protection: Lens type: Lens color: Amber Diffused Lens size: Connector tpe: 6.0" 24 AWG wire Connector number: Connector for lamp test: Number LED chip: Indicator color: Amber Dom wave length: Peak wave length (mA): 583.0 Op. voltage (V): 5.0 Forward volt max: 7.5 Rectifier: AC current: DC current: 10.0 Lum in min (mcd): 2.2 Lum in type (DC): 8.0 Voltage type (%): Op. temperature (°C): Storage temperature (°C): Narrative: Viewing angle (°): 60 RoHS Status: Yes </p>
--	--

5110F Series Panel Mounted LED Indicator Light

DESCRIPTION AND FEATURES



Features

- Super Brite T-1 LED
- Diffused lens allows wide angle viewing.
- Low current -only 2 mA.
- Built-in chip resistor operates directly off 5 and 12 volt supply , no external resistor needed.

Mounting: Will snap-fit into Ø.155/.158 hole in panels .031/.062 thick*

Wire Leads: No.24 AWG, 6" long, stripped .250

Anode(+): Red lead

Housing: Black Nylon

*We recommend using an installation tool to press against flange of housing rather than LED.

ELECTRO-OPTICAL CHARACTERISTICS

Part Number	Color	Typ. Intensity (mcd)	Rated Current (mA)	Continuous Forward Current Max. (mA)	Forward Voltage Typ. (V)	Forward Voltage Max. (V)	Peak Forward Current @ 1ms-300pps (A)	Reverse Break-down Voltage Min. (V)	Peak Wavelength (nm)
5110F1	Red	10	10	30	2.0	3.0	1.0	5	635
5110F3	Amber	7	10	25	2.0	3.0	.09	5	603
5110F5	Green	16	20	30	2.2	3.0	.09	4	562
5110F7	Yellow	6.3	20	30	2.1	3.0	1.0	5	585
5110F1LC	Red	2.5	2	7	1.8	2.2	.007	5	635
5110F5LC	Green	2.1	2	7	1.8	2.2	.007	5	565
5110F7LC	Yellow	1.8	2	7	1.9	2.7	.007	5	583
5110F1-5V	Red	8.0	10	20	5	7.5	-	5	655
5110F3-5V	Amber	8.0	10	15	5	7.5	-	5	583
5110F5-5V	Green	8.0	10	15	5	7.5	-	5	565
5110F1-12V	Red	8	13	20	12	15	-	5	655
5110F3-12V	Amber	8	13	20	12	15	-	5	583
5110F5-12V	Green	8	13	20	12	15	-	5	565