SNAP Digital Input Modules

Features

- > Four channels per module
- 4,000-volt transient isolation
- Convenient pluggable wiring terminals
- Channel-specific LEDs
- Operating temperature: 0 to 70 °C
- UL and CE approved
- Accepts up to 14 AWG wire
- Factory Mutual approved (part numbers ending in FM)



SNAP Digital Input Modules

Description

Opto 22 SNAP I/O digital input modules are part of the SNAP PAC System. Optical isolation on these modules provides 4,000 volts of transient (4000 V for 1 ms) protection for sensitive control electronics from industrial field signals. Digital input modules can sense either AC or DC signals.

All SNAP digital modules have removable top-mounted connectors to provide easy access for field wiring, and all operate on 5 VDC control logic. Each digital module features integral channel-specific LEDs for convenient troubleshooting and maintenance. Each module is factory tested twice and is UL and CE approved. In addition, part numbers ending in FM are Factory Mutual approved.

SNAP input modules are used to sense the on or off status for AC or DC voltages from such sources as proximity switches, push buttons, or auxiliary contacts. The SNAP-IDC5G is ideal for detecting 48 VDC in telecom applications. The SNAP-IDC5-HT is designed for sensors that have a high leakage current.

The SNAP-IDC5-SW and SNAP-IDC5-SW-NC modules supply power to an external dry contact switch and sense

Part Numbers

Part	Description			
SNAP-IAC5	SNAP 4-channel 90-140 VAC input, 5 VDC logic			
SNAP-IAC5A	SNAP 4-channel 180–280 VAC input, 5 VDC logic			
SNAP-IAC5MA*	SNAP 4-channel isolated 90–140 VAC/VDC input, 5 VDC logic, with manual/auto switches			
SNAP-IAC5FM	SNAP 4-channel 90–140 VAC/VDC input, 5 VDC logic, Factory Mutual approved			
SNAP-IAC5AFM	SNAP 4-channel 180–280 VAC input, 5 VDC logic, Factory Mutual approved			
SNAP-IDC5	SNAP 4-channel 10–32 VDC input, 5 VDC logic			
SNAP-IDC5D	SNAP 4-channel 2.5–28 VDC input, 5 VDC logic			
SNAP-IDC5FAST	SNAP 4-channel high-speed 2.5–16 VDC input, VDC logic			
SNAP-IDC5-FAST-A*	SNAP 4-channel high-speed 18–32 VDC input, 5 VDC logic			
SNAP-IDC5G*	SNAP 4-channel 35–75 VAC/DC input, 5 VDC logic			
SNAP-IDC5AF	SNAP 4-channel high-speed 75–140 VDC input, 5 VDC logic			
SNAP-IDC5GF	SNAP 4-channel high-speed 35–75 VDC input, 5 VDC logic			
SNAP-IDC5HT	SNAP 4-channel 15-32 VDC leakage-tolerant input, 5 VDC logic			
SNAP-IDC5MA	SNAP 4-channel isolated high-speed 10–32 VAC/VDC input, 5 VDC logic, with manual/auto switches			
SNAP-IDC5-SW*	SNAP 4-channel switch status input, normally open			
SNAP-IDC5-SW-NC*	SNAP 4-channel switch status input, normally closed			
SNAP-IDC5FM	SNAP 4-channel 10–32 VDC input, 5 VDC logic, Factory Mutual approved			
SNAP-IDC5DFM	SNAP 4-channel 2.5-28 VDC input, 5 VDC logic			
SNAP-RETN4	SNAP 4-module retention rail (OEM)			
SNAP-RETN4B	SNAP 4-module retention rail, 25-pack (OEM)			
SNAP-RETN6	SNAP 6-module retention rail (OEM)			
SNAP-RETN6B	SNAP 6-module retention rail, 25-pack (OEM)			
SNAP-FUSE4AB	SNAP 4-amp fuse, 25-pac			
* III. approval ponding				

^{*} UL approval pending

Specifications: DC Input Modules (continued)

See page 7 for SNAP-IDC5-SW and SNAP-IDC5-SW-NC specifications and wiring.)

SNAP Digital Input Modules

	SNAP-IDC5FAST*	SNAP-IDC5-FAST-A**	SNAP-IDC5MA	
Key Feature	High-speed	High-speed	Diagnostic switches	
Field Side Ratings (each channel)				
Nominal Input Voltage	5 VDC	28 VDC	24 VAC/VDC	
Channel-to-channel isolation	300 VAC (1,500 V transient)	300 VAC (1,500 V transient)	300 VAC (1,500 V transient)	
Input Voltage Range	2.5-16 VDC	18–32 VDC	10-32 VAC/VDC	
Turn-on Voltage	2.5 VDC	18 VDC	10 VAC/VDC	
Turn-off Voltage	1 VDC	5 VDC	3 VAC/VDC	
Input Resistance	440 ohms (nominal)	8 K ohms (nominal)	15 K ohms (nominal)	
Logic Side Ratings				
Logic Output Voltage	<.5 V max. (on) @ 2 mA sinking 2.7 V min. (off) @ 0.4 mA sourcing	<.5 V max. (on) @ 2 mA sinking 2.7 V min. (off) @ 0.4 mA sourcing	<.5 V max. (on) @ 2 mA sinking 2.7 V min. (off) @ 400 mA sourcing	
Logic Supply Voltage***	5 VDC ± 0.25 VDC	5 VDC ± 0.25 VDC	5 VDC ± 0.25 VDC	
Logic Supply Current	50 mA maximum	50 mA maximum	50 mA maximum	
Negative True Logic Output Drive	TTL 74 Series = 1 UL TTL 74LS Series = 5 UL	TTL 74 Series = 1 UL TTL 74LS Series = 5 UL	TTL 74 Series = 1 UL TTL 74LS Series = 5 UL	
Module Ratings				
Number of Channels Per Module	4	4	4	
Turn-on Time	.025 msec*	.025 msec**	5 msec	
Turn-off Time	.025 msec*	.025 msec**	15 msec	
Optical Isolation (Field Side to Logic Side)	4,000 volts (transient)	4,000 volts (transient)	4,000 volts (transient)	
Temperature	0 °C to 70 °C, operating -30 °C to 85 °C, storage	0 °C to 70 °C, operating -30 °C to 85 °C, storage	0 °C to 70 °C, operating -30 °C to 85 °C, storage	

^{*} At 20kHz, 5Vp-p square wave input, 50% duty cycle.


^{**} At 20kHz, 28Vp-p square wave input, 50% duty cycle.

^{***} When used with an I/O processor (brain or on-the-rack controller), the processor requires 5.0 to 5.2 VDC.

SNAP Digital Input Modules

Dimensional Drawing

All Modules Except MA



*** +/- .030" **** +/- .060" NO * REFERENCE ONLY

PAGE 12

SNAP Digital Input Modules

Dimensional Drawing

All Models

SNAP Digital Module Mounted on SNAP Rack

