

HyperLink Wireless brand 2.4 GHz 8 dBi High Performance Omnidirectional Wireless LAN Antenna - Model: HGV-2409U

Applications and Features

Applications:	• • • •	2.4 GHz ISM Band IEEE 802.11b and 802.11g Wireless LAN Bluetooth® Public Wireless Hotspot WiFi Wireless Video Systems Multipoint and Mobile Applications
Features:	• • • •	High performance Economical Compact, lightweight design Durable UV-stable fiberglass radome Vented end cap and drain holes in base

- All weather operation
- Integral N-Female connector
- Can be installed in up or down positions
- Includes Mast Mounting Kit

Description

High Performance


The HyperGain® Model HGV-2409U is and economical yet high performance omnidirectional Wi-Fi antenna designed for the 2.4GHz ISM band. These compact and lightweight antennas are ideally suited for IEEE 802.11b and 802.11g wireless LANs, Bluetooth, public wireless hotspot application and other multipoint applications where wide coverage is desired.

Versatile and Economical

This antenna features an integral N-Female bulkhead type connector that mounts through the wall of an equipment enclosure. Included with the HGV-2409U is a mast mounting kit. Consisting of a heavy-duty steel bracket and a pair of U-bolts, this kit allows installation on masts up to 2.0" in diameter.

All Weather Operation

Constructed for all weather operation, the HGV-2409U features sealed collinear brass elements inside a durable UV-stable machine gray fiberglass radome. A vented end cap and drain holes in the base help prevent moisture build-up inside the antenna. These features allow the HGV-2409U to be mounted in up or down positions.








Specifications

Frequency	2400-2500 MHz
Frequency	2400-2500 MHZ
Gain	8 dBi
Polarization	Vertical
Vertical Beam Width	15°
Horizontal Beam Width	360°
Impedance	50 Ohm
Max. Input Power	100 Watts
VSWR	< 1.5:1 avg.
Weight	1.1 lbs. (0.5 kg)
Length	19.7 in. (50 cm)
Base Diameter	1.27 in. (3.22 cm)
Radome Diameter	.75 in. (1.90 cm)
Radome Material	Gray Fiberglass
Wind Survival	>150 MPH
Operating Temperature	-40° C to to 85° C (-40° F to 185° F)
Connector	Integral N-Type Female (Bulkhead type)

RF Antenna Gain Pattern



Guaranteed Quality

This product is backed by Hyperlink's Limited Warranty.



Mounting Options

1	1.0
1	1995

Ceiling/Wall Universal Antenna Mount can be used with HyperLink's 4.5" sq and **HGX-UMOUNT02** 8.5" sq. patch antennas as well as N-Type bulkhead and TNC/BNC bulkhead omni directional antennas. Includes ceiling/wall mounting hardware.