

What can we help you find?

## 7012PD Product Details

[Share](#) | [Print](#) | [Email](#)


**7012PD**

TE Internal Number: 2-1423159-6

 Active

### Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- 7000 Electropneumatic Timing - Industrial Series
- Input Voltage = 125 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 240 VAC
- Mounting Options = Panel Mount

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Series = 7000 Electropneumatic Timing - Industrial
- Termination Type = Screw Terminal

#### Mechanical Attachment:

- Mounting Options = Panel Mount

#### Electrical Characteristics:

- Input Voltage (VDC) = 125
- Contact Rating = 10A @ 240 VAC

#### Dimensions:

- Approx. Dimensions (L x W x H) (mm [in]) = 114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]

#### Contact Features:

- Delay Time = 5 seconds to 50 seconds
- Type of Control = Knob
- Repeatability, Max. =  $\pm 5\%$

#### Configuration Features:

- [Contact - Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

#### Industry Standards:

- Approved Standards = CE Approved, CSA Certified, FM Approved, UL Listed
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Conditions for Usage:

- Temperature Range (°C) = -30 - +75

#### Operation/Application:

- Mode of Operation = On-Delay

#### Other:

- Brand = Agastat