

What can we help you find?

## 7022AD Product Details

[Share](#) | [Print](#) | [Email](#)


**7022AD**

TE Internal Number:  
1423162-7

 Active

### Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- 7000 Electropneumatic Timing - Industrial Series
- Input Voltage = 110 VAC, 120 VAC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 240 VAC
- Mounting Options = Panel Mount

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

## Documentation & Additional Information

### Product Drawings:

- None Available

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files:

- None Available

### Additional Information:

- [Product Line Information](#)

### Related Products:

- [Tooling](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- Series = 7000 Electropneumatic Timing - Industrial
- Termination Type = Screw Terminal

### Mechanical Attachment:

- Mounting Options = Panel Mount

### Electrical Characteristics:

- Input Voltage (VAC) = 110, 120
- Contact Rating = 10A @ 240 VAC

### Dimensions:

- Approx. Dimensions (L x W x H) (mm [in]) = 114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]

### Contact Features:

- Delay Time = 5 seconds to 50 seconds
- Type of Control = Knob
- Repeatability, Max. =  $\pm 5\%$

### Configuration Features:

- [Contact - Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

### Industry Standards:

- Approved Standards = CE Approved, CSA Certified, FM Approved, UL Listed
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

### Conditions for Usage:

- Temperature Range (°C) = -30 - +75

### Operation/Application:

- Mode of Operation = Off-Delay

### Other:

- Brand = Agastat