Digital Phosphor Oscilloscopes

TDS3000C Series



Performance You Need at a Price You Can Afford

Performance in an Affordable Package

The TDS3000C Series digital phosphor oscilloscopes (DPO) provide you with the performance you need at a price you can afford. Bandwidths range from 100 MHz to 500 MHz, with up to 5 GS/s sample rates for accurate representation of your signal.

DPOs Provide a Greater Level of Insight into Complex Signals

To solve a problem, first you need to see it. The TDS3000C Series combines 3,600 wfms/s continuous waveform capture rate and real-time intensity grading so you can see the problem and solve it.

Fast waveform capture rates on a continuous basis save time by quickly revealing the nature of faults so advanced triggers can be applied to isolate them.

Real-time intensity grading highlights the details about the history of a signal's activity, making it easier to understand the characteristics of the waveforms you've captured. Unlike other comparable oscilloscopes, the history remains even after the acquisition is stopped.

Quickly Debug and Characterize Signals with DRT Sampling Technology and sin(x)/x Interpolation

The TDS3000C Series combines unique digital real-time (DRT) sampling technology with sin(x)/x interpolation to allow you to accurately characterize a wide range of signal types on all channels simultaneously. With the TDS3000C Series there is no change in sampling rate when additional channels are turned on, unlike other comparable oscilloscopes. This sampling technology makes it possible to capture high-frequency information, such as glitches and edge anomalies, that elude other oscilloscopes in its class, while sin(x)/x interpolation ensures precise reconstruction of each waveform.

Features & Benefits

Key Performance Specifications

100 MHz, 300 MHz and 500 MHz bandwidth models 2 or 4 channels

Sample rates up to 5 GS/s real-time on all channels

10 k standard record length on all channels

3,600 wfms/s continuous waveform capture rate Suite of advanced triggers

Ease of Use Features

Front panel USB host port for easy storage and transfer of measurement data

25 automatic measurements FFT standard

Multiple language user interface WaveAlert[®] automatic waveform anomaly detection

TekProbe® interface supports active, differential and current probes for automatic scaling and units

Portable Design

Lightweight design (only 7 lbs/3.2 kg) for easy transport Optional internal battery operation provides up to three hours without line power

Application Modules for Specialized Analysis

Advanced analysis module Limit testing module Telecommunications mask testing module Extended video module 601 Serial digital video module

Applications

Digital design and debug Video installation and service Power supply design Education and training Telecommunications mask testing Manufacturing test General bench testing



Characteristics

TDS3000C Series Electrical Characteristics

| | TDS3012C | TDS3014C | TDS3032C | TDS3034C | TDS3052C | TDS3054C |
|---|---|--------------|-----------------|-----------------|-----------------|-----------------|
| Bandwidth | 100 MHz | 100 MHz | 300 MHz | 300 MHz | 500 MHz | 500 MHz |
| Calculated Rise | 3.5 ns | 3.5 ns | 1.2 ns | 1.2 ns | 0.7 ns | 0.7 ns |
| Time (typical) | | | | | | |
| Input Channels | 2 | 4 | 2 | 4 | 2 | 4 |
| External Trigger Input Included on all models | | | | | | |
| Sample Rate on | 1.25 GS/s | 1.25 GS/s | 2.5 GS/s | 2.5 GS/s | 5 GS/s | 5 GS/s |
| Each Channel | | | | | | |
| Record Length | 10 k points | | | | | |
| Vertical Resolution | 9 bits | | | | | |
| Vertical Sensitivity, 1 M Ω | 1 mV/div to 10 V/div | | | | | |
| Vertical Sensitivity, 50 Ω | 1 mV/div to 1 V/div | | | | | |
| Input Coupling | AC, DC, GND | | | | | |
| Input Impedance | 1 M $m \Omega$ in parallel with 13 pF or 50 $m \Omega$ | | | | | |
| DC Gain Accuracy | <u>+</u> 2% | | | | | |
| Maximum Input Voltage, 1 | ximum Input Voltage, 1 MΩ 150 V _{RMS} with peaks at \leq 400 V | | | | | |
| Maximum Input Voltage, 50 | 0Ω 5 V _{RMS} with peaks at $\leq 30 V$ | | | | | |
| Position Range | ± 5 div | | | | | |
| Bandwidth Limit | 20 MHz | 20 MHz | 20 MHz, 150 MHz | 20 MHz, 150 MHz | 20 MHz, 150 MHz | 20 MHz, 150 MHz |
| Time Base Range | 4 ns to 10 s | 4 ns to 10 s | 2 ns to 10 s | 2 ns to 10 s | 1 ns to 10 s | 1 ns to 10 s |
| Time Base Accuracy | ± 20 ppm over any 1 ms time interval | | | | | |

Input/Output Interfaces

| Ethernet Port | RJ-45 connector, supports 10Base-T LAN | | |
|------------------------|---|--|--|
| USB Port | Front-panel USB 2.0 host port | | |
| | Supports USB flash drive | | |
| GPIB Port | Full talk/listen modes, setting and measurements | | |
| | (Optional with TDS3GV Communications Module) | | |
| RS-232-C Port | DB-9 male connector, full talk/listen modes; control of all modes, settings and measurements | | |
| | Baud rates up to 38,400 | | |
| | (Optional with TDS3GV Communications Module) | | |
| VGA Video Port | DB-15 female connector, monitor output for direct display on large VGA-equipped monitors | | |
| | (Optional with TDS3GV Communications Module) | | |
| External Trigger Input | BNC connector, input impedence > 1 M Ω in parallel with 17 pF; max input voltage is 150 V _{RMS} | | |

Acquisition Modes

DPO – Captures and displays complex waveforms, random events and subtle patterns in actual signal behavior. DPOs provide 3 dimensions of signal information in real time: Amplitude, time and the distribution of amplitude over time.

Peak Detect – High frequency and random glitch capture. Captures glitches as narrow as 1 ns (typical) using acquisition hardware at all time base settings. WaveAlert[®] – Monitors the incoming signals on all channels and alerts the user to any waveform that deviates from the normal waveform being acquired. Sample – Sample data only.

Average – Waveform averaged, selectable from 2 to 512.

Envelope – Min-max values acquired over one or more acquisitions.

Single Sequence – Use the Single Sequence button to capture a single triggered acquisition sequence at a time.

Trigger System

Main Trigger Modes – Auto (supports Roll Mode for 40 ms/div and slower), Normal, Single Sequence. B Trigger – Trigger after time or events. Trigger After Time Range – 13.2 ns to 50 s. Trigger After Events Range – 1 to 9,999,999 events.

Trigger Types

Edge – Conventional level-driven trigger. Positive or negative slope on any channel. Coupling selections: AC, DC, Noise Reject, HF Reject, LF Reject. Video – Trigger on all lines or individual lines, odd/even or all fields on NTSC, PAL, SECAM. Extended Video – Trigger on specific lines in broadcast and non-broadcast (custom) standards and on analog HDTV formats (1080i, 1080p, 720p, 480p). Requires TDS3VID or TDS3SDI application module. Pulse Width (or Glitch) – Trigger on a pulse width <, >, =, ≠ to a selectable time limit ranging from 39.6 ns to 50 s. **Runt** – Trigger on a pulse that crosses one threshold but fails to cross a second threshold before crossing the first again.

Slew Rate – Trigger on pulse edge rates that are either faster or slower than a set rate. Edges can be rising, falling or either.

Pattern – Specifies AND, OR, NAND, NOR when true or false for a specific time.

State – Any logic state. Triggerable on rising or falling edge of a clock. Logic triggers can be used on combinations of 2 inputs (not 4).

Comm – Provides isolated pulse triggering required to perform DS1/DS3 telecommunications mask testing per ANSI T1.102 standard. Requires

TDS3TMT application module.

Alternate – Sequentially uses each active channel as a trigger source.

Digital Phosphor Oscilloscopes

► TDS3000C Series

Waveform Measurements Cursors – Amplitude, Time.

Automatic Measurements – Display any four measurements from any combination of waveforms. Or display all measurements with measurement snapshot feature. Measurements include Period, Frequency, +Width, –Width, Rise time, Fall time, +Duty cycle, –Duty cycle, +Overshoot, High, Low, Max, Min, Peak-to-peak, Amplitude, Mean, Cycle mean, RMS, Cycle RMS, Burst width, Delay, Phase, Area*1, Cycle Area*1.

Measurement Statistics – Mean, Min, Max, Standard deviation. Requires TDS3AAM application module.

Thresholds – User-definable thresholds for automatic measurements; settable in percent or voltage. Gating – Isolate a specific occurrence within an acquisition to take measurements, using either the screen or cursors.

Waveform Math

Arithmetic – Add, subtract, multiply and divide waveforms.

FFT – Spectral magnitude. Set FFT vertical scale to Linear RMS or dBV RMS and FFT window to Rectangular, Hamming, Hanning or Blackman-Harris. **Advanced Math*1** – Integrate, Differentiate, Define extensive algebraic expressions including analog waveforms, math functions, scalars, up to two useradjustable variables and results of parametric measurements. For example: (Intg (Ch1–Mean(Ch1)) x 1.414 x VAR1).

Waveform Processing

Autoset – Single-button, automatic setup of all channels for vertical, horizontal and trigger systems, with undo autoset.

Deskew – Channel-to-channel deskew ± 10 ns may be manually entered for better timing measurements and more accurate math waveforms.

Display Characteristics

Display Type – 6.5 in. (165.1 mm) liquid crystal TFT color display.

Display Resolution – 640 horizontal x 480 vertical pixels (VGA).

Interpolation - Sin(x)/x.

Waveform styles – Dots, vectors, variable persistence, infinite persistence.

Graticules – Full, grid, cross-hair and frame. NTSC, PAL, SECAM and vectorscope (100% and 75% color bars) with optional TDS3VID or TDS3SDI application modules.

Format – YT, XY and Gated XYZ (XY with Z-axis blanking available on 4-channel instruments only).

Power Source

AC line power

 $\begin{array}{l} \textbf{Source voltage} - 100 \ V_{\text{RMS}} \ to \ 240 \ V_{\text{RMS}} \ \pm 10\%.\\ \textbf{Source frequency} - 45 \ \text{Hz} \ to \ 440 \ \text{Hz} \ from \ 100 \ V \\ to \ 120 \ \text{V}; \ 45 \ \text{Hz} \ to \ 66 \ \text{Hz} \ from \ 120 \ V \ to \ 240 \ \text{V}.\\ \textbf{Power consumption} - 75 \ \text{W} \ maximum.\\ \textbf{Battery power} - \ \text{Requires TDS3BATC, rechargeable} \\ lithium \ ion \ battery \ pack. \ Operating \ time, \ typical \ - \\ 3 \ hours. \end{array}$

Environmental and Safety

| | Operating | Non-operating | |
|-------------------------------|--|------------------|--|
| Temperature | 0 °C to +50 °C | -40 °C to +71 °C | |
| Humidity | Operating and Non-operating: up to 95% RH at or below +30 °C | | |
| | Operating and Non-operating: up to 45% RH +30 °C up to +50 °C | | |
| Altitude | To 3,000 m | 15,000 m | |
| Electromagnetic Compatibility | Meets or exceeds EN61326 Class A, Annex D radiated and conducted emissions and immunity; | | |
| | EN6100-3-2 AC Powerline Harmonic Emissions; EN6100-3-3 Voltage Changes, Fluctuation and Flicker; | | |
| | FCC 47 CFR, Part 15, Subpart B, Class A; Australian EMC framework | | |
| Safety | UL61010B-1, CSA1010.1, IEC61010-1, EN61010-1 | | |

Physical Characteristics

Instrument Dimensions mm in 375 14.8 Width Height 176 6.9 Depth 149 5.9 Weight lbs. kg Instrument only 3.2 7 with accessories 4.5 9.8

Instrument Shipping

| Package Dimensions | mm | in. |
|--------------------|-----|------|
| Width | 502 | 19.8 |
| Height | 375 | 14.8 |
| Depth | 369 | 14.5 |

Rackmount (RM3000)

| Dimension | mm | in. |
|-----------|-----|-----|
| Width | 484 | 19 |
| Height | 178 | 7 |
| Depth | 152 | 6 |

*1 Requires TDS3AAM application module.

Digital Phosphor Oscilloscopes

TDS3000C Series

Ordering Information

TDS3000C Series Digital Phosphor Oscilloscopes

TDS3012C – 100 MHz, 2 Channel, 1.25 GS/s. TDS3014C – 100 MHz, 4 Channel, 1.25 GS/s. TDS3032C – 300 MHz, 2 Channel, 2.5 GS/s. TDS3034C – 300 MHz, 4 Channel, 2.5 GS/s. TDS3052C – 500 MHz, 2 Channel, 5 GS/s. TDS3054C – 500 MHz, 4 Channel, 5 GS/s.

Standard Accessories

P6139A – 500 MHz, 10x passive probe (one per channel).

User Manual and Translated Front Panel

Overlay – Please specify preferred language option. **Power Cord** – Please specify plug option.

Accessory Tray

Protective Front Cover

OpenChoice® PC Communication Software –

Enables fast and easy communication between Windows PC and the TDS3000C series via LAN, GPIB or RS-232. Transfer and save settings, waveforms, measurements and screen images.

NI LabVIEW SignalExpress[™] Tektronix

Edition LE – A fully interactive measurement software environment optimized for the TDS3000C series. Enables you to acquire, generate, analyze, compare, import and save measurement data and signals using intuitive drag-and-drop user interface that does not require any programming. Standard TDS3000C series support for acquiring, controlling, viewing and exporting your live signal data is permanently available through the software. A 30-day trial period of the full version provides additional signal processing, advance analysis, mixed signal, sweeping, limit testing and user-defined step capabilities. Order SIGEXPTE for permanent full version capability.

Traceable Certificate of Calibration – NIM/NIST. Documentation CD

3 Year Warranty – Covering all labor and parts excluding probes and accessories.

Options

International Power Plug Options

Opt. A0 – North America. Opt. A1 – Universal Euro. Opt. A2 – United Kingdom. Opt. A3 – Australia. Opt. A5 – Switzerland. Opt. A6 – Japan. Opt. A10 – China. Opt. A11 – India. Opt. A99 – No power cord.

Language Options

Opt. L0 – English. Opt. L1 – French. Opt. L2 – Italian. Opt. L3 – German. Opt. L4 – Spanish. Opt. L5 – Japanese. Opt. L6 – Portuguese. Opt. L7 – Simplified Chinese. Opt. L8 – Traditional Chinese. Opt. L9 – Korean. Opt. L10 – Russian. Opt. L99 – No manual.

Recommended Accessories

TDS3GV – GPIB, VGA, RS-232 interface. TDS3AAM – Advanced Analysis Module. Adds extended math capability, arbitrary math expressions, measurement statistics and additional automated measurements.

TDS3LIM – Limit Testing Module. Adds custom waveform limit testing capabilities. TDS3TMT – Telecom Mask Testing Module. Adds pass/fail compliance of ITU-T G.703 and ANSI T1.102 standards, custom mask testing and more. TDS3VID – Extended Video Analysis Module. Adds video quickmenu, autoset, hold, line count trigger, video picture mode, vectorscope*² mode, HDTV format trigger graticules and more.

TDS3SDI – Serial/Digital Video Module. Adds 601 serial digital video to analog video conversion, video picture, vectorscope,*² and analog HDTV triggering capabilities and more.

TDS3BATC – Lithium ion battery pack for up to 3 hours continuous operation without line power. **TDS3CHG** – Fast charger for battery pack.

AC3000 – Soft case for carrying instrument. HCTEK4321 – Hard plastic case for carrying instrument (requires AC3000).

RM3000 - Rackmount kit.

SIGEXPTE – NI LabVIEW SignalExpress[™] Tektronix Edition Software full version.

Service Manual – English only (071-2507-00). TNGTDS01 – Extensive instructions and step-by-step lab exercises provide education about the operation of TDS3000C Series Oscilloscopes. Kit includes self-paced CD-ROM based manual and signal source board. Optional hard copy manual available for order separately.

Recommended Probes

P6243 – 1 GHz, ≤1 pF input C 10X active probe. P5205 – 1.3 kV, 100 MHz high voltage differential probe. P5210 – 5.6 kV, 50 MHz high voltage differential

probe. **P5100** – 2.5 kV, 100X high voltage passive probe. **TCP202** – 50 MHz, 15 A AC/DC current probe. **TCP303**^{*3} – 15 MHz, 150 A current probe. **TCP305**^{*3} – 50 MHz, 50 A current probe. **TCP312**^{*3} – 100 MHz, 30 A current probe. **TCP404XL**^{*4} – 2 MHz, 500 A current probe. **TCP404XL**^{*4} – 2 MHz, 500 A current probe. **TCP4400** – 50 MHz probe amplifier. **ADA400A** – 100X, 10X, 1X, 0.1X high gain differential amplifier.

Service Options

Available at time of purchase

Opt. CA1 – Provides a single calibration event or coverage for the designated calibration interval, whichever comes first.
Opt. C3 – Calibration Service – 3 years.
Opt. C5 – Calibration Service – 5 years.
Opt. D1 – Calibration Data Report.
Opt. D3 – Calibration Data Report – 3 years (with Option C3).

Opt. D5 - Calibration Data Report -

5 years (with Option C5).

Opt. R5 - Repair Service - 5 year.

Available after purchase

TDS30xxC-CA1 – Provides a single calibration event or coverage for the designated calibration interval, whichever comes first.

TDS30xxC-R1PW – Repair service coverage 1 year post warranty.

TDS30xxC-R2PW – Repair service coverage 2 years post warranty.

TDS30xxC-R5DW – Repair service coverage 5 years (includes product warranty period); 5 year period starts at time of customer instrument purchase.

*2 Vectorscope does not support composite video.

*³ Requires TCPA300 probe amplifier.

*4 Requires TCPA400 probe amplifier.