# Preferred Heat Shrink Products

## HEAVY WALL, ADHESIVE LINED, IRRADIATED POLYOLEFIN

**RoHS COMPLIANT** FIT.-621

## **CHOOSE FIT**-621 For:

- Over Expanded to a 6 to 1 Shrink Ratio
- Shrinks to 1/6 its Original Size
- Heavy Duty Adhesive Inner Lining
- Low Water Absorption
- Excellent Durability and Toughness
- Resistant to Oils and Chemicals
- Convenient Pre-cut 6 Inch Lengths

## **FIT**-621 **APPLICATIONS:**

- Protection in Severe Environments
- Large to Small Connector-to-Cable
- Underground Utility Splice Protection
- Corrosion Protection of Metal Parts
- Protects Substrates in Direct Burial **Applications**
- Heavy Duty Abrasion Resistance

## **CHARACTERISTICS**

#### **OPERATING TEMPERATURE:**

■ -55°C to 90°C

#### **SHRINKAGE RATIO:**

Approximately 6 to 1 at 121°C

#### **COLOR DESCRIPTION:**

■ All Standard Packages: Black

#### **PHYSICAL PROPERTIES:**

- Tensile Strength: 1200 psi, (84 kg/cm²)
- Ultimate Elongation: 200%
- Longitudinal Shrinkage: −10%
- Specific Gravity: 1.4
- Low Temperature Flexibility: To -55°C (No Crackina)

#### **CHEMICAL PROPERTIES:**

- Corrosive Effect: Non-Corrosive
- Fungus Resistance: No Growth
- Water Absorption: 0.5%
- Chemical Resistance: JP-8 Hydraulic Fluids, Deicing Fluid, Lubricating Oil

#### **ELECTRICAL PROPERTIES:**

- Dielectric Strength: 200V/mil (79 kV/cm)
  Volume Resistivity: 10<sup>13</sup> ohm cm

### **SPECIFICATIONS**

■ RoHS Compliant





Alpha Part No. and Size	Minimum Supplied I.D. Inches mm		Maximum Rec. I.D. Inches mm		Nom. Rec. Wall Thickness Inches mm		Standard Package
<b>FIT</b> -621-5/8	0.60	15,24	0.150	3,81	0.060 1,	52	10 x 6 In. Lengths (5 Feet) 3 x 6 In. Lengths (1.5 Feet)
<b>FIT</b> -621-1-1/4	1.25	31,75	0.220	5,59	0.059 1,4	49	10 x 6 In. Lengths (5 Feet) 3 x 6 In. Lengths (1.5 Feet)
<b>FIT</b> -621-2	2.00	50,80	0.375	9,50	0.105 2,7	70	10 x 6 In. Lengths (5 Feet) 3 x 6 In. Lengths (1.5 Feet) 24 x 6 In. Lengths (12 Feet)
<b>FIT</b> -621-2-1/2	2.50	63,50	0.500	12,70	0.120 3,0	05	10 x 6 In. Lengths (1.5 Feet) 3 x 6 In. Lengths (1.5 Feet)
<b>FIT</b> -621-3	3.00	76,20	0.750	19,05	0.120 3,0	05	10 x 6 In. Lengths (5 Feet) 3 x 6 In. Lengths (1.5 Feet)
<b>FIT</b> -621-4	4.00	101,60	0.900	22,86	0.140 3,	55	10 x 6 In. Lengths (5 Feet) 3 x 6 In. Lengths (1.5 Feet)



