ALPHA WIRE COMPANY CUSTOMER PRODUCT SPECIFICATION							
CU Part Number: 2401C Page 1 of 2 Pages			STOMER PRODUCT SP	Issue: Issue Date: Effective Date:	5 5/20/2005 8/1/2005		
A.		nstruction			Diameters		
	1)	Component 1 a) Conductor	2 X 1 COND 22 (7/30) AWG TC				
		b) Insulation	0.016" Wall, Nom. Polyethyl	ene(PF)	0.062		
		(1) Color(s)	e.e.e				
		Cond Color 1 BLACK	Cond Color 2 NATURAL	Cond Color			
	2)	Cable Assembly	2 Components Cabled				
	2)	a) Twists:	6.9 Twists/foot (min)				
	3)	Shield:	Alum/Mylar Tape, 25% Over	lap, Min.			
	,	a) Foil Direction	Foil Facing Out	•			
		b) Drain Wire	22 (7/30) AWG TC				
	4)	Jacket	0.020" Wall, Nom.,PVC		0.168 (0.178 Max.)		
		a) Color(s) b) Print	GRAY ALPHA WIRE-* P/N 2401C				
		b) Print	SHIELDED 75C (UL) TYPE)		
			LLXXXXXX CSA TYPE CM	G FT4 ROHS			
			* = Factory Code				
			[Note: Product may have c(UL) or (CSA markings depending	g upon plant of manufacture.]		
5.		lustry Approvals					
	1)	UL	AWM/STYLE2092 CM	60°C / 300V 75°C			
			VW-1	750			
	2)	CSA International	CMG	60°C			
	-,		FT4				
	3)						
			All materials used in the ma				
			Directive 2002/95/EU regard				
			substances in electrical and		nt. Consult Alpha Wire's		
	4)	California Proposition 65.	web site for compliance Dat The outer surface materials		cture of this part meet the		
	- T)		requirements of California P		otare or this part meet the		
C.	Physical & Mechanical Properties						
	1)	Temperature Range	-20 to 75°C				
	2)	Bend Radius	10X Cable Diameter				
		Pull Tension	16.5 Lbs, Maximum				
D.		ectrical Properties	(For Engineering purposes	only)			
		Voltage Rating	300 V _{RMS}	anduator to Conduc	stor		
		Capacitance Ground Capacitance	20 pf/ft @1 kHz, Nominal C 36 pf/ft @1 kHz, Nominal				
	3) 4)	Characteristic Impedance					
		Inductance	0.2 µH/ft, Nominal				
		Conductor DCR	16.3 Ω/1000ft @20°C, Nor	inal			
		OA Shield DCR	11.7 Ω/1000ft @20°C, Nom				
-	Ótł		-				

Ε. 1) Packaging

- a) 1000 FT
 - b) BOX 1000FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE COMPANY CUSTOMER PRODUCT SPECIFICATION

Part Number: 2401C	Issue:	5	
Page 2 of 2 Pages	Issue Date:	5/20/2005	
	Effective Date:	8/1/2005	

c) BOX 500FT

d) 500 FT

e) 328 FT

f) 100 FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.