

Replacement Products

Resistance Soldering Accessories



Precision Timer Module Model 105PTM

Combine the intense power of resistance soldering with precision cycle time repeatability!

Specifications:

- Designed for use with Power Units set at or below 1,200 Watts.
- Digital LCD Timer Module w. multiple functionality
- Run light, Lighted Rocker Switch, 10 AMP Circuit Protection & Heavy-duty aluminum case, Available in 110 or 220V.
- Rugged, Industrial Footswitch with 6 foot (1.83m) w. 3.5mm micro-jack plug for low voltage activation.
- Three conductor, Detachable AC Cord set.

Weight: 1.5LBS (0.675KGS)



Footswitch Model 10519

For foot control of most power units up to and including 1800 Watts. Eliminates sparking on contact and removal of electrodes from work. Provides more accurate timing of soldering operations. Recommended in most applications. A rugged, industrial switch with six foot (1.83m) three-wire cord and NEMA 5-15 P/R piggyback plug.

Weight: 1.0LBS (0.45KGS)



Twist-Lock Footswitch Model 10518

Same as Model 10519, except with two-wire Midget Twist Lock plug. Must be used with Twist Lock style resistance soldering Power Units when using a standard handpiece. (105B2TL, 105C1TL, 105C2)

Weight: 1.0LBS (0.45KGS)



Grounding Vise for Holding Parts Hands-Free Model 105V12

- This versatile accessory functions as a holding fixture while providing a return path to the power unit.
- For use with single electrode resistance soldering or tweezer handpieces with Model 105Y10 adapter.
- Work is held at a comfortable 3 1/2" (88.9mm) height.
- Compatible with American Beauty resistance soldering power units up to and including Model 105C2 at 1,800W and all single electrode handpieces.
- 6" (15.24cm) extension cable included.

Weight: 3.5LBS (1.575KGS)

See Product Data Sheet



Lead for Return
Current - Alligator Clamp
Model 10512A

Specifications:

- 14 AWG Cable
- Taper Pin Connection Style

Weight: 0.3LBS (0.135KGS)

Used with the following tools:

- 10515 3/32" Diameter Single Carbon Handpiece
- 10572 1/8" Diameter Single Carbon Handpiece
- 10573 3/16" Diameter Single Carbon Handpiece
- 10552 5/64" Diameter Single Stainless Steel Handpiece



Leads for Return
Current - Standard Clamp
Model 10512

Specifications:

- 10 AWG Cable
- Taper Pin Connection Style

Weight: 0.4LBS (0.18KGS)

Used with the following tool:

• 10511 - Standard 1/4" Diameter Single Carbon Handpiece



Lead for Return
Current - Heavy-Duty "C" Clamp
Model 10537

Specifications:


6 AWG Cable

• Ring Terminal Connection Style

Weight: 0.6LBS (0.27KGS)

Used with the following tool:

• 10536 - 1/2" Diameter Heavy-Duty Single Carbon Handpiece



Panel Attachement for 100 and 250 Watt Power Units Model 10595

Attaches to Power Units 105A3 or 105A12 to hold two 1/8" (3.18mm) diameter, adjustable electrodes. Takes the place of "standing soldering iron", but draws full current only when working. For soldering and desoldering. Popular for auto-electric remanufacturing.

Weight: 1.0LBS (0.45KGS)

Replacement Electrodes: Model # 10594



Panel Attachement for 1,100 Watt Power Unit Model 10513A

Attaches to Model 105B2 Power Unit to hold two electrodes. Comes with two 1/4" (6.35mm) and two 3/8" (9.53mm) diameter carbon electrodes and two Adapter Bushings, Model 10538. Used to desolder and assemble automotive alternators, starters for autoelectric rebuild, bus bar and similar electrical work.

Included in system:

• 10535 - Medium Electrical Work Resistance Soldering System

Weight: 6.0LBS (2.7KGS)

Replacement Electrodes: Model # 10549

See Product Data Sheet



Panel Attachement for 1,800 Watt Power Unit Model 10513B

Same as Model 10513A, except for use with Power Unit Model 105C1.

Weight: 6.0LBS (2.7KGS)

Replacement Electrodes: Model # 10550

See Product Data Sheet



Handpiece Adapter Model 105Y10

Connects both jaws of soldering tweezers to one terminal of power unit. Must use with a grounding accessory, Model 10512 recommened. The part held by tweezers is heated when in contact with grounded workpiece. The result is more even heating between the two electrodes of the handpiece. Excellent for hobbyists for brass locomotives and scratch building.

Weight: 1.0LBS (0.45KGS)

No Photo **Available**

General Operating Instructions Model 105_Series

See Product Data Sheet

American Beauty Soldering Tools are proudly manufactured by Assembly Technologies International, Inc.

1177 West Maple Road Clawson, MI 48017-1059 **United States** (800) 550-2510 (248) 280-2810

Fax: (248) 280-2878

info@assemblytech.com