



Pencil Style Soldering Irons

These Pencil-Style Soldering Irons Define Quality!

Designed and built to give top performance under the most demanding production line conditions and to withstand rugged usage in all maintenance and repair operations. Plug-type tip is seated deep in element for quick heat transfer. Modular design provides for easy maintenance. Please take a moment to examine our Model V3600 Voltage Control Station and all of the advantages it brings to your operation.

Features & Benefits:

- Ni-Chrome Wound Heating Element Proven industry's most reliable heating element.
- o Paragon® Iron-Clad Tips Outlasts ordinary tips many times over!
- o Iron Uses Plug-Type Tips Superior heat transfer. Minimizes maintenance.
- o Intricate Thermal Management Design Baffles deflect heat from handle.
- Air-Cooled Finger Grip Improves operator comfort; pencil-style gives precise control.
- Modular Construction Easy replacement of any part.



Little Dandy Pencil-Style Soldering Iron Model 3108

Common Applications: Ideal for soldering miniature and small electronic connections, printed circuit board work and integrated circuits.

Specifications:

- WATTAGE 20, 25, 30 Watts
- REPLACEMENT HEATING ELEMENT NUMBER 9014
- MAXIMUM TIP TEMPERATURE (F) 805°F, 900°F, 970°F
- MAXIMUM TIP TEMPERATURE (C) 429°C, 482°C, 521°C
- OVERALL LENGTH 61/2" (16.5cm)
- TIP SHANK DIAMETER 1/8" (3.18mm)
- TIP LENGTH 21/4" (5.27cm)
- PRODUCT WEIGHT 2 oz. (56.7g)
- SHIPPING WEIGHT 1/2"lb. (226.7g)

The following Paragon® tip comes standard with this item:

• 501 - Paragon Soldering Iron Tips

We also offer the following additional Paragon® tips for this item: 502, 503, 505, 507, 510, 512



Little Dandy Pencil-Style Soldering Iron Model 3110

Common Applications: Perfect for soldering small to medium electronic and electrical connections.

Specifications:

- WATTAGE 25, 30, 35 Watts
- REPLACEMENT HEATING ELEMENT NUMBER 9010
- MAXIMUM TIP TEMPERATURE (F) 835°F, 890°F, 940°F
- MAXIMUM TIP TEMPERATURE (C) 446°C, 477°C, 504°C
- OVERALL LENGTH 61/2" (16.5cm)
- TIP SHANK DIAMETER 3/16" (4.72mm)
- TIP LENGTH 21/4" (5.27cm)
- PRODUCT WEIGHT 3 oz. (85g)
- SHIPPING WEIGHT 1/2"lb. (226.7g)

The following Paragon® tip comes standard with this item:

• 618 - Paragon Soldering Iron Tips

We also offer the following additional Paragon[®] tips for this item: 604, 605, 607, 610, 613, 615, 617, 625, 626, 627, 630, 643, 646



Little Dandy Pencil-Style Soldering Iron **Model 3112**

Common Applications: The right soldering iron for soldering electrical and electronic connections such as lugs and posts. Enough heat for light to intermediate sheet metal and leaded glasswork.

Specifications:

- WATTAGE 40, 50, 60 Watts
- REPLACEMENT HEATING ELEMENT NUMBER 9012
- MAXIMUM TIP TEMPERATURE (F) 950°F, 1050°F, 1130°F
- MAXIMUM TIP TEMPERATURE (C) 510°C, 566°C, 610°C
- OVERALL LENGTH 7¾" (19.7cm)
- TIP SHANK DIAMETER 1/4" (6.35mm)
- TIP LENGTH 21/4" (5.27cm)
- PRODUCT WEIGHT 4½ oz. (127.6g)
- SHIPPING WEIGHT ½"lb. (226.7g)

The following Paragon® tip comes standard with this item:

• 720 - Paragon Soldering Iron Tips

We also offer the following additional Paragon® tips for this item: 701, 703, 704, 706, 714, 715, 716, 721, 724, 730, 738, 739, 749

> American Beauty Soldering Tools are proudly manufactured by Assembly Technologies International, Inc. 1177 West Maple Road

Clawson, MI 48017-1059 **United States** (800) 550-2510 (248) 280-2810

Fax: (248) 280-2878