ALPHA WIRE COMPANY CUSTOMER PRODUCT SPECIFICATION

Part Number: 6311 Issue: 3

Page 1 of 2 Pages Issue Date: 5/23/2005 Effective Date: 8/1/2005

A. Construction <u>Diameters</u>

1) Component 1 40 X 1 COND a) Conductor 24 (7/32) AWG TC

b) Insulation 0.010" Wall, Nom. PVC, Semi Rigid 0.044

(1) Color Code Alpha Wire Color Code F

Cond	Color	Cond	Color	Cond	Color
1	BLACK	15	BLUE/WHITE	29	WHITE/RED/GREEN
2	WHITE	16	BLACK/RED	30	RED/BLACK/GREEN
3	RED	17	WHITE/RED	31	GREEN/BLACK/ORANGE
4	GREEN	18	ORANGE/RED	32	ORANGE/BLACK/GREEN
5	ORANGE	19	BLUE/RED	33	BLUE/WHITE/ORANGE
6	BLUE	20	RED/GREEN	34	BLACK/WHITE/ORANGE
7	WHITE/BLACK	21	ORANGE/GREEN	35	WHITE/RED/ORANGE
8	RED/BLACK	22	BLACK/WHITE/RED	36	ORANGE/WHITE/BLUE
9	GREEN/BLACK	23	WHITE/BLACK/RED	37	WHITE/RED/BLUE
10	ORANGE/BLACK	24	RED/BLACK/WHITE	38	BLACK/WHITE/GREEN
11	BLUE/BLACK	25	GREEN/BLACK/WHITE	39	WHITE/BLACK/GREEN
12	BLACK/WHITE	26	ORANGE/BLACK/WHITE	40	RED/WHITE/GREEN
13	RED/WHITE	27	BLUE/BLACK/WHITE		
14	GREEN/WHITE	28	BLACK/RED/GREEN		

2) Cable Assembly 40 Components Cabled a) Twists: 2.5 Twists/foot (min)

3) Shield: Alum/Mylar Tape, 25% Overlap, Min.

a) Foil Direction Foil Facing Out
b) Drain Wire 24 (7/32) AWG TC

4) Jacket 0.040" Wall, Nom., PVC 0.406 (0.429 Max.)

a) Color(s) GRAY

b) Print ALPHA WIRE-* P/N 6311 40/C 24 AWG

SHIELDED 75C (UL) TYPE CM OR AWM 2464 --- LLXXXXXX

CSA TYPE CMG FT4 ROHS

* = Factory Code

[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]

B. Industry Approvals

1) UL AWM/STYLE2464 80°C / 300V

CM 75°C

VW-1

2) CSA International CMG 60°C

FT4

3) EU Directive 2002/95/EC(RoHS):

All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.

4) California Proposition 65: The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

C. Physical & Mechanical Properties

1) Temperature Range -20 to 80°C

2) Bend Radius3) Pull Tension10X Cable Diameter144 Lbs, Maximum

D. Electrical Properties (For Engineering purposes only)

1) Voltage Rating 300 V_{RMS}

2) Capacitance 32 pf/ft @1 kHz, Nominal Conductor to Conductor

3) Ground Capacitance 58 pf/ft @1 kHz, Nominal 4) Inductance 0.19 µH/ft, Nominal

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described berein

ALPHA WIRE COMPANY CUSTOMER PRODUCT SPECIFICATION

Part Number: 6311 Issue: 3

Page 2 of 2 Pages Issue Date: 5/23/2005 Effective Date: 8/1/2005

5) Conductor DCR

6) OA Shield DCR

E. Other

1) Packaging

- a) 1000 FT
- b) 500 FT
- c) 100 FT

26 Ω /1000ft @20°C, Nominal 13.4 Ω /1000ft @20°C, Nominal

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.