ALPHA WIRE COMPANY **CUSTOMER PRODUCT SPECIFICATION**

Part Number: 6418 Issue:

Page 1 of 2 Pages **Issue Date:** 5/26/2005 **Effective Date:** 8/1/2005

A. Construction **Diameters**

1) Component 1 3 X 1 PAIR

22 (7/.0096) AWG TC a) Conductor

0.013" Wall, Nom. PVC 0.055 b) Insulation ALPHA NUMERIC NUMBERS - 1-ONE ALTERNATING AND (1) Print

INVERTED 2 INCH SPACING(CTR. TO CTR.)

(2) Color Code Alpha Wire Color Code BR

Pair	Color	Pair	Color	Pair	Color
1	BLACK#1-RED#1	2	BLACK#2-RED#2	3	BLACK#3-RED#3

c) Pair 2/Cond Cabled Together (1) Twists: 8.0 Twists/foot (approx.) 3 Components Cabled Cable Assembly 4.4 Twists/foot (min) a) Twists:

b) Core Wrap Clear Mylar Tape, 25% Overlap, Min. 3) Shield: Alum/Mylar Tape, 25% Overlap, Min.

a) Foil Direction Foil Facing In b) Drain Wire 24 (7/32) AWG TC

4) Jacket 0.043" Wall, Nom., PVC 0.288 (0.302 Max.)

a) Color(s) **GRAY**

ALPHA WIRE-* P/N 6418 3PR 22 AWG b) Print

> SHIELDED 105C (UL) TYPE PLTC SUN. RES. OR TYPE CM --- LLXXXXXX CSA TYPE CMG FT4 ROHS

* = Factory Code

[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]

B. Industry Approvals

1) UL CM 105°C **PLTC** 105°C **SUN RES**

CSA International **CMG** 60°C

FT4

EU Directive 2002/95/EC(RoHS):

All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.

4) California Proposition 65: The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

C. Physical & Mechanical Properties

1) Temperature Range -20 to 105°C Bend Radius 2) 10X Cable Diameter 3) Pull Tension 34 Lbs, Maximum

D. Electrical Properties (For Engineering purposes only)

1) Voltage Rating 300 V_{RMS}

2) Mutual Capacitance 34 pf/ft @1 kHz, Nominal 3) Ground Capacitance 61 pf/ft @1 kHz, Nominal

Characteristic Impedance 66 Ω

5) Inductance 0.19 µH/ft, Nominal

6) Conductor DCR 18 Ω/1000ft @20°C, Nominal

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described

ALPHA WIRE COMPANY CUSTOMER PRODUCT SPECIFICATION

Part Number: 6418 Issue: 4

Page 2 of 2 Pages Issue Date: 5/26/2005 Effective Date: 8/1/2005

7) OA Shield DCR

15.9 Ω/1000ft @20°C, Nominal

E. Other

1) Packaging

a) 1000 FT

b) 500 FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.