ALPHA WIRE COMPANY CUSTOMER PRODUCT SPECIFICATION

Part Number: 2414C Issue: 5

Page 1 of 2 Pages Issue Date: 5/20/2005 Effective Date: 8/1/2005

A. Construction <u>Diameters</u>

1) Component 1 4 X 1 COND

a) Conductor 20 (7/28) AWG TC

b) Insulation 0.016" Wall, Nom. Polyethylene(PE) 0.070

(1) Color(s)

Cond	Color	Cond	Color	Cond	Color
1	BLACK	3	NATURAL		
2	RED	4	GREEN		

2) Cable Assembly 4 Components Cabled a) Twists: 4.8 Twists/foot (min)

3) Shield: Alum/Mylar Tape, 25% Overlap, Min.

a) Foil Direction Foil Facing Out
b) Drain Wire 20 (7/28) AWG TC

4) Jacket 0.020" Wall, Nom., PVC 0.213 (0.224 Max.)

a) Color(s) GRAY

b) Print ALPHA WIRE-* P/N 2414C 4/C 20 AWG

SHIELDED 75C (UL) TYPE CM OR AWM 2094 ----LLXXXXXX CSA TYPE CMG FT4 ROHS

* = Factory Code

[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]

B. Industry Approvals

1) UL AWM/STYLE2094 60°C / 300V

CM 75°C

VW-1

2) CSA International CMG 60°C

FT4

3) EU Directive 2002/95/EC(RoHS):

All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.

4) California Proposition 65: The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

C. Physical & Mechanical Properties

1) Temperature Range -20 to 75°C

2) Bend Radius 10X Cable Diameter 3) Pull Tension 44 Lbs, Maximum

D. Electrical Properties (For Engineering purposes only)

1) Voltage Rating 300 V_{RMS}

2) Capacitance 20.7 pf/ft @1 kHz, Nominal Conductor to Conductor

3) Ground Capacitance 37 pf/ft @1 kHz, Nominal 4) Inductance 0.19 µH/ft, Nominal

5) Conductor DCR 10.2 $\Omega/1000$ ft @20°C, Nominal 8.2 $\Omega/1000$ ft @20°C, Nominal

E. Other

1) Packaging

a) 1000 FT

b) BOX 1000FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described berein

ALPHA WIRE COMPANY CUSTOMER PRODUCT SPECIFICATION

Part Number: 2414C Issue: 5

Page 2 of 2 Pages Issue Date: 5/20/2005 Effective Date: 8/1/2005

c) BOX 500FT

d) 500 FT

e) 328 FT

f) 100 FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.