

1259

EXPLOSION-PROOF

- Will not cause an explosion in certain ignitable gas-air and dust-air atmospheres*



IMPACT RESISTANT

- Heavy duty construction minimizes potential for damage to light
- Break resistant lens protects lamp from damage



NON-CONDUCTIVE

- Protects user from immediate electrical shock



IDENTIFIABLE

- Internationally known color for instant recognition



HANDY

- Hanger ring in end cap gives ability to hang up or belt-carry



MSHA approved for use in methane-air mixture and UL listed for Division I and II, Class I, Group C and D environments. *For use in gas-air mixtures of Acetone, Butane, Benzene, Diethyl Ether, Ethyl and methyl Alcohols, Gasoline, Methane (natural gas), Naphtha and Propane. Approved also for use in dust-air mixtures of Class II, Group G. Designed so that if lamp is broken, electrical circuit will be opened before filament can ignite these flammable or explosive gas-air mixtures in the surrounding atmosphere.



WARNING:

USE ONLY PR-2 AND 2 SIZE "D" 1.5 VOLT ALKALINE BATTERIES.
RISK OF EXPLOSION – DO NOT OPEN IN HAZARDOUS AREA. TO PREVENT THE IGNITION OF A HAZARDOUS ATMOSPHERE, BATTERIES MUST ONLY BE CHANGED IN AN AREA KNOWN TO BE NON-HAZARDOUS.

Before Using Your Flashlight:

Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation: Industrial
2 D Mine Safety Light
UL/MSHA/CSA approved

Model: 1259

Color: Safety Orange

Power Source: Two "D"

ANSI/NEDA: 15 Series

Lamp: PR-2

Lamp Rating: 2.4V, 0.5A


Lamp Life: 15 Hours

Lamp Output: 11.4 Lumens

Typical Weight: 113 grams (4.0 oz.)
(without batteries)

Dimensions (in): 2.37 x 2.37 x 8

Performance:



Important Notice

This datasheet contains information specific to products manufactured at the time of its publication

Contents herein do not constitute a warranty
©Energizer / All Rights Reserved