


DO NOT SCALE THIS DRAWING

REVISIONS				
SYM	DESCRIPTION	DATE	E.C.O. NO.	APPR.
A	OFFICIAL ENG. RELEASE TO MFG.	2-8-63	7660	
U	REDRAWN, NO CHANGES	4/5/91	38053	DR
V	CHANGE PUSHOUT / WAS 12LBS	2/26/92	38819	CPM
W	ADDED NOTES 5 THRU 8 ADDED CABLE ENTRY DIM ADDED PLATE LETTERS ITEMS 3, 9, 10, 11 & 12 WERE S/A 31-5333-1 CHANGED PLATE NOTE 4 REMOVED NOTES 2 & 3.	10/1/92	39185	




28000
DRAWING NUMBER ISSUE
W

NOTES:

1. PLATING MUST CONFORM TO AMPHENOL SPEC. 349-50560. CONTACT IS SILVER PLATED, ALL OTHER METAL PARTS ARE ASTROPLATED (REF).
4. ITEM 1 TO WITHSTAND A PUSH OUT LOAD OF 6 LBS AFTER STAKING.
5. MUST CONFORM TO AMPHENOL SPEC. 349-50551, SEC. 303. OMIT REFERENCE TO CONTACT.
6. PACKAGE THIS CONNECTOR IN BAG 999-226.
7. ITEMS 2, 5, 6, 7 & 8 WILL BE PACKAGED LOOSE.
8. ASTERISK (*) INDICATES CABLE ENTRY DIM'S.

31-914 H	1	12	WASHER	NOTE 1
95631	1	11	WASHER	SEE COMP.
31-10720-H	1	10	RING	NOTE 1
82-1535-3	1	9	GASKET	
28005-H	1	8	CLAMP NUT	NOTE 1
82-946-22H	1	7	CLAMP WASHER	NOTE 1
28007-H	1	6	CLAMP GASKET	NOTE 1
28004-H	1	5	BRAID CLAMP	NOTE 1
31-10852-H	1	4	BODY	NOTE 1
31-1500 G	1	3	BAYONET SLEEVE	NOTE 1
28003-F	1	2	CONTACT	NOTE 1
28002	1	1	INSULATOR	

PART NO.	QUAN	UOM	DESCRIPTION	CODE	FINISH
28002	1	1	INSULATOR		



RECOMMENDED CABLE STRIPPING DIM'S

REMOVE ALL BURR, BREAK CORNERS AND SHARP EDGES TO MAXIMUM UNLESS OTHERWISE SPECIFIED

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request, and (3) are confidential and are not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp. or by any other person to anyone for any purpose is not to be regarded by implication or otherwise as in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications or other data.

H:\DEPT611\MHV\000\ASSY\28000

NEXT ASSY	USED ON	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES NOT OTHERWISE SPECIFIED ARE:
		2 PLACE DECIMAL 0.015 (0.381 mm)
		3 PLACE DECIMAL 0.005 (0.127 mm)
		ANGLES ± 1°
MATERIAL		REFERENCE DRAWING NO. SIGNAL CORP SPEC SC-C-83132
SPECIFICATION		G.E. SPEC 175A1001 Rev A
FINISH		

DRAWN BY	DATE	TITLE
TERRI ALBERA	4/4/91	MINI H.V. PLUG FOR RG59/U CABLE 5000V UG-932/U
CHECKED ABR	5-26-81	
ENGINEER H.G.H.	6-2-81	
QUALITY ASSURANCE N.J. SLADEK	6-2-81	
DATE	10-1-92	

Amphenol Corporation
RF/Microwave Operations
Danbury, Conn. U.S.A.

SCALE 6:1 SHEET OF

74868 C 28000 W