# ENGINEERING DATASHEET




D


EVEREADY BATTERY COMPANY, INC. www.energizer.com 1-800-383-7323 / CANADA - USA + 44 (0) 208 920 2306 / EUROPE


# ENERGIZER NO. NH50

# **Industry Standard Dimensions**



# **Typical Discharge Characteristics**





Classification:
Chemical System:

Designation: Nominal Voltage: Rated Capacity:

Typical Weight: Typical Volume: Jacket: ANSI-1.2H4 1.2 Volts

Nickel-Metal Hydride (NiMH)

Specifications

Rechargeable

2500 mAh (to 1.0 volts) Based on 500 mA (0.2C) discharge rate

73.0 grams (2.6 oz.) 56.5 cubic centimeters (3.5 cubic inch) Plastic Label

#### Internal Resistance:

The internal resistance of the cell varies with state of charge, as follows:

Cell ChargedCell 1/2 Discharged11 milliohms21 milliohms(tolerance of ±20% applies to above values)

### AC Impedance (No Load):

The impedance of the charged cell varies with frequency, as follows:

Frequency (Hz) 1000 Impedance (milliohms) (Charged Cell) 9

Above values based on AC current set at 1.0 ampere. Value tolerances are  $\pm 20\%$ .

#### **Operating and Storage Temperatures:**

To maintain maximum performance, observe the following general guidelines regarding environmental conditions.

Charge:	0°C to 40°C (32°F to 104°F)
Discharge:	0°C to 50°C (32°F to 122°F)
Storage:	-20°C to 30°C (-4°F to 86°F)
Humidity:	65±20%

Operating at extreme temperatures, will significantly impact battery cycle life.

## Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication. **Contents herein do not constitute a warranty.** ©Eveready Battery Company, Inc. - All Rights Reserved