

Hi-Current DC Power Supply 0-64V/0-15A Model 1795



The model 1795 is a cost effective, high power, regulated DC power supply with an output rating of (0 to 64V, 0 to 15A). It is a linear high current DC power supply suitable for bench operation or standard 19" rack operation. This linear power supply is a high power workhorse that will easily deliver clean power to your high current circuits.

- Constant Voltage/Constant Current Operation
- Remote Programming Facility
- Facility for Presetting the Output Voltage and Max.
- Load Current Limits
- Separate DC Output ON/OFF Switch
- Remote Sensing Facility
- High Stability and Close Regulation $\pm 0.01\%$
- Meet CE Specifications

Data Sheet

Models 1794, 1795 & 1796

Regulated DC Power Supplies

Models 1794, 1795 & 1796 are cost effective, high power, regulated DC power supplies. These linear power supplies are high power workhorses that will easily deliver clean power to your high-current circuits. Special features include the ability to set constant current with no load and remote sense to compensate for any wire loss.

The power supplies are designed to have superior performance to comparable models costing 20 to 30% more. Meets CE specifications.

- **Constant Voltage/Constant Current Operation**
- **Remote Programming Facility**
- **Facility for Presetting the Output Voltage and Max. Load Current Limits**
- **Separate DC Output ON/OFF Switch**
- **Remote Sensing Facility**
- **High Stability and Close Regulation $\pm 0.01\%$**
- **Meet CE Specifications**



Specifications models

	1794	1795	1796
Output (DC)	0-32V	0-64V	0-16V
Output Current (DC)	0-30A	0-15A	0-50A
Constant Voltage Mode			
Line Regulation		$\pm 0.01\% \pm 2\text{mV}$	
Load Regulation		$\pm 0.01\% \pm 2\text{mV}$	
Ripple and Noise		1mV rms max (20Hz - 20MHz)	
Constant Current Mode			
Line Regulation		$\pm 0.05\% \pm 10\text{mA}$	
Load Regulation		$\pm 0.05\% \pm 10\text{mA}$	
Ripple and Noise		6mA rms Max (20Hz - 20MHz)	
Overload Protection		Constant current type	
Stability		$\pm 0.2\% \pm 10\text{mV}$ in CV mode	
		$\pm 0.5\% \pm 10\text{mA}$ in CC mode	
Operating Temperature		32° to 104°F (0° to 40°C)	
Input		115V / 60 Hz	
Dimension (W x H x D)		19 x 5.25 x 15.75" (483 x 133 x 400mm)	
Accessories Supplied		User Manual	