

SCRIPTION

The Amphenol "SD" series features precision formed contacts and boardlocks.

This series gives you Amphenol's high standards of quality and reliability to meet all of your commercial requirements.

Economical right angle PCB mount connectors

Industrial

Telecom

Any industry standard
 I / O connections

Specifications

• Connectors according to: MIL C24308 - NFC 93425-HE5

	Materials and Platings
Shells	Steel, tin over nickel plating
Insulator	Glass-filled thermoplastic, UL 94V- 0
Pin contacts	Brass, selected gold in mating area;
	2.54μm (100 μ") min.tin on
	termination area over 1.27µm
	(50μ") min.nickel
Socket contact	Phosphor bronze, selected gold in
	mating area;2.54μ(100μ") min.tin
	on termination area over 1.27µm
	(50μ") min.nickel
Rear insert	Brass, 2.54µm (100µ") min.nickel plated
Boardlock	Phosphor bronze or Brass, 2.54µm
	(100µ") min.nickel plated
Screwlock	Brass, 2.54μm (100μ") min.nickel plated

	Electrical Data
Current rating	5A
Voltage rating	250V AC/ rms 50Hz
Withstanding voltage	1000V AC/rms 50Hz for one minute
Insulation resistance	1000MΩ at 500V DC
Contact resistance	15mΩ max

	Climatic Data
Operating temperature Salt spray	-55°C to +125°C 24 hours

Mechanical Data

Single contact insertion force 0.54kg (1.19lb) max Single contact withdrawal force 0.06kg (0.13lb) min

Mating and unmating force Unit: kg (lb)

	A4 S	Style	1A Style		
No. of Cts	Mate (max)	Unmate (min)	Mate (max)	Unmate (min)	
9	3.05 (6.74)	0.36 (0.79)	4.6 (10.17)	0.4 (0.88)	
15	5.09 (11.24)	0.46 (1.01)	7.7 (17.02)	0.5 (1.10)	
25	8.44 (18.66)	0.81 (1.8)	12.7 (28.07)	0.8 (1.77)	
37	12.51 (27.65)	1.1 (2.47)	17.7 (39.12)	1.2 (2.65)	

Standard plating thickness • gold • 0.38

• gold flash

• 0.381µm (15µ") gold


• 0.76 µm (30µ") gold

Ampheno, RoHS




MAIN CHARACTERISTICS

A4 style (MIL Footprint)




Nb OF	DIMENSIONS mm (inch)								
CONTACTS	A	В	С	D	E	F			
9	30.84 (1.21)	24.99 (.98)	16.92 (.67)	16.24 (.64)	11.09 (.44)	2.74 (.108)			
15	39.14 (1.54)	33.32 (1.31)	25.25 (.99)	24.56 (.97)	19.39 (.76)	2.74 (.108)			
25	53.04 (2.09)	47.04 (1.85)	38.96 (1.53)	38.38 (1.51)	33.24 (1.31)	2.77 (.109)			
37	69.32 (2.73)	63.50 (2.50)	55.42 (2.18)	54.76 (2.16)	49.86 (1.96)	2.77 (.109)			

1A style (European Footprint)




Nb OF	DIMENSIONS mm (inch)								
CONTACTS	A	В	С	D	E	F			
9	30.84 (1.21)	24.99 (.98)	16.92 (.67)	16.24 (.64)	11.96 (.43)	2.74 (.108)			
15	39.1 (1.54)	33.32 (1.31)	25.25 (.99)	24.66 (.97)	19.18 (.755)	2.74 (.108)			
25	53.09 (2.09)	47.04 (1.85)	38.96 (1.53)	38.38 (1.51)	33.24 (1.31)	2.77 (.109)			
37	69.4 (2.73)	63.50 (2.50)	55.42 (2.18)	54.84 (2.16)	49.86 (1.96)	2.77 (.109)			

Panel mounting option




Front Female Screwlock

4F / 3F



Threaded Rear Insert 4R / 3R

How to order




For special request, please consult factory





D-Sub connectors - Stamped and Formed Contacts

RIGHT ANGLE BOARD MOUNT CONNECTORS FOOTPRINT 14.99 mm (.590")



The Amphenol "SD" series features precision formed contacts and boardlocks.

This series gives you Amphenol's high standards of quality and reliability to meet all of your commercial requirements.

Specifications

• UL File: E119881

CHARACTERISTICS

• Connectors according to MIL C24308

	Materials and Platings						
Shells	Steel, tin over nickel plating						
Insulator	Glass-filled thermoplastic, UL 94V-0						
Pin contacts	Brass, selected gold in mating area;						
	2.54µm (100µ") min. tin						
	on termination area over						
	1.27µm (50µ") min. nickel						
Socket contact	Phosphor bronze, selected gold in						
	mating area; 2.54μm (100μ") min. tin-						
	on termination area over 1.27µm						
	(50µ") min. nickel						
Rear insert	Brass, 2.54µm (100µ") min. nickel plated						
Screwlock	Brass, 2.54µm (100µ") min. nickel plated						

Electrical Data
5A
600V AC/rms 50Hz
1000V AC/rms 50Hz for one minute
5000ΜΩ
10mΩ max

	Climatic Data
Operating temperature Salt Spray	-55°C to +125°C 24 hours

	Olimatic Data
Operating temperature Salt Spray	-55°C to +125°C 24 hours

	١	/	е	C	h	a	n	ij	ca	ı	D	a	ta	3
--	---	---	---	---	---	---	---	----	----	---	---	---	----	---

Mating and unmating force

Unit: kg (lb)

No. of Cts	Mate (max)	Unmate (min)
9 (size E)	3.05 (6.74)	0.36 (0.79)
15 (size A)	5.09 (11.24)	0.46 (1.01)
25 (size B)	8.44 (18.66)	0.81 (1.8)
37 (size C)	12.51 (27.65)	1.1 (2.47)

Standard plating thickness

• gold flash

• 0.4µm (15µ") gold

• 0.76 µm (30µ") gold

Economical right angle PCB mount connectors

Industrial

Telecom


· Any industry standard I / O connections








Shell Size Dimensions




Recommended P.C.B.Layout




Nb OF			DIMENSIONS mm (inch)			
CONTACTS	Α	В	С	D	E	Х
9	30.84 (1.214)	24.99 (.984)	16.92 (.666)	16.26 (.640)	11.08 (.436)	2.74
15	39.24 (1.545)	33.32 (1.312)	25.25 (.994)	24.56 (.967)	19.39 (.763)	2.74
25	53.04 (2.088)	47.04 (1.852)	38.96 (1.534)	38.30 (1.508)	33.24 (1.309)	2.77
37	69.34 (2.730)	63.50 (2.500)	55.42 (2.182)	54.76 (2.156)	49.86 (1.963)	2.77

Panel mounting option




Front Female Screwlock 4F/3F



Threaded Rear Insert 4R/3R

How to order



For special request, please consult factory

STRAIGHT PCB TERMINATION **ONE METAL SHELL CONNECTORS**

The one shell D-sub Amphenol series features, stamped and formed contacts.

This series gives you Amphenol's high standards of quality and reliability to meet all of your commercial requirements

Specifications

CHARACTERISTICS

• Connectors according to MIL C24308

Mating and unmating force

	Materials and Platings
Shells	Steel, tin over nickel plating
Insulator	Glass-filled thermoplastic, UL 94V-0
Contacts	Copper alloy, with selective gold plating
Boardlock	Brass with nickel plating
Screwlock	Brass with nickel plating
	. •
Corcwicon	Drade war moker planning

	Electrical Data
Current rating	5A
Voltage rating	600V AC/rms 50Hz
Withstanding voltage	1000V AC/rms 50Hz for one minute
Insulation resistance	5000ΜΩ
Contact resistance	10mΩ max

	Climatic Data
Operating temperature	-55°C to +125°C

Cililatic Data
Operating temperature -55°C to +125°C

Mechanical Data

Unit: kg (lb)	- 	I
No. of Cts	Mate (max)	Unmate (min)
9	3.05 (6.74)	0.36 (0.79)
15	5.09 (11.24)	0.46 (1.01)
25	8.44 (18.66)	0.81 (1.8)
37	12.51 (27.65)	1.1 (2.47)

Standard plating thicknesses	 gold flash
	• 0.4µm (15µ") gold
	• 0.76 μm (30μ") gold

Economical straight PCB, one shell connectors

 Industrial Telecom

> · Any industry standard I / O connections

