Design Features

*Top, bottom and side panels .05" aluminum. Frame, 6063-T5 aluminum extrusions.

*Accommodate 19.00" panels.

*Panel Mounting Rails have #10-32 tapped holes on E.I.A. spacing (Use #7346 screws - order separately)

*Panels not included but are available.

*.09" aluminum alloy doors attach to mounting rails and have black thermoplastic flush-type latches.

*Cabinet - 500# equipment load capacity. Carrying Handles limited to 100# capacity.

Bonus Features

*Recessed handles are attached to two steel flanges extending the length of the cabinet. This added support assures carrying safety.
* Two 16-gauge steel vertically adjustable chassis supports included.
*Shipped completely assembled.

Finishes

Gray Texture (GT) Royal Blue Texture (RB) . Available in other Bud Textured Finishes at no extra cost.

Classic II - Cabinets & Doors						
Catalog Number	Drawings	Height	Panel Space	Weight (Lbs.)	Door Catalog Number	Weight (Lbs.)
AGC-9268		8.81"	7.00"	30	AGD-368	2.00
AGC-9269		10.56"	8.75"	32	AGD-369	2.75
AGC-9270		12.31"	10.50"	33	AGD-370	3.00
AGC-9271		14.06"	12.25"	34	AGD-371	3.50
AGC-9272		15.81"	14.00"	35	AGD-372	4.00
AGC-9273		17.56"	15.75"	36	AGD-373	4.75
AGC-9274		19.31"	17.50"	37	AGD-374	5.00
AGC-9275		21.06"	19.25"	39	AGD-375	5.50
AGC-9276		22.81"	21.00"	40	AGD-376	6.25
AGC-9277		24.56"	22.75"	41	AGD-377	6.75
AGC-9278		26.31"	24.50"	42	AGD-378	7.25
AGC-9279		28.06"	26.25"	43	AGD-379	7.50
AGC-9280		29.81"	28.00"	45	AGD-380	8.00

Bud Industries, Inc.

PART NAME	CLASSIC II CABINET	PART No.	AGC-9268 THRU AGC-9280

MATERIAL:
    CABINET FRAME & MOUNTING RAIL EXTRUSIONS___ #6063-T5 ALUMINUM ALLOY
    TOP, BOTTOM & SIDE PANELS_____ 0.050 THK. ALUMINUM
    HANDLE CHANNELS & CHASSIS SUPPORTS_____ 16 GA. STEEL (ZINC COATED)
   HANDLES _____ MOLDED ABS

FINISH:
    CABINET & HANDLE CHANNELS _____ ROYAL BLUE TEXTURE
                                                 OR GRAY TEXTURE
   CHASSIS SUPPORTS _____ SMOOTH BLACK
    HANDLES – BLACK

    LEADING EDGES OF CABINET FRONT TO BE NATURAL

MOUNTING RAILS TAPPED #10-32 ON WESTERN ELECTRIC HOLE SPACING

LOAD RATING: 500 LBS. MAX.

TOP VIEW

FRONT VIEW

20.812
0.875
17.874
18.312
19.062
12.374 REF.
2.750
B
A

RIGHT SIDE VIEW

21.436 REF.
20.812
0.875
0.312

SECTION "A-A"

20.562 C.I.D.
2.750 REF.
18.688 REF.

BOTTOM VIEW

PART No.	A (PANEL SPACE)	B
AGC-9268	7.000	8.812
AGC-9269	8.750	10.562
AGC-9270	10.500	12.312
AGC-9271	12.250	14.062
AGC-9272	14.000	15.812
AGC-9273	15.750	17.562
AGC-9274	17.500	19.312
AGC-9275	19.250	21.062
AGC-9276	21.000	22.812
AGC-9277	22.750	24.562
AGC-9278	24.500	26.312
AGC-9279	26.250	28.062
AGC-9280	28.000	29.812