

EVEREADY BATTERY COMPANY, INC.


www.energizer.com

1-800-383-7323 / CANADA - USA + 44 (0) 208 920 2306 / EUROPE


ENERGIZER NO. NH35




Industry Standard Dimensions



Typical Discharge Characteristics





Specifications

Classification: Rechargeable

Chemical System: Nickel-Metal Hydride (NiMH)

Designation: ANSI-1.2H3 Nominal Voltage: 1.2 Volts

Rated Capacity: 2500 mAh (to 1.0 volts)

Based on 500 mA (0.2C) discharge rate

Typical Weight: 60.0 grams (2.1 oz.)

Typical Volume: 26.9 cubic centimeters (1.6 cubic inch)

Jacket: Plastic Label

Internal Resistance:

The internal resistance of the cell varies with state of charge, as follows:

Cell 1/2 Discharged Cell Charged 11 milliohms 21 milliohms (tolerance of ±20% applies to above values)

AC Impedance (No Load):

The impedance of the charged cell varies with frequency, as follows:

Frequency (Hz) Impedance (milliohms) (Charged Cell) 1000

9

Above values based on AC current set at 1.0 ampere. Value tolerances are ±20%.

Operating and Storage Temperatures:

To maintain maximum performance, observe the following general guidelines regarding environmental conditions.

> Charge: 0°C to 40°C (32°F to 104°F) 0°C to 50°C (32°F to 122°F) Discharge: -20°C to 30°C (-4°F to 86°F) Storage:

Humidity: 65±20%

Operating at extreme temperatures, will significantly impact battery cycle life.

Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication. Contents herein do not constitute a warranty.

© Eveready Battery Company, Inc. - All Rights Reserved

Form No. FBC - 7103G Page 1 of 1