


Cabinets **Econocab**



Design Features

- *All welded 18-gauge steel construction
- *Stationary panel mouting rails resulting in a 14.50 inch clear inside depth. Rails have .28" dia. holes on E.I.A. universal spacing (Use #295 cage nuts and #7346 screws order separately)
- *Accepts standard 19.00" wide panels
- *Available in 5 panel space heights.
- *Snap-in handles and feet are included.
- *Cabinet 500# equipment load capacity Carrying Handles limited to 150#

Finishes

Black Texture (BT) Sand Texture (S) Special colors available upon request.

Catalog Number	Drawings	Panel Space PS	Height A	Width B	Depth C	Weight (Lbs.)
EC-9902		7.00"	9.06"	21.06"	15.50"	14.00
EC-9903		8.75"	10.81"	21.06"	15.50"	14.75
EC-9904		10.50"	12.56"	21.06"	15.50"	15.50
EC-9905		12.25"	14.31"	21.06"	15.50"	16.25
EC-9906		14.00"	16.06"	21.06"	15.50"	17.00



