

DURACELL® Watch Batteries

Duracell Watch Batteries (Silver Oxide)

Duracell	IEC	ANSI	Overall Ht.(MM)	Overall Ht.(in.)	Diameter (MM)	Diameter (in.)
D301/386	SR43	1132SO/1133SO	4.2	0.165	11.6	0.457
D303/357	SR44	1131SO	5.6	0.22	11.6	0.457
D309/393	SR48	1136SO/1137SO	5.4	0.213	7.9	0.311
D361/362	SR58	1158SO	2.1	0.083	7.9	0.311
D364	SR60	1175SO	2.15	0.085	6.8	0.268
D370/371	SR69	-	2.1	0.083	9.5	0.374
D377	SR66	1176SO	2.6	0.102	6.8	0.268
D379	-	1191SO	2.15	0.085	5.8	0.228
D381/391	SR55	1160SO/1170SO	2.1	0.083	11.6	0.457
D384/392	SR41	1134SO/1135SO	3.6	0.142	7.9	0.311
D389/390	SR54	1138SO	3	0.120	11.6	0.457
D395/399	SR57	1162SO/1165SO	2.7	0.106	9.5	0.374
D396/397	SR59	1163SO/1164SO	2.6	0.102	7.9	0.311

Duracell	Endpoint Voltage	Typical Capacity (MAh)
D301/386	1.2V	120
D303/357	1.2V	165
D309/393	1.2V	70
D361/362	1.2V	24
D364	1.2V	18
D370/371	1.2V	33
D377	1.2V	25
D379	1.2V	14
D381/391	1.2V	40
D384/392	1.2V	42
D389/390	1.2V	70
D395/399	1.2V	55
D396/397	1.2V	30

DURACELL®
BATTERIES

* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage.

SILVER

PRIMARY

CELLS & BATTERIES

The high volumetric energy density of DURACELL® silver oxide button cells, and their ability to deliver this energy at relatively high current drains, makes them ideal for miniature devices where space is limited. Silver cells also have an extremely stable discharge voltage, good shelf life, and the ability to operate over a wide temperature range.

DURACELL PRODUCT NUMBER	NOMINAL VOLTAGE (V)	RATED CAPACITY ⁽¹⁾ (mAh)	RATED VOLTAGE CUTOFF (V)	LOAD (OHMS)	APPROX. DRAIN (mA)	DIMENSIONS		AVERAGE WEIGHT		MAXIMUM VOLUME	TERMINALS	CROSS REFERENCE	
						MAXIMUM DIAMETER	MAXIMUM HEIGHT	oz.	g	in ³	cm ³	NEDA/ANSI	IEC
						in.	mm	in.	mm				
SELECTED BUTTON & CYLINDRICAL CELLS													
D301/386	1.55	120	1.2	15,000	0.10	0.455	11.56	0.165	4.19	0.060	1.70	0.026	0.426
D303/357	1.55	165	1.2	1,000	1.50	0.455	11.56	0.220	5.58	0.080	2.30	0.033	0.540
D309/393	1.55	70	1.2	10,000	0.15	0.310	7.87	0.212	5.38	0.036	1.00	0.015	0.245
D361/362	1.55	24	1.2	50,000	0.03	0.308	7.83	0.085	2.15	0.016	0.44	0.006	0.098
D364	1.55	18	1.2	50,000	0.03	0.268	6.80	0.085	2.15	0.012	0.35	0.004	0.066
D370/371	1.55	33	1.2	30,000	0.05	0.372	9.45	0.085	2.15	0.023	0.64	0.009	0.147
D377	1.55	25	1.2	50,000	0.03	0.267	6.78	0.104	2.64	0.014	0.40	0.005	0.082
D379	1.55	14	1.2	68,000	0.02	0.228	5.79	0.085	2.15	0.008	0.23	0.003	0.049
D381/391	1.55	40	1.2	15,000	0.10	0.455	11.56	0.087	2.21	0.030	0.85	0.013	0.213
D384/392	1.55	42	1.2	15,000	0.10	0.310	7.87	0.142	3.60	0.025	0.72	0.010	0.164
D389/390	1.55	70	1.2	13,000	0.11	0.455	11.56	0.120	3.05	0.042	1.20	0.021	0.327
D395/399	1.55	55	1.2	30,000	0.05	0.374	9.50	0.106	2.69	0.029	0.81	0.011	0.180
D396/397	1.55	30	1.2	30,000	0.05	0.311	7.90	0.104	2.64	0.019	0.54	0.007	0.114
MS76	1.55	180	1.2	1,500	1.00	0.455	11.56	0.210	5.33	0.081	2.30	0.033	0.540

(1) Rated at 70°F (21°C). Typical capacities can be higher or lower based on user's particular application.

DURACELL®