

Electrical UL/CSA Electrical IEC Electronics Consumer/Aftermarket OEM Transportation Terminal Blocks Systems/Services/Software

Cooper Bussmann

Homepage About Cooper Bussmann Contact Us Privacy Legal Cooper Bussmann® Brand Site Map

C520-100mA

FAST ACTING, 5 X 15 mm, GLASS

Product Information		
Product Type:	Fuse	
Product Family:	Electronic	
Brand:	Cooper Bussmann	

Recommended Products				
	Rec. Inline Fuse Holder:	HHT		
	Rec. Fuse Clips:	1A3399 Series		

Physical Properties

Dimensions.	0.59in.(L) ×	0.2in.(W)	×	0in.
	(H)			

Electrical Properties		
Maximum AC Voltage:	250	
Amperage Rating:	0.1	
AC Interrupting Ratings:	35 at 250V10000 at 125V	
Melting I ² T:	0.001	
Fast Acting:	Yes	
Resistance:	0.245	
Voltage Drop:	3100	





5mm x 15mm Fuses C520 Series, Fast Acting, Glass Tube

Description

- Fast acting
- 5mm x 15mm physical size
- · Glass tube, nickel-plated brass endcap construction
- Optional sleeve is flexible flouropolymer (U.L. flammability rating VW-1).
- UL Listed product meets standard UL 248-14

ELECTRICAL CHARACTERISTICS			
Rated Current Amp Rating Opening Tim			
	100%	None	
100mA - 5A	135%	1 hours max.	
	200%	2 seconds max.	

Agency Information

- UL Listed Card: Guide JDYX, File E19180
- CSA Certification Card: Class 1422-01, LR65063

Ordering


- Specify packaging, product, and option code
- For -R option, drop mA or A from product code (i.e. C520-3-R)





Dimensions

Drawing Not to Scale



	SPECIFICATIONS					
Product Code	Voltage Rating		ing Rating d Voltage	Typical DC Cold Resistance*	Typical Melting I²t†	Typical Voltage
	AC	250VAC	125VAC	(ohms)	AC	Drop (mV)‡
C520-100mA	250V	35A	10,000A	22.30	0.0010	2230
C520-125mA	250V	35A	10,000A	15.20	0.0019	1930
C520-250mA	250V	35A	10,000A	5.60	0.012	1450
C520-375mA	250V	35A	10,000A	2.53	0.039	968
C520-500mA	250V	35A	10,000A	1.66	0.059	845
C520-750mA	250V	35A	10,000A	0.91	0.264	686
C520-1.5A	250V	100A	10,000A	0.900	0.800	135
C520-2A	250V	100A	10,000A	0.064	1.9	136
C520-2.5A	250V	100A	10,000A	0.046	2.9	121
C520-3A	250V	100A	10,000A	0.038	6.1	116
C520-3.5A	250V	100A	10,000A	0.032	9.7	115
C520-4A	250V	200A	10,000A	0.022	16.6	88
C520-5A	250V	200A	10,000A	0.018	22.4	91

^{*} DC Cold Resistance (Measured at <10% of rated current)


[†] Typical Melting I²t (A²Sec) (maximum I²t at 10 times rated current)

[‡] Typical Voltage Drop (Voltage drop was measured at 25°C±3°C ambient temperature at rated current)



5mm x 15mm Fuses C520 Series, Fast Acting, Glass Tube

TIME CURRENT CURVE Time-Current Characteristic Curves—Average Melt



PACKAGING CODE		
Packaging Code	Description	
BK 100 pieces of fuses packed into a cardboard carton		
BK1	1,000 pieces of fuses packed into a cardboard carton	

OPTION CODE		
Option Code	Description	
S	Insulation Sleeve	
-R	RoHS compliant version	

