

# Bi-Directional Reentrant Horn Loudspeaker

## Model BDT30A

### Description

The BDT30A is a compact loudspeaker designed for one- or two-way sound and communication systems. Ideal for use in industrial plants, warehouses, schools, construction sites, transportation terminals, and recreational areas.

Speaker assembly required.



### Features

- Twin reentrant horns for bi-directional projection
- High intelligibility and efficiency
- Ideal for both one-way and talkback paging applications
- Weatherproof
- Sturdy, all-metal construction
- 30 watts; 25 or 70V operation
- Variable tap impedance selector switch
- Screw terminals make installation fast and easy
- For indoor and outdoor use
- Uniquely designed all-purpose mounting bracket for simple installation

**BOGEN®**

54-7761-02r2 Printed in USA 0004  
© 2000 Bogen Communications Inc. All rights reserved.  
Specifications subject to change without notice.

## General Specifications

<b>Power Rating (RMS):</b>	30 watts continuous; 40 watts equalized					
<b>Frequency Response:</b>	225Hz to 14kHz					
<b>Impedance:</b>	25/70 volts					
<b>Sound Pressure Level:</b>	121dB @ four feet on axis with 30 watt input @ 1000Hz, each horn					
<b>Dispersion:</b>	100° each horn					
<b>Sensitivity as Microphone:</b>	-22dBm [Ref: 10 dynes/cm2]					
<b>Dimensions:</b>	16-1/2" W x 9-3/4" H (41.9 x 24.8 cm)					
<b>Shipping Weight:</b>	8 lbs. (3.6kg)					
<b>Finish:</b>	Textured mocha enamel					
<b>Impedance Selector Switch Settings:</b>	25V @ 15, 7.5, 3.7, 1.8 watts 70V @ 30, 15, 7.5, 3.7, 1.8 watts					
<b>Sound Pressure Level in dB @ 1000Hz:</b>	<b>Watts</b>	<b>Feet on Axis</b>				
	<b>Input:</b>	<b>4</b>	<b>8</b>	<b>16</b>	<b>32</b>	<b>64</b>
	30 —	121	115	109	103	97
	15 —	118	112	106	100	94
	7.5 —	115	109	103	97	91
	3.7 —	112	106	100	94	88
	1.8 —	109	103	97	91	85

## Architects and Engineers Specifications

The loudspeaker shall be a Bogen Model BDT30A, or approved equivalent, reentrant horn type loudspeaker. The frequency response shall be from 225Hz to 14kHz. Rated power output shall be 30 watts RMS continuous. Dispersion shall be 100°, each horn. Sound pressure level, measured four feet on axis with 30 watt input @ 1000Hz, shall be at least 121dB for each horn.

The unit shall incorporate a seven-position weather-sealed switch, to allow matching the loudspeaker to a 25V or 70V constant-voltage line. Power handling capacity shall be adjustable at 70V to 30, 15, 7.5, 3.7 or 1.8 watts, and at 25V to 15, 7.5, 3.7 or 1.8 watts. Impedance shall be adjustable to 2,500, 1,300, 666, 333, 167, 89, or 45 ohms.

The loudspeaker shall be of weatherproof all metal construction, with driver enclosed within a waterproof housing. The loudspeaker shall include a self-aligning, field replaceable diaphragm.

Screw terminals shall be provided for connection to the audio line. A plastic cover shall be provided to protect the connectors and impedance selector switch, and to provide strain relief for the audio line.

An all-purpose mounting bracket shall provide precise positioning in the vertical and horizontal planes with a single adjustment. The bracket shall include banding slots to permit mounting the loudspeaker on beams or pillars. Bracket and loudspeaker shall be finished in textured mocha enamel. The unit shall measure 16-1/2" W x 9-3/4" H. Shipping weight shall be 8 lbs.

**BOGEN<sup>®</sup>**  
**COMMUNICATIONS, INC.**

50 Spring Street, Ramsey, NJ 07446  
201-934-8500; Fax: 201-934-9832; Web Site: [www.bogen.com](http://www.bogen.com)