

lectrical UL/CSA	Electrical IEC	Electronics	Consumer/Aftermarke	et OEM Transportatio	on Terminal Blocks	Systems/Services/Software
Cooper Bussma Homepage About Cooper Bussma Contact Us Privacy Legal Cooper Bussmann® Bi Site Map	nn 📗		2-2-1/2 pelay Supplementary I	Fuse, 500V, 2-1/2A, 13/3	2 - 1-1/2 Inches	
	Pro	duct Informa	tion			
	Proc	duct Type:	Fuse			
	Proc	duct Family:	Electrical Power			
	Brar	nd:	Cooper Bussmann			
					Certifications	
	Rec	ommended P	Products		UL Listed	
	Rec.	. Fuse Block:	BM603 Series		CSA Certified	
	Rec. Hold	. Inline Fuse der:	HEB Series			
	Rec.	. Panel-mount	HPS Series	Electrical	Properties	

Maximum AC

Amperage Rating:

AC Interrupting

Voltage:

Ratings:

Time Delay:

500

2.5

Yes

• 10000 at 500V

Physical Properties							
Dimensions:	1.5in.(L) \times 0.41in.(W) \times 0in. (H)						

HPS Series

CHM Series

5960 Series

SAMI-7 Series

Fuse Holder:

Holder:

Rec. Modular Fuse

Rec. Fuse Clips:


Rec. Cover:

Bussmann®

FNQ

Tron[®] Time-Delay Fuses 13/32" x 1-1/2" Midget 500 Volt, 1/10-30 Amps





Catalog Symbol: FNQ (5AG) TIME-DELAY 1/10 TO 30A 500Vac (OR LESS) Interrupting Rating:10,000A UL LISTED, STD 248-14, (GUIDE # JDYX, FILE # E19180) CSA CERTIFIED (CLASS 1422-01; FILE 53787)

Catalog Symbol and Ampere Ratings


		-	
FNQ-1/10	FNQ-8/10	FNQ-3-2/10	FNQ-9
FNQ-1/8	FNQ-1	FNQ-3-1/2	FNQ-10
FNQ-15/100	FNQ-1-1/8	FNQ-4	FNQ-12
FNQ-3/16	FNQ-1-1/4	FNQ-4-1/2	FNQ-14
FNQ-2/10	FNQ-1-1/2	FNQ-5	FNQ-15
FNQ-1/4	FNQ-1-6/10	FNQ-5-6/10	FNQ-20
FNQ-3/10	FNQ-2	FNQ-6	FNQ-25
FNQ-4/10	FNQ-2-1/4	FNQ-6-1/4	FNQ-30
FNQ-1/2	FNQ-2-1/2	FNQ-7	_
FNQ-6/10	FNQ-3	FNQ-8	_

Carton Quantity and Weight							
Ampere	Carton	Weight*					
Ratings	Qty	Lbs.	Kg.				
1-30	10	.180	.082				


* Weight per carton.

- Fibre tube.
- Nickel plated brass endcaps.
- For motor control transformers and other circuits with in-rush currents.

Time-Current Characteristic Curve-Average Melt



RMS SYMMETRICAL IN AMPERES



C€

