
DURACELL[®] COPPERTOP[™]

Alkaline-Manganese Dioxide Battery

MN1604 Size: 9V (6LR61)



Nominal Voltage:	9 V
Nominal Internal Impedance:	1,700 m-ohm @ 1kHz
Average Weight:	45 gm (1.6 oz.)
Volume:	22.8 cm ³ (1.39 in. ³)
Terminals:	Miniature Snap
Operating Temperature Range:	-20°C to 54°C (-4°F to 130°F)
NEDA/ANSI: IEC:	1604A 6LR61

TYPICAL DISCHARGE CHARACTERISTICS AT 21 °C (70°F)




* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.

DURACELL[®] COPPERTOP[™] MN1604 Size: 9V (6LR61) **Alkaline-Manganese Dioxide Battery**

TYPICAL CONSTANT CURRENT DISCHARGE CHARACTERISTICS AT 21°C (70°F) 1000 100 10

Service Hours





BATTERIES

Berkshire Corporate Park Bethel, CT 06801 U.S.A. Telephone: Toll-free 1-800-544-5454 Internet: www.duracell.com

> Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.

TYPICAL DISCHARGE CHARACTERISTICS AT 21°C (70°F)





Zn/MnO₂