

Cooper Bussmann

[Homepage](#)
[About Cooper Bussmann](#)
[Contact Us](#)
[Privacy](#)
[Legal](#)
[Cooper Bussmann® Brand](#)
[Site Map](#)



SC-15

Class G, Time-Delay Fuse, 15A, 600V

Product Information

Product Type:	Fuse
Product Family:	Electrical Power
Brand:	Cooper Bussmann
Class:	G

Recommended Products

Rec. Fuse Block:	BG301 Series
Rec. Inline Fuse Holder:	HEG-AA
Rec. Panel-mount Fuse Holder:	HPS-EE

Physical Properties

Dimensions:	1.31in.(L) × 0.41in.(W) × 0in.(H)
-------------	-----------------------------------

Certifications

[UL Listed](#)

[CSA Certified](#)

Electrical Properties

Maximum AC Voltage:	600
Maximum DC Voltage:	170
Amperage Rating:	15
AC Interrupting Ratings:	<ul style="list-style-type: none">100000 at 600V
DC Interrupting Ratings:	<ul style="list-style-type: none">10000 at 170V
Fuse Class:	Class G
Time Delay:	Yes

Time-Delay Fuses

Class G – 600 Volt, ½ - 20 Amps
480 Volt, 25 - 60 Amps



Catalog Symbol: SC

Current-Limiting

Ampere Rating: ½ to 60A (fast-acting),
 7 to 60A (time-delay)

Voltage Ratings:

SC ½ to 20 600Vac, 170Vdc

SC 25 to 60 480Vac, 300Vdc

Interrupting Rating: 100,000A RMS Sym. AC, 10,000A dc

Agency Information:

UL Listed, Std. 248-5, Class G, Guide JDDZ, File E4273

CSA Certified, C22.2 No. 248.5, Class 1422-01, File 53787

Catalog Numbers


SC-½	SC-6	SC-25
SC-1	SC-7	SC-30
SC-1½	SC-8	SC-35
SC-2	SC-9	SC-40
SC-2½	SC-10	SC-45
SC-3	SC-12	SC-50
SC-4	SC-15	SC-60
SC-5	SC-20	—

Carton Quantity and Weight

Catalog Number	Carton Qty.	Weight†	
		Lbs.	Kg.
½-15	4	0.060	0.0272
20	4	0.064	0.029
25-30	2	0.040	0.018
35-60	2	0.075	0.0340

†Weight per carton.

Dimensional Data



Fuse (Amps)	A
SC-½ to 15	1.31"
SC-20	1.41"
SC-25 to 30	1.62"
SC-35 to 60	2.25"

General Information:

- Compact branch-circuit units with high interrupting rating and current-limitation.
- With 600V rating, they can be used in 120/208, 120/240 and 277/480V circuits.
- Length variations relative to case size make the "rejection" type fuses.
- In general, SC fuses are about ⅓ the size of the 600V NEC fuse type.
- SC fuses with ampere ratings above 6A have a degree of overload time-delay which permits them to pass temporary overloads. At 200% load, they have a minimum opening time of 12 seconds.



Recommended fuseblocks/fuseholders for Class G fuses

See Data Sheets listed below

- Open fuseblocks - 1106
- In-line fuseholders - 1123, 1124

CE