

GSC25 Commercial/GSM25 Medical

25 WATT GLOBAL PERFORMANCE SWITCHERS

GLOBAL PERFORMANCE SWITCHERS

Features:

- Industry's smallest 25 W switcher
- 2.50 x 4.25 x 0.86"
- Conducted EMI exceeds FCC Class B and CISPR 22 Class B (Commercial models) and CISPR 11 Class B (Medical models)
- Overvoltage protection standard
- Commercial Approved to UL1950, CSA-C22.2 No.950, EN60950
- Medical Approved to UL2601-1, IEC60601-1 EN60601-1 and CSA-C22.2 No. 601-1
- RoHS Compliant (G suffix)
- CE marked to LVD

SPECIFICATIONS

Ac Input

90-264 Vac, 47-63 Hz single phase.

Input Current

Maximum input current at minimum 120 Vac, 60 Hz with full rated output load is 0.6 A.

Hold-up Time

15 ms minimum from loss of ac input at full load, nominal line (120 Vac).

Output Power

Normal continuous output power is 25 W, 28 W peak for 60 sec. maximum duration, 10% duty cycle. Factory set to begin power limiting at approximately 30 W.

Output Regulation

Regulation from initial setpoint measured by changing load from 5% load to 50% load or 50% load to full load in either direction. Initial setpoint tolerance is measured at 50% load. A minimum load of 5% of the output current on the +5.1 V output (125 mA) is required to maintain proper regulation.

Overload Protection

Fully protected against short circuit and output overload. Short circuit protection is cycling type power limit

Output Noise

0.5% rms, 1% pk-pk, 20 MHz bandwidth, differential mode. Measured with scope probe directly across output terminals of the power supply with load terminated with 0.1 uF capacitor.

Transient Response

Main output: 750 μ s typical response time for return to within 0.5% of final value for a 50% load step within the regulation limits of minimum and maximum load, $\Delta l/\Delta t < 0.2 A/\mu$ s. Maximum voltage deviation is 3.5%. Startup/shutdown overshoot less than 2%.

Overvoltage Protection

Built in with firing point set per ratings table. OVP firing reduces voltage to less than 50% of nominal voltage in 50 ms.

Voltage Adjustment


Factory set with fixed resistors to maximize reliability.

Efficiency

70% minimum at full rated load, nominal input voltage.

Input Protection

Internal ac fuse provided on all units.





ONDO

Inrush Current

Inrush is limited by internal thermistor. The inrush at 230 Vac, averaged over the first ac half-cycle under cold start conditions will not exceed 32 A.

Temperature Coefficient

0.03%/°C typical on all outputs.

Environmental

Designed for 0 to 50°C operation at full rated output power; derate output current and total output power by 2.5% per °C between 50 - 70°C. See Environmental and Packaging Specifications on next page.

EMI/EMC Compliance

All models include built-in EMI filtering to meet the following emissions requirements:

	EMI SPECIFICATIONS	COMPLIANCE LEVEL				
-	Conducted Emissions GSC25 Conducted Emissions GSM25 Static Discharge RF Field Susceptibility Fast Transients/Bursts Surge Susceptibility	EN55022 Class B; FCC Class B EN55011 Class B; FCC Class B EN61000-4-2, 6 kV contact, 8 kV air EN61000-4-3, 3 V/meter EN61000-4-4, 2 kV, 5 kHz EN61000-4-5, 1 kV diff., 2 kV com.				

Commercial Safety:

Condor D.C. Power Supplies, Inc. declares under our sole responsibility that all GSC models are in conformity with the applicable requirements of EN60950 following the provisions of the Low Voltage Directive 73/23/EEC. All GSC models are approved to UL1950, CSA-C22.2 No.950, EN60950.

GSM25 Medical Model Earth Leakage Current

Leakage current measured in the Gnd wire connection when measured per UL2601-1 or IEC60601-1 is as follows:

Model	Normal Leakage	Fault Leakage	Test Voltage	Test Method
GSM25	50 µA	78 µA	132 Vca/60 Hz	UL2601-1
GSM25	94 µA	150 μA	264 Vca/50 Hz	IEC60601-1

Medical Safety

Condor D.C. Power Supplies, Inc. declares under our sole responsibility that all GSM models are in conformity with the applicable requirements of UL2601-1 Patient Care Equipment, CSA-C22.2 No.601.1, IEC60601-1, EN 60601-1.


Commercial Model	Medical Model	Output No.	Output	Current	Load Regulation	Initial Setpoint Tolerance	OVP Setting	Ripple and Noise	Notes
GSC25A	GSM25A	1	+ 5.1 V	2.5 A	1%	1%	$6.2 \pm 0.6 V$	1%	А
		2	+12 V	1.5 A	4%	3%		1%	А
		3	- 12 V	0.2 A	1%	4%		1%	В
GSC25B	GSM25B	1	+ 5 V	2.5 A	1%	1%	$6.2\pm0.6V$	1%	А
		2	+15 V	1.5 A	4%	3%		1%	А
		3	- 15 V	0.2 A	1%	4%		1%	В
GSC25D	GSM25D	1	+5.1 V	2.5 A	1%	1%	$6.2\pm0.6V$	1%	А
		2	+24 V	1.0 A	4%	3%		1%	А
		3	-12 V	0.2 A	1%	4%		1%	В

A. To maintain proper regulation on output 2, +5.1 V current must be at least 1/4 and not greater than 5 times V2 current. V1 must be adjusted within 1% of 5.1 V to maintain full load regulation on V2.

B. Thermal foldback type current limit

C. Add "G" suffix to model number for RoHS compliant model.

GSC25/GSM25 MECHANICAL SPECIFICATIONS



I OLLI U UIOLO.	
X.XX =± 0.030 (0.76MM)	
X.XXX =± 0.010 (0.25MM)	

ENVIRONMENTAL SPECIFICATIONS	OPERATING	NON-OPERATING
Temperature (A)	See individual specs.	-40 to +85°C
Humidity (A)	0 to 95% RH	0 to 95% RH
Shock (B)	20 g _{pk}	40 g _{pk}
Altitude	-500 to 10,000 ft	-500 to 40,000 ft
Vibration (C)	1.5 g _{rms'} 0.003 g²/Hz	5 g _{rms'} 0.026 g²/Hz

A. Units should be allowed to warm up/operate under

non-condensing conditions before application of power.

B. Shock testing—half-sinusoidal, 10 ± 3 ms duration, \pm direction, 3 orthogonal axes, total 6 shocks.

C. Random vibration—10 to 2000Hz, 6dB/octave roll-off from 350 to 2000Hz, 3 orthogonal axes. Tested for 10 min./axis operating and 1 hr./axis non-operating.