
Bussmann®

FNQ-R

CC-TRON[®] Time-Delay Fuses $1_{3_{2}}^{1_{32}}$ " × $1_{2}^{1_{2}}$ ", 600 Volt, $\frac{1}{4}$ to 30 Amps



Dimensional Data



Catalog Symbol: FNQ-R Time-Delay Application: Circuit Transformer Protection Ampere Rating: ½ to 30A Voltage Rating: 600Vac (or less)† Interrupting Rating: 200,000A RMS Sym. (UL) Agency Information: UL Listed, Std. 248-4, Class CC, Guide JDDZ, File E4273 CSA Certified, Class CC CSA, Class 1422-01, File 53787–HRC-MISC

†12-30A is 300Vdc and 10k AIR.

Electrical Ratings (Catalog Symbol and Amperes)

		,	
FNQ-R-1/4	FNQ-R-13/10	FNQ-R-3%	FNQ-R-8
FNQ-R-3/10	FNQ-R-1%	FNQ-R-31/2	FNQ-R-9
FNQ-R-4/10	FNQ-R-11/2	FNQ-R-4	FNQ-R-10
FNQ-R-1/2	FNQ-R-1%	FNQ-R-41/2	FNQ-R-12
FNQ-R-%10	FNQ-R-1%10	FNQ-R-5	FNQ-R-15
FNQ-R-¾	FNQ-R-2	FNQ-R-5%10	FNQ-R-171/2
FNQ-R-%10	FNQ-R-21/4	FNQ-R-6	FNQ-R-20
FNQ-R-1	FNQ-R-21/2	FNQ-R-61/4	FNQ-R-25
FNQ-R-11%	FNQ-R-2%10	FNQ-R-7	FNQ-R-30
FNQ-R-11/2	FNQ-R-3	FNQ-R-71/2	_

Carton Quantity and Weight

Ampere Ratings	Carton Qty.	Weight*	
		Lbs.	Kg.
1⁄4-30	10	.200	.091

*Weight per carton

General Information:

- The Bussmann CC-TRON[®] (FNQ-R) was designed to meet the needs of control circuit transformer protection.
- Current-limitation protects down stream components against damaging thermal and magnetic effects of shortcircuit currents.
- High inrush time-delay. Control circuit transformers can experience inrush currents up to 85 times their full-load current rating. FNQ-R fuses can be sized according to NEC and UL requirements and still allow the high inrush currents, with significantly more time-delay than the UL minimum value of 12 seconds at 200% for Class CC fuses.
- Melamine tube. Nickel-plated brass endcaps.

Maximum Acceptable Rating of Overcurrent Device*

Rated Primary Current (Amperes)	Maximum Rating of Overcurrent Protective Device Expressed As A Percent of Transformer Primary Current Rating	
Less than 2A	500**	
2A to less than 9A	167	
9A or more	125	

*UL 508A Table 42.1.

**300% for other than motor control applications.

C€

COOPER Bussmann 11-20-02 SB02450

Form No. FNQ-R Page 1 of 2 Data Sheet: 1014