Honeywell



Representative photograph, actual product appearance may vary.

Due to regional agency approval requirements, some products may not be available in your area. Please contact your regional Honeywell office regarding your product of choice.

RV6NAYSD103A

RV6 Series Industrial Potentiometer, Conductive Plastic Element, Solder hook Terminals, 0.5 W Power Rating, 10 kOhm Resistance Value

Features

- Compact 12,7 mm [0.5 in] diameter
- Conductive plastic element
- Linear taper
- Robust nickel-plated brass shaft and bushings
- Meets MIL-PRF-94 standards
- Solder hook terminals

Typical Applications

- Manual controls
- Medical equipment
- Telecommunications

Description

The RV6 Series is a military qualified potentiometer made in accordance to MIL-PRF-94 specifications. It offers a 1/2 watt power rating and a conductive plastic element.

Honeywell

RV6NAYSD103A


RV6 Series Industrial Potentiometer, Conductive Plastic Element, Solder hook Terminals, 0.5 W Power Rating, 10 kOhm Resistance Value


| Product Specifications | |
|------------------------|---|
| Potentiometer Type | Industrial |
| Element Type | Conductive Plastic |
| Terminal Type | Solder Hook |
| Power Rating | 0.5 W |
| Resistance Value | 10 kOhm |
| Resistance Tolerance | ± 10 % |
| Linearity | ± 5 % |
| Bushing Thread | 6,35 mm [0.25 in] x 32 NEF-2A |
| Bushing length | 6,35 mm [0.25 in] |
| Bushing Type | Standard |
| Shaft Diameter | 3,18 mm [0.125 in] |
| Shaft length | 22,22 mm [0.875 in] |
| Shaft Ending | Slotted |
| Body | 12.7 mm [0.5 in] diameter, ± 0.79 mm [0.031 in] |
| Electrical Taper | Linear |
| Operating Temperature | -40 °C to 120 °C [-40 °F to 248 °F] |
| Working Voltage (Max.) | 350 V |
| Rotational Life | 50000 cycles |
| Mechanical Rotation | 295° |
| Availability | Global |
| Series Name | RV6 Series |
| UNSPSC Code | 4111363300 |
| UNSPSC Commodity | 4111363300 Potentiometers |

Honeywell


RV6NAYSD103A

RV6 Series Industrial Potentiometer, Conductive Plastic Element, Solder hook Terminals, 0.5 W Power Rating, 10 kOhm Resistance Value





SPLIT LOCKING BUSHING



Honeywell

RV6NAYSD103A

RV6 Series Industrial Potentiometer, Conductive Plastic Element, Solder hook Terminals, 0.5 W Power Rating, 10 kOhm Resistance Value

A WARNING PERSONAL INJURY

DO NOT USE these products as safety or emergency stop devices, or in any other application where failure of the product could result in personal injury.

Failure to comply with these instructions could result in death or serious injury.

A WARNING MISUSE OF DOCUMENTATION

- The information presented in this product sheet (or catalog) is for reference only. DO NOT USE this document as product installation information.
- Complete installation, operation and maintenance information is provided in the instructions supplied with each product.

Failure to comply with these instructions could result in death or serious injury.

© Copyright Honeywell Inc. 1998-2004 All rights reserved.