



## Specification of CR14250SE

High Capacity Cylindrical Laser Sealed  
Primary Lithium Battery


Nominal Capacity <sup>*1</sup>	850 mAh
Nominal Voltage	3 V
Standard Discharge Current	0,5 mA
Max. Discharge Current	Continuous <sup>*2</sup> 7 mA
	Pulse <sup>*3</sup> 70 mA
Temperature Range	-40°C - +85°C
Weight	9 g
Dimensions	Height (H) 25,0 mm
	Diameter (D) 14,5 mm

<sup>\*1</sup> Nominal capacity is determined to an end voltage of 2,0V when the battery is allowed to discharge at a standard current level at 23°C.

<sup>\*2</sup> Current value is determined so that 50% of the nominal capacity is obtained with an end voltage of 2,0V at 23°C.

<sup>\*3</sup> Current value for obtaining 2,0V cell voltage when 15 sec. pulse applied at 50% discharge depth (23°C)

Dimensions



Size with shrinktube

D = 14,5,  
H = 25,0,

(unit: mm)