





Panasonic ideas for life

10 A MINIATURE POWER RELAY

DK RELAYS





FEATURES

- Large capacity in small size: 10 A 250 V AC (1a)
- High sensitivity: 200 mW nominal operating power
- High breakdown voltage 4,000 Vrms between contacts and coil 1,000 Vrms between open contacts Meeting FCC Part 68
- Sealed construction
- · Latching types available

SPECIFICATIONS

Contact

o o i i i u o i					
Arrangemen	t	1 Form A	2 Form A, 1 Form A 1 Form B		
	t resistance, max. drop 6 V DC 1A)	30 mΩ			
Contact mat	erial	Gold flash ov	er silver alloy		
	Nominal switching capacity	10 A 250 V AC 10 A 30 V DC	8 A 250 V AC 8 A 30 V DC		
	Max. switching power	300 W, 2,500 VA	240 W, 2,000 VA		
Rating (resistive)	Max. switching voltage	250 V AC, 30 V DC	250 V AC, 30 V DC		
	Max. switching current	10 A	8 A		
	Min. switching capacity#1	10 mA, 5 V DC			
Expected life (min. operations)	Mechanical	5×	10 ⁷		
	Electrical (resistive)	10 ⁵ (10 A 250 V AC, 10 A 30 V DC)	10 ⁵ (8 A 250 V AC, 8 A 30 V DC)		

Coil

Nominal operating power	200 mW			
#1 This value can change due to the sw	itching frequency, environmental conditions			

and desired reliability level, therefore it is recommended to check this with the actual load.

Remarks

- Specifications will vary with foreign standards certification ratings.
- Measurement at same location as "Initial breakdown voltage" section
- *2 Detection current: 10 mA
- *3 Wave is standard shock voltage of $\pm 1.2 \times 50 \mu s$ according to JEC-212-1981
- *4 Excluding contact bounce time
- $^{\star 5}$ Half-wave pulse of sine wave: 11ms; detection time: 10 μs
- *6 Half-wave pulse of sine wave: 6ms
- *7 Detection time: 10μs
- *8 Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT

Characteristics


Max. operating speed			20 cpm (at rated load)			
Initial insulation resistance*1			Min. 1,000 mΩ (at 500 V DC)			
Initial breakdown	Between open contacts		1,000 Vrms			
voltage*2	Between and coil	n contacts	4,000 Vrms			
Surge voltag contact*3	e betwee	en coil and	Min. 10,000 V			
Operate time (at nominal v			Max. 10 ms (Approx. 5 ms)			
Release time (at nominal v		t diode)*4	Max. 8 ms (Approx. 3 ms)			
Temperature rise (at nominal voltage)			Max. 40°C with nominal coil voltage and at 10 A switching current			
Shock	Function	nal*5	Min. 98 m/s² {10 G}			
resistance	Destruc	tive*6	Min. 980 m/s ² {100 G}			
Vibration	Function	nal*7	88.2 m/s ² {9 G}, 10 to 55 Hz at double amplitude of 1.5 mm			
resistance	Destructive		176.4 m/s ² {18 G}, 10 to 55 Hz at double amplitude of 3.0 mm			
operation, tra	Conditions for operation, transport		−40°C to +65°C −40°F to +149°F			
and storage* (Not freezing condensing a temperature)	and at low Humidity		5 to 85% R.H.			
Unit 1	Form A		Approx. 5.6 g .20 oz			
weight 1	Form A	1 Form B,	Approx. 6 g .21 oz			

12V

TYPICAL APPLICATIONS

- · Switching power supply
- Power switching for various OA equipment
- · Control or driving relays for industrial machines (robotics, numerical control machines, etc.)
- Output relays for programmable logic controllers, temperature controllers, timers and so on.
- · Home appliances

ORDERING INFORMATION Ex. DK



12

Notes: 1. Standard packing Carton: 50 pcs.; Case: 500 pcs. UL/CSA, TÜV approved type is standard.

2. 1 coil latching type available.

TYPES AND COIL DATA (at 20°C 68°F)

Single side stable

	Part No.	Nominal voltage, V DC	Pick-up voltage, V DC (max.)	Drop-out voltage, V DC (min.)	Nominal operating current, mA (±10%)	Coil resistance, Ω (±10%)	Nominal operating power, mW	Maximum allowable voltage, V DC (at 65°C 149°F)
	DK1a-3V (-F)	3	2.1	0.3	66.6	45	200	3.9
	DK1a-5V (-F)	5	3.5	0.5	40	125	200	6.5
1 Form A	DK1a-6V (-F)	6	4.2	0.6	33.3	180	200	7.8
I FOIIII A	DK1a-9V (-F)	9	6.3	0.9	22.2	405	200	11.7
	DK1a-12V (-F)	12	8.4	1.2	16.6	720	200	15.6
	DK1a-24V (-F)	24	16.8	2.4	8.3	2,880	200	31.2
	DK1a1b-3V	3	2.1	0.3	66.6	45	200	3.9
	DK1a1b-5V	5	3.5	0.5	40	125	200	6.5
1 Form A	DK1a1b-6V	6	4.2	0.6	33.3	180	200	7.8
1 Form B	DK1a1b-9V	9	6.3	0.9	22.2	405	200	11.7
	DK1a1b-12V	12	8.4	1.2	16.6	720	200	15.6
	DK1a1b-24V	24	16.8	2.4	8.3	2,880	200	31.2
	DK2a-3V	3	2.1	0.3	66.6	45	200	3.9
	DK2a-5V	5	3.5	0.5	40	125	200	6.5
2 Form A +	DK2a-6V	6	4.2	0.6	33.3	180	200	7.8
	DK2a-9V	9	6.3	0.9	22.2	405	200	11.7
	DK2a-12V	12	8.4	1.2	16.6	720	200	15.6
	DK2a-24V	24	16.8	2.4	8.3	2,880	200	31.2

2 coil latching


	Part No.	Nominal voltage, V DC	Set voltage, V DC (max.)	Reset voltage, V DC (max.)	Nominal operating current, mA (±10%)		Coil resistance, Ω (±10%)		Nominal operating power, mW		Maximum allowable voltage, V DC (at 65°C
					Set	Reset	Set	Reset	Set	Reset	149°F)
	DK1a-L2-3V (-F)	3	2.1	2.1	66.6	66.6	45	45	200	200	3.9
	DK1a-L2-5V (-F)	5	3.5	3.5	40	40	125	125	200	200	6.5
1 Form A	DK1a-L2-6V (-F)	6	4.2	4.2	33.3	33.3	180	180	200	200	7.8
I FOIIII A	DK1a-L2-9V (-F)	9	6.3	6.3	22.2	22.2	405	405	200	200	11.7
	DK1a-L2-12V (-F)	12	8.4	8.4	16.6	16.6	720	720	200	200	15.6
	DK1a-L2-24V (-F)	24	16.8	16.8	8.3	8.3	2,880	2,880	200	200	31.2
1 Form A 1 Form B	DK1a1b-L2-3V	3	2.1	2.1	66.6	66.6	45	45	200	200	3.9
	DK1a1b-L2-5V	5	3.5	3.5	40	40	125	125	200	200	6.5
	DK1a1b-L2-6V	6	4.2	4.2	33.3	33.3	180	180	200	200	7.8
	DK1a1b-L2-9V	9	6.3	6.3	22.2	22.2	405	405	200	200	11.7
	DK1a1b-L2-12V	12	8.4	8.4	16.6	16.6	720	720	200	200	15.6
	DK1a1b-L2-24V	24	16.8	16.8	8.3	8.3	2,880	2,880	200	200	31.2
	DK2a-L2-3V	3	2.1	2.1	66.6	66.6	45	45	200	200	3.9
2 Form A	DK2a-L2-5V	5	3.5	3.5	40	40	125	125	200	200	6.5
	DK2a-L2-6V	6	4.2	4.2	33.3	33.3	180	180	200	200	7.8
	DK2a-L2-9V	9	6.3	6.3	22.2	22.2	405	405	200	200	11.7
	DK2a-L2-12V	12	8.4	8.4	16.6	16.6	720	720	200	200	15.6
	DK2a-L2-24V	24	16.8	16.8	8.3	8.3	2,880	2,880	200	200	31.2

4. Coil temperature rise Sample: DK1a1b-12V, 5 pcs

Ambient temperature: 20°C 68°F

ပွ 50 Coil temperature rise, 40 30 20 100 110 120 130 Coil applied voltage,%V


5. Ambient temperature characteristics




DIMENSIONS

1.1 Form A type








General tolerance: $\pm 0.3 \pm .012$


PC board pattern (Copper-side view)



Schematic (Bottom view) Single side stable (Deenergized condition)

mm inch





The above shows 2 coil latching type. No.5 terminal is eliminated on single side stable type.

Tolerance: ±0.1 ±.004


2 coil latching (Reset condition)





Since this is a polarized relay, the connection to the coil should be done according to the above schematic.


2. 1 Form A 1 Form B type, 2 Form A type














Schematic (Bottom view) <1 Form A 1 Form B type>












<2 Form A>



Since this is a polarized relay, the connection to the coil should be done according to the above schematic.

Note:

Relay out-line and PC board pattern are common for both 1 Form A 1 Form B type and 2 Form A type.

General tolerance: ±0.3 ±.012

Tolerance: ±0.1 ±.004

DK relay socket

TYPES AND RELAY COMPATIBILITY



	Socket	1 Fo	rm A	1 Form A 1 Form B, 2 Form A		
Relay		Single side stable type	2 coil latching type	Single side stable type	2 coil latching type	
1 Faure A	Single side stable type	DK1a-PS	DK1a-PSL2	_	_	
1 Form A	2 coil latching type	_	DK1a-PSL2	_	_	
1 Form A 1 Form B	Single side stable type	_	_	DK2a-PS	DK2a-PSL2	
2 Form A	2 coil latching type	_	_	_	DK2a-PSL2	


SPECIFICATIONS


Breakdown voltage*1 4,000 Vrms (Except the portion between coil terminals)	
Insulation resistance	Min. 1,000 mΩ (at 500 V DC)
Heat resistance	150°C (for 1 hour)
Max. continuous current	10 A (DK1a-PS, DK1a-PSL2), 8 A (DK2a-PS, DK2a-PSL2)


Remarks

DIMENSIONS

mm inch








The above shows 2 coil latching type. No.2 and 5 terminal are eliminated on single side stable type. Tolerance: $\pm 0.1\,\pm.004$


General tolerance: ±0.3 ±.012

FIXING AND REMOVAL METHOD


1. Match the direction of relay and socket.




2. Both ends of the relay are to be secured firmly so that the socket hooks on the top surface of the relay.



3. Remove the relay, applying force in the direction shown below.




4. In case there is not enough space to grasp relay with fingers, use screwdrivers in the way shown below.



NOTES

1. Phase synchronization of AC-load switching

In case of switching the contact synchronized with phase of load voltage, the life of contact might be shorter or contact failure might be caused. Please confirm this matter in the actual system in this case. If necessary, the phase control would be recommended.



2. Soldering should be done under the following conditions:

250°C 482°F within 10s 300°C 572°F within 5s 350°C 662°F within 3s

For Cautions for Use, see Relay Technical Information

^{*1} Detection current: 10 mA