




MODEL# : LITH-9V / ULLTH9V

LITHIUM THIONYL CHLORIDE BATTERY


Characteristics

Nominal capacity(0.5mA-2.0v).....	1200mAh
Nominal voltage.....	10.8v
Max.constant current.....	.25mA
Max.pulse current.....	.50mA
Weight.....	40g
Volume.....	.26X17X48.8mm
Workable temperature.....	-55C ~ +85C




NOT FOR USE IN MEDICAL OR HIGH DRAIN DEVICES


Discharge characteristic



Voltage vs temperature



Capacity vs current



Storage characteristics

