CHEMICALS

NEW PRODUCTS

Big Bath³ Contact Cleaner Rolls



Big Bath³ Contact Cleaner is the replacement choice for HCFC 141b cleaners (contains no HCFC's or CFC's). It is non-flammable, non-ozone depleting, and is safe on some plastic. This non-residue cleaner is effective on switches, PC boards, motors, electrical and electronic components. Big Bath³ helps dissipate moisture, and is fast drying.

Applications:

Can be used on live circuits, including switches, relays, controls PC boards, motors, electrical and electronic components. Test for compatibility with sensitive plastics. Incompatible with ABS, PS, and Lexan. Environmental Data:

CFC: 0% HCFC: 0% ODP: 0 VOC: 56%

Part No. 19-912	12 oz. Aerosol	Replaces Part No. 19-901
Part No. 19-913	16 oz. Aerosol	Replaces Part No. 19-624
Part No. 19-907	16 oz. Anti-Static Aerosol	Replaces Part No. 19-902-SF & 19-903-SF

Big Bath³ Contact Cleaner and Degreaser



Big Bath³ Cleaner and Degreaser is an excellent non-flammable general purpose cleaner/degreaser. The product is non-ozone depleting (contains no HCFC's or CFC's). It is a replacement for cleaner/degreasers containing HCFC 141b. Big Bath ³ Cleaner and Degreaser will dissipate moisture and is safe on some plastics.

Applications:

General cleaning and degreasing applications, electronic and electrical equipment. Test for compatibility with sensitive plastics. Incompatible with ABS, PS, and Lexan. Can be used on energized circuits. Environmental Data:

CFC: 0% HCFC: 0% ODP: 0 VOC: 58%

Part No. 19-905	12 oz. Aerosol	Replaces Part No. 19-902, 19-903-6, 19-2903-3
Part No. 19-906	16 oz. Aerosol	Replaces Part No. 19-903 & 19-2903-8

GC NPB³ – Cleaner and Degreaser RoHS



GC NPB3 - Cleaner and Degreaser is an aggressive cleaner used for removing a broad range of contaminants and heavy soils. Highly recommended for metal cleaning. Contains no HCFC's or CFC's and is non-ozone depleting. Is safe on most surfaces except polycarbonate, polystyrene, ABS and acrylic materials. (To insure complete compatibility, test before use.)

Applications:

Heavy soils on metal, motors, machinery and other types of metal cleaning. Can be used on energized circuits.

Environmental Data:

CFC: 0% HCFC: 0% ODP: 0 VOC: 70%

	070 ODI. 0 10C. 7070	,
Part No. 19-801	12 oz. Aerosol	New Size
Part No. 19-802	16 oz. Aerosol	Replaces Part No. 19-8669

Flux Solv³ RoHS

Flux Solv³ is a fast evaporating, non-ozone depleting flux remover that leaves no residue. It is formulated to remove R, RA, RMA and SA type fluxes. Flux Solv³ is non-flammable and safe on many plastics. Flux Solv³ contains no HCFC's or CFC's and is a replacement for HCFC 141b flux removers.

PC boards, electronic and electrical components. Test for compatibility with sensitive plastics. Incompatible with ABS, PS, and Lexan.

Environmental Data:

CFC: 0% HCFC: 0% ODP: 0 VOC: 60%

Part No. 19-272 16 oz. Aerosol	Replaces Part No. 19-328-22
--------------------------------	------------------------------------









MSDS Number:285

MATERIAL SAFETY DATA SHEET

Complies with OSHA Hazard Communication Standard 29 CFR 1910.1200

Product Type: Cleaner/Degreaser

Product Name: GC-NPB³
Part Number(s): 19-801 12 oz. 19-802 16 oz.

Section 1 - Identification of Product

HMIS RatingsLeast0Health = 2Slight1Flammability = 0Moderate2Reactivity = 0High3Extreme4

Chemical Family: Solvent Cleaner

Section 2 - Hazardous Ingredients

				VAPOR			FLASH	
CHEMICAL AND		OSHA .	ACGIH	PRESSURE			POINT	% By
COMMON NAME(S)	CAS. #	PEL	TLV	@ 25 DEG. C	LEL	UEL	DEG. F	Wt.
N-Propyl Bromide	106-94-5	N/E	N/E	111mmHg	4.0	7.8	None	80 - 90
1,1,1,2-Tetrafluoro-	811-97-2	N/A*	N/A*	96 psia	Nonf	lammable	None	10 - 20
ethane								
Proprietary Mixture	Unknown	Unk	nown	Unknown	Un	known	Unknown	<5

of Stabilizers

NOTE: This product does not contain any ingredients subject to Section 313 of SARA Title III.

N/A is not available or not applicable N/E is not established

Section 3 - Physical Data

BOILING POINT (Deg. F): Concentrate Range: 75

SPECIFIC GRAVITY(Water = 1): Concentrate: 1.2

Propellant: -109.2

VAPOR PRESSURE (mmHg): See Section 2

PERCENT VOLATILE BY

WEIGHT (%): 100% **VAPOR DENSITY (Air = 1):** >1 **EVAPORATION RATE (BA = 1):** >1

SOLUBILITY IN WATER: Negligible

Part Number(s): 19-801, 19-802 Page 1 of 5

^{*}Limit established by The E.I. DuPont Company is 1000ppm

MSDS Number: 285

REACTIVITY IN WATER: None

APPEARANCE AND ODOR: CONCENTRATE: Clear liquid, irritating odor at high concentrations.

PROPELLANT: Colorless, odorless gas.

VOC: 70%

Section 4 - Fire & Explosion Hazard Data

FINISHED PACKAGE: Pressurized containers.

FLASH POINT: See Section 2

FLAMMABLE LIMITS IN

AIR - % BY VOLUME: See Section 2

EXTINGUISHER MEDIA: Water fog, dry chemical, carbon dioxide

AUTO-IGNITION

TEMPERATURE: Unknown

SPECIAL FIRE FIGHTING

PROCEDURES: Water may be used to cool closed containers to prevent pressure build-up

and possible bursting when exposed to high temperatures. Firemen should

wear self-contained, positive pressure, respiratory equipment.

UNUSUAL FIRE AND

EXPLOSION HAZARDS: Contents under pressure. Self-pressurized aerosol containers. Keep

temperature of containers below 120° F. to prevent bursting. Hazardous

decomposition products.

Section 5 - Health Hazard Data

THRESHOLD LIMIT VALUE: See Section 2 SIGNS AND SYMPTOMS OF EXPOSURE:

EYE CONTACT: Contact with liquid or mist may cause irritation. Vapors may irritate eyes.

SKIN CONTACT: Prolonged contact may cause irritation, defatting of skin.

INHALATION: Overexposure to vapor may cause dizziness, loss of concentration and

irritation. Repeated inhalation of high concentrations may cause lung, kidney, liver, urinary, blood, bone marrow, central nervous system, and

reproductive effects. Product vapors displace air and can

cause suffocation especially in confined space. INTENTIONAL MISUSE BY DELIBERATELY CONCENTRATING AND INHALING THE

CONTENTS OF THE CAN MAY BE HARMFUL OR FATAL.

INGESTION: Not expected to be a hazard in normal industrial use. Aspiration may

cause rapid absorption through the lungs, which may result in systemic

effects.