

SPECIFICATIONS

	MODEL		ADA600F-24	ADA600F-30	ADA600F-36	ADA600F-48	
	VOLTAGE[V]		AC85 - 264 1 ¢ or DC 120 -	- 350 (AC64 or DC90 optiona	lly available *6)		
	FREQUENCY[Hz]		50/60 (47 - 63) or DC				
INPUT		ACIN 100V	84typ (lo=100%)	86typ (lo=100%)	86typ (lo=100%)	86typ (lo=100%)	
	EFFICIENCY[%]	ACIN 200V	86typ (lo=100%)	87typ (lo=100%)	87typ (lo=100%)	89typ (lo=100%)	
		ACIN 100V	0.99typ (lo=100%)				
	POWER FACTOR	ACIN 200V	0.98typ (lo=100%)				
		ACIN 100V * 1	20typ (lo=100%) (More than	3sec.to re-start)			
	INRUSH CURRENT[A]	ACIN 200V * 1	40typ (Io=100%) (More than 3sec.to re-start)				
	LEAKAGE CURRENT[mA]		0.75max (60Hz, According to IEC60950 and DEN-AN) (Io=100%)				
	VOLTAGE[V]		24	30	36	48	
	CURRENT[A]	ACIN 100V *2	14 (Peak 25) convection	11 (Peak 20) convection	9 (Peak 16.5) convection	6.5 (Peak 12.5) convectior	
		ACIN 100V *2	21 (Peak 25) forced air	16.5 (Peak 20) forced air	14 (Peak 16.5) forced air	10.5 (Peak 12.5) forced ai	
		ACIN 200V *2	15 (Peak 31) convection	12 (Peak 24.5) convection	10 (Peak 20.5) convection	7 (Peak 15.5) convection	
		ACIN 200V *2	25 (Peak 31) forced air	20 (Peak 24.5) forced air	16.5 (Peak 20.5) forced air	12.5 (Peak 15.5) forced ai	
	LINE REGULATION[I	mV]	96max	120max	144max	192max	
	LOAD REGULATION	[mV]	150max	180max	240max	300max	
		0 to +50℃ *3	120max	160max	200max	200max	
OUTPUT	BIPPI F(mVn-n)	-10 - 0°C *3	160max	230max	260max	300max	
		0 to +50℃ *3	150max	190max	230max	250max	
		-10 - 0°C *3	180max	250max	280max	400max	
	TEMPERATURE REGULATION[mV]	0 to +50℃	240max	300max	360max	480max	
	DRIFT[mV]	*4	96max	120max	144max	192max	
	START-UP TIME[ms]		500max (ACIN 100V, Io=100%)				
	HOLD-UP TIME[ms]		20typ (ACIN 100V, Io=100%)				
	OUTPUT VOLTAGE ADJUSTMENT RANGEIVI			27.0 - 33.0	33.0 - 41.0	41.0 - 52.8	
	OUTPUT VOLTAGE SET	TING[V]	23.5 - 24.5	29.0 - 31.0	35.0 - 37.0	47.0 - 49.0	
			Works over 101% of peak current and recovers automatically				
ROTECTION	OVERVOLTAGE PROTECTION[V]		31 - 34.5	40 - 48	51 - 60	64 - 76	
RCUIT AND			LED (Green)				
THERS	ALARM OUTPUT		Detecting low input voltage(PF), detecting low output voltage(LV). (Optional : -W, refer to Instruction Manual 5)				
	REMOTE ON/OFF(RC)		Requirement for external source (Option : -R, refer to Instruction Manual 5)				
	INPUT-OUTPUT RC	*5					
SOLATION	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature)				
	OUTPUT · RC-FG	*5	AC500V 1minute, Cutoff current = 100mA, DC500V 50M Ω min (At Room Temperature)				
	OPERATING TEMP., HUMID. AND ALTITUDE						
	STORAGE TEMP., HUMID.AND ALTITUDE						
ENVIRONMENT	VIBRATION		10 - 55Hz, 19.6m/s ² (2G), 3minutes period, 60minutes each along X, Y and Z axis				
	IMPACT		196.1m/s ² (20G), 11ms, once each X, Y and Z axis				
AFETY AND			UL60950-1, C-UL(CSA60950-1), EN60950-1, EN60965, EN50178 Complies with DEN-AN and IEC60950-1 (At only AC input				
	CONDUCTED NOISE		Complies with FCC-B, CISPR22-B, EN55022-B, VCCI-B				
EGULATIONS	HARMONIC ATTENUATOR		Complies with IEC61000-3-2 *8				
	CASE SIZE/WEIGHT		65 x 127 x 195mm [2.56 x 5 x 7.68 inches] (W x H x D) (without terminal block) /1.5kg max				
DTHERS	COOLING METHOD		Convection/Forced air				

less) is excluded.

*2 Peak loading for 10sec.And Duty 35% max.Refer to Instruction Manual 4.Forced air is shown in Instruction Manual 2.3.

*3 This is the value that measured on measuring board with capacitor of 22 µ F within 150mm from output terminal.Measured by 20MHz oscilloscope or Ripple-Noise meter (Equivalent to KEISOKU-GIKEN: RM101). with the input voltage held constant at the rated input/output.

- *5 Applicable when remote control (optional) is added.*6 Derating is required.Consult us for details.


*7 Please contact us about safety approvals for the model with option. *8 Please contact us about class C.


A sound may occur from power supply at pulse loading. *

ADA600F | CO\$EL

ADA

Block diagram





: PF Alarm ground(-W)

11-12 NC : N.C. PF+ : PF Alarm(-W)

13


14 PF

AC(L)

FG

Average 21A max per pin for TB1

** Tolerance : ±1 (±0.04)
** Weight : 1.5kg max
PCB material / thickness : FR-4 / 1.6mm [0.06]
** Chassis and cover material : aluminium
** Dimensions in mn. [] = inches
** Mounting torque : 1.2N • m(12.8kgf · cm) max
** Screw tighting torque
M4 : 1.6N • m(16.5kgf · cm) max, M3 : 0.8N • m(8.5kgf • cm) max
** 10 terminal for option-J and -T is shown in Instruction Manual 5.



SPECIFICATIONS

	MODEL		ADA750F-24	ADA750F-30	ADA750F-36	ADA750F-48	
	VOLTAGE[V]		AC85 - 264 1 \$\phi\$ or DC 120 -	350 (AC64 or DC90 optional	ly available *6)		
	FREQUENCY[Hz]		50/60 (47 - 63) or DC				
INPUT		ACIN 100V	86typ (lo=100%)	86typ (lo=100%)	87typ (lo=100%)	87typ (lo=100%)	
	EFFICIENCY[%]	ACIN 200V	88typ (lo=100%)	88typ (lo=100%)	89typ (lo=100%)	89typ (lo=100%)	
		ACIN 100V	0.99typ (lo=100%)				
	POWER FACTOR	ACIN 200V	0.98typ (lo=100%)				
		ACIN 100V * 1	20typ (lo=100%) (More than	3sec.to re-start)			
	INRUSH CURRENT[A]	ACIN 200V * 1	40typ (lo=100%) (More than 3sec.to re-start)				
	LEAKAGE CURRENT[mA]		0.75max (60Hz, According to IEC60950 and DEN-AN) (Io=100%)				
	VOLTAGE[V]		24	30	36	48	
		ACIN 100V *2	17 (Peak 42) convection	13.5 (Peak 33.5) convection	11 (Peak 28) convection	8 (Peak 21) convection	
		ACIN 100V *2	25 (Peak 42) forced air	20 (Peak 33.5) forced air	16.5 (Peak 28) forced air	12.5 (Peak 21) forced air	
	CURRENT[A]	ACIN 200V *2	19 (Peak 63) convection	15 (Peak 50) convection	12.5 (Peak 42) convection	9 (Peak 31.5) convection	
		ACIN 200V *2	31.5 (Peak 63) forced air	24.5 (Peak 50) forced air	20.5 (Peak 42) forced air	15.5 (Peak 31.5) forced ai	
	LINE REGULATION[mV]	96max	120max	144max	192max	
	LOAD REGULATION	[mV]	150max	180max	240max	300max	
		0 to +50℃ *3	120max	160max	200max	200max	
OUTPUT	RIPPLE[mVp-p]	-10 - 0°C *3	160max	230max	260max	300max	
		0 to +50℃ *3	150max	190max	230max	250max	
	RIPPLE NOISE[mVp-p]	-10 - 0°C *3	180max	250max	280max	400max	
	TEMPERATURE REGULATION[mV]	0 to +50°C	240max	300max	360max	480max	
	DRIFT[mV]	*4	96max	120max	144max	192max	
	START-UP TIME[ms]		500max (ACIN 100V, Io=100%)				
	HOLD-UP TIME[ms]		20typ (ACIN 100V, Io=100%)				
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]			27.0 - 33.0	33.0 - 41.0	41.0 - 52.8	
	OUTPUT VOLTAGE SET	TING[V]	23.5 - 24.5	29.0 - 31.0	35.0 - 37.0	47.0 - 49.0	
			Works over 101% of peak current and recovers automatically				
ROTECTION	OVERVOLTAGE PROTECTION[V]		31 - 34.5	40 - 48	51 - 60	64 - 76	
IRCUIT AND			LED (Green)				
THERS	ALARM OUTPUT		Detecting low input voltage(PF), detecting low output voltage(LV). (Optional : -W, refer to Instruction Manual 5)				
	REMOTE ON/OFF(RC)		Requirement for external source (Option : -R, refer to Instruction Manual 5)				
	INPUT-OUTPUT RC	*5	AC3,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature)				
SOLATION	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature)				
	OUTPUT · RC-FG *5		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At Room Temperature)				
	OPERATING TEMP., HUMID.AND ALTITUDE						
	STORAGE TEMP.,HUMID.AND ALTITUDE		-				
ENVIRONMENT	VIBRATION		10 - 55Hz, 19.6m/s ² (2G), 3minutes period, 60minutes each along X, Y and Z axis				
	IMPACT		196.1m/s ² (20G), 11ms, once each X, Y and Z axis				
	AGENCY APPROVALS		UL60950-1, C-UL(CSA60950-1), EN60950-1, EN60065, EN50178 Complies with DEN-AN and IEC60950-1 (At only AC input				
NOISE	CONDUCTED NOISE		Complies with FCC-B, CISPR22-B, EN55022-B, VCCI-B				
			Complies with IEC61000-3-2 *8				
	CASE SIZE/WEIGHT		70×127×230mm [2.76×5×9.06 inches] (W×H×D) (without terminal block) /1.9kg max				
DTHERS	COOLING METHOD		Convection/Forced air				

*1 The value is primary surge. The current of input surge to a built-in EMI/EMC Filter (0.2ms or less) is excluded.

*2 Peak loading for 10sec.And Duty 35% max.Refer to Instruction Manual 4.Forced air is shown in Instruction Manual 2.3.

*3 This is the value that measured on measuring board with capacitor of 22 µ F within 150mm from output terminal.Measured by 20MHz oscilloscope or Ripple-Noise meter (Equivalent to KEISOKU-GIKEN: RM101). *4 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25 with the input voltage held constant at the rated input/output.

*5 Applicable when remote control (optional) is added.*6 Derating is required.Consult us for details.

*6 Derating is required. Consult us for details.
 *7 Please contact us about safety approvals for the model with option.


*8 Please contact us about safety approvals for the model with op
 *8


* A sound may occur from power supply at pulse loading.

ADA750F | COŞEL

ADA

Block diagram





: LV Alarm(-W)

: PF Alarm(-W)

: N.C PF+

LV Alarm ground(-W)

: PF Alarm ground(-W)

3-8 NC NC LV+

9 10 LV-

13

NC 11-12

> PF-14

ж FIII а	Issign		
Symbol	Function	Screw type	
VB	Voltage balance	140	
CB	Current balance	M3	
+V	Output terminal(+)		
+V	Output terminal(+) Output terminal(-) M4		
-V			
-V	Output terminal(-)	11/14	
FG	Frame ground		
N	AC(N)		
	AC(L)		

Average 21A max per pin for TB1

* Tolerance :=1 [=0.04]
* Weight : 1.9kg max
* PCB material / thickness : FR-4 / 1.6mm [0.06]
* Chassis and cover material : aluminium
* Dimensions in mm, []= inches
* Mounting torque : 1.2N + m(12.8kgf + cm) max
* Screw tighting torque
M4 : 1.6N + m(16.9kgf + cm) max, M3 : 0.8N + m(8.5kgf + cm) max
* Uo terminal for option-J and -T is shown in Instruction Manual 5.

AC-DC Power Supplies Enclosed type Ordering information COSEL **ADA1000F** ADA 1000 F -24 -2 3 • 1 Series name Output wattage Recommended EMI/EMC Filter NAC-20-472 Universal input Output voltage Gitter voltage</l **RoHS** ADA F :with Fan unit High voltage pulse noise type : NAP series Low leakage current type : NAM series T :Vertical terminal block J :Connector type *The EMI/EMC Filter is recommended to connect with several devices. C :with Coating R :Remote ON/OFF N1:DIN rail W:Alarms and Redundant operation Specification is changed at option,refer to Instruction Manual.

Please refer to derating curve, because the rated load current depends on cooling method that is convection cooling or forced air.

SPECIFICATIONS

	MODEL		ADA1000F-24	ADA1000F-30	ADA1000F-36	ADA1000F-48	
	VOLTAGE[V]		AC85 - 264 1 ¢ or DC 120 -	- 350 (AC64 or DC90 optiona	Ily available *6)		
	FREQUENCY[Hz]		50/60 (47 - 63) or DC				
		ACIN 100V	86typ (lo=100%)	86typ (lo=100%)	87typ (lo=100%)	87typ (lo=100%)	
INPUT	EFFICIENCY[%]	ACIN 200V	88typ (lo=100%)	88typ (lo=100%)	89typ (lo=100%)	89typ (lo=100%)	
		ACIN 100V	0.99typ (lo=100%)				
	POWER FACTOR	ACIN 200V	0.98typ (lo=100%)				
		ACIN 100V *1	20typ (Io=100%) (More than 3sec.to re-start)				
	INRUSH CURRENT[A]	ACIN 200V *1	40typ (Io=100%) (More than 3sec.to re-start)				
	LEAKAGE CURRENT[mA]		0.75max (60Hz, According to IEC60950 and DEN-AN) (Io=100%)				
	VOLTAGE[V]		24	30	36	48	
		ACIN 100V *2	21 (Peak 63) convection	16.5 (Peak 50) convection	14 (Peak 42) convection	10.5 (Peak 31.5) convection	
		ACIN 100V *2	33 (Peak 63) forced air	26 (Peak 50) forced air	22 (Peak 42) forced air	16.5 (Peak 31.5) forced air	
	CURRENT[A]	ACIN 200V *2	25 (Peak 83) convection	20 (Peak 66) convection	16.5 (Peak 55) convection	11.5 (Peak 41.5) convectior	
		ACIN 200V *2	42 (Peak 83) forced air	33.5 (Peak 66) forced air	28 (Peak 55) forced air	21 (Peak 41.5) forced air	
	LINE REGULATION[I	mV]	96max	120max	144max	192max	
	LOAD REGULATION	[mV]	150max	180max	240max	300max	
		0 to +50℃ *3	120max	160max	200max	200max	
OUTPUT	RIPPLE[mVp-p]	-10 - 0℃ *3	160max	230max	260max	300max	
		0 to +50℃ *3	150max	190max	230max	250max	
	RIPPLE NOISE[mVp-p]	-10 - 0°C *3	180max	250max	280max	400max	
	TEMPERATURE REGULATION[mV]	0 to +50℃	240max	300max	360max	480max	
	DRIFT[mV]	*4	96max	120max	144max	192max	
	START-UP TIME[ms]		500max (ACIN 100V, Io=100%)				
	HOLD-UP TIME[ms]		20typ (ACIN 100V, Io=100%)				
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		21.6 - 27.0	27.0 - 33.0	33.0 - 41.0	41.0 - 52.8	
	OUTPUT VOLTAGE SET	TING[V]	23.5 - 24.5	29.0 - 31.0	35.0 - 37.0	47 - 49	
	OVERCURRENT PROTECTION		Works over 101% of peak current and recovers automatically				
ROTECTION	OVERVOLTAGE PROTECTION[V]		31 - 34.5	40 - 48	51 - 60	64 - 76	
IRCUIT AND	OPERATING INDICATION		LED (Green)				
DTHERS	ALARM OUTPUT		Detecting low input voltage(PF), detecting low output voltage(LV). (Optional : -W, refer to Instruction Manual 5)				
	REMOTE ON/OFF(RC)		Requirement for external source (Option : -R, refer to Instruction Manual 5)				
	INPUT-OUTPUT · RC	*5	AC3,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature)				
SOLATION	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature)				
	OUTPUT · RC-FG	*5	AC500V 1minute, Cutoff current = 100mA, DC500V 50M Ω min (At Room Temperature)				
	OPERATING TEMP.,HUMID.AND	ALTITUDE	-10 to +71°C, 20 - 90%RH (Non condensing) (Refer to DERATING CURVE), 3,000m (10,000feet) max				
	STORAGE TEMP.,HUMID.AND ALTITUDE		-20 to +75°C, 20 - 90%RH (Non condensing), 9,000m (30,000feet) max				
ENVIRONMENT	VIBRATION		10 - 55Hz, 19.6m/s ² (2G), 3minutes period, 60minutes each along X, Y and Z axis				
	IMPACT		196.1m/s ² (20G), 11ms, once each X, Y and Z axis				
	AGENCY APPROVALS		UL60950-1, C-UL(CSA60950-1), EN60950-1, EN60065, EN50178 Complies with DEN-AN and IEC60950-1 (At only AC input)				
NOISE	CONDUCTED NOISE		Complies with FCC-B, CISPR22-B, EN55022-B, VCCI-B				
REGULATIONS			Complies with IEC61000-3-2 *8				
	CASE SIZE/WEIGHT		75×127×280mm [2.95×5×11.02 inches] (W×H×D) (without terminal block) /2.5kg max				
OTHERS	COOLING METHOD		Convection/Forced air	-			

less) is excluded.

*2 Peak loading for 10sec.And Duty 35% max.Refer to Instruction Manual 4.Forced air is shown in Instruction Manual 2.3.

*3 This is the value that measured on measuring board with capacitor of 22 µ F within 150mm from output terminal.Measured by 20MHz oscilloscope or Ripple-Noise meter (Equivalent to KEISOKU-GIKEN: RM101). with the input voltage held constant at the rated input/output.

*5 Applicable when remote control (optional) is added.*6 Derating is required.Consult us for details.


*7 Please contact us about safety approvals for the model with option.


*8 Please contact us about class C. A sound may occur from power supply at pulse loading. *

ADA1000F | CO\$EL

ADA

Block diagram





NC : N.C. PF+ : PF Alarm(-W)

: PF Alarm ground(-W)

11-12

13 14 PF-

Average 21A max per pin for TB1

Ν

** Tolerance : ±1 [±0.04]
** Weigh: 2.5kg max
** PCB material / thickness : FR-4 / 1.6mm [0.06]
** Chassis and cover material : aluminium
** Dimensions in mm, []= inches
** Mounting torque : 1.2N • m(12.8kg f • cm) max
** Screw tighting torque
M4 : 1.6N • m(16.5kg f • cm) max, M3 : 0.8N • m(8.5kg f • cm) max
** I/0 terminal for option-J and -T is shown in Instruction Manual 5.