

AUTOMOTIVE MICRO-ISO RELAY

CM RELAYS



mm inch

FEATURES

• Small size: 20 mm(L)×15 mm(W)×22 mm(H) .787 inch(L)×.591 inch(L)×.866 inch(H) • Wide line-up PC board and Plug-in type, Resistor and diode inside type. 24V DC type is also available. Compact and high-capacity 35A load switching N.O.: 35A 14V DC, N.C.: 20A 14V DC (Sealed type) Min. 5×10^4 N.O.: 35A 14V DC, N.C.: 20A 14V DC (Flux-resistant type) Min. 105 *12V DC type Micro-ISO type terminals

TYPICAL APPLICATIONS

- Fan motor
- Heater
- Head lump
- Air Compressor
- EPS
- ABS
- Blower fan
- Defogger, etc.

SPECIFICATIONS

| Contact |
|---------|
|---------|

| Туре | | 12 V coil voltage | 24 V coil voltage | |
|-------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--|
| Arrangeme | nt | 1 Form A, 1 Form C | | |
| Contact ma | aterial | Silver alloy | | |
| Initial conta (By voltage | ct resistance drop 6 V DC 1 A) | Max. 15mΩ | | |
| Contact vol | Max. N.O.: 0.5 V Max. N.O. Contact voltage drop (at 35 A 14 V DC) (at 15 A 28 Max. N.C.: 0.3 V Max. N.C. (at 20 A 14 V DC) (at 8 A 28 | | Max. N.O.: 0.3 V (at 15 A 28 V DC) Max. N.C.: 0.2 V (at 8 A 28 V DC) | |
| Rating (resistive load) | Nominal switching capacity | N.O.: 35 A 14 V DC N.C.: 20 A 14 V DC | N.O.: 15 A 28 V DC N.C.: 8 A 28 V DC | |
| | Max. carrying current | N.O.: 20 A (14 V DC, at 85°C 185°F) N.C.: 10 A (14 V DC, at 85°C 185°F) | N.O.: 15 A (28 V DC, at 85°C 185°F) N.C.: 8 A (28 V DC, at 85°C 185°F) | |
| | Min. switching capacity ^{#1} | 1 A 12 V DC | 1 A 24 V DC | |
| Expected | Mechanical (at 120 cpm) | Min. 10 ⁶ | | |
| life | Electrical (at rated load) | Flux-resistant type: Min. 10^{5*1} Sealed type: Min. 5×10^4 | | |
| Coil | | | | |
| Nominal operating power | | 1.5 W 1.7 W | 1.8 W 2.0 W | |

type) type) #1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

(Internal resistor

Characteristics

| Туре | | 24V coil type | 12V coil type | | |
|------------------------------------------------------------------------------|---------------------------|----------------------------------------------|--------------------------|--|--|
| Max. operating spee (at nominal switchin | ed g capacity) | 15 cpm | | | |
| Initial insulation resi | stance*2 | Min. 20 MΩ (| Min. 20 MΩ (at 500 V DC) | | |
| Initial breakdown | Between open contacts | 500 Vrms for 1 min. | | | |
| voltage*3 | Between contacts and coil | 500 Vrms for 1 min. | | | |
| Operate time*4 (at nominal voltage) (at 20°C 85°F) | | Max. 10 ms | | | |
| Release time*4 (at nominal voltage) (at 20°C 85°F) | | Max. 10 ms Max. 15 ms (with diode) | | | |
| Ohaali vaaiatamaa | Functional*5 | Min. 200 m/s² {20G} | | | |
| SHOCK TESISLATICE | Destructive*6 | Min. 1,000m/s ² {100G} | | | |
| Vibration | Functional | 10 Hz to 500 Hz, Min. 44.1 m/s² {4.5 G} | | | |
| resistance | Destructive*7 | 10 Hz to 2,000 Hz, Min. 44.1 m/s² {4.5 G} | | | |
| Conditions for operation, trans- | Ambient temp.*9 | −40°C to + 85°C −40°F to + 185°F | | | |
| port and storage*8 (Not freezing and condensing at low temperature) | Humidity | 5% R.H. to 85% R.H. | | | |
| Mass | | Approx. 20g .71oz | | | |

Remarks

(Internal resistor

- *1 At nominal switching capacity, operating frequency: 2s ON, 2s OFF
- *2 Measurement at same location as "Initial breakdown voltage" section.

*3 Detection current: 10mA *4 Excluding contact bounce time.

*5 Half-wave pulse of sine wave: 11 ms; detection time: 10 μs

*6 Half-wave pulse of sine wave: 6 ms

*7 Time of vibration for each direction; X, Y, Z direction: 4 hours

- *8 Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT
- *9 Ambient temperature 125°C 257°F type is also considerable on request. Please contact us for details.

ORDERING INFORMATION

| | CM 1 | F — R — P | - 12V | |
|-----------------------------|--------------------------------------------|-----------------------------------------------------------------------|---------------------------------------|-------------------|
| Contact arrangement | Protective construction | Classification of types | Mounting classification | Coil voltage (DC) |
| 1a: 1 Form A 1: 1 Form C | Nil: Sealed type F: Flux-resistant type | Nil: Standard type D: with diode inside R: with resistor inside | Nil: Plug-in type P: PC board type | 12 V 24 V |

Note: Bulk package: 50 pcs.; Case: 200 pcs.

TYPES

Packing quantity: Inner 50pcs, Outer 200pcs.

| Contact arrangement | Part No. | Coil voltage | Mounting classification | Protective construction |
|---------------------|-------------|--------------|-------------------------|-------------------------|
| 1 Form A | CM1a-12V | | | Sealed type |
| | CM1aF-12V | 12 V DC | Plug-in type | Flux-resistant type |
| | CM1a-P-12V | | | Sealed type |
| | CM1aF-P-12V | | PC board type | Flux-resistant type |
| | CM1-12V | | Di se in tra s | Sealed type |
| | CM1F-12V | | Plug-in type | Flux-resistant type |
| 1 Form C | CM1-P-12V | | PC board type | Sealed type |
| | CM1F-P-12V | | | Flux-resistant type |
| | | | - | |
| Contact arrangement | Part No. | Coil voltage | Mounting classification | Protective construction |
| | CM1a-24V | | Plug in type | Sealed type |
| 1 Earm A | CM1aF-24V | | Fidg-III type | Flux-resistant type |
| | CM1a-P-24V | 24 V DC | PC beard type | Sealed type |
| | CM1aF-P-24V | | PC board type | Flux-resistant type |
| | CM1-24V | | Diver in two | Sealed type |
| | CM1F-24V | | Plug-in type | Flux-resistant type |
| 1 Form C | CM1-P-24V | | DC beard time | Sealed type |
| | CM1F-P-24V | | PC board type | Flux-resistant type |

COIL DATA (at 20°C 68°F)

| Nominal voltage, V DC | Pick-up voltage, V DC | Drop-out voltage, V DC | Nominal current, mA | Coil resistance, ohm | Nominal operating power, W | Usable voltage range, V DC |
|--------------------------|--------------------------|---------------------------|------------------------|-------------------------|----------------------------|-------------------------------|
| 12 | 3 to 7 | 1.2 to 4.2 | 125±10% | 96±10% | 1.5 | 10 to 16 |
| 24 | 6 to 14 | 2.4 to 8.4 | 75±10% | 320±10% | 1.8 | 20 to 32 |

DIMENSIONS

1. Micro-ISO Plug-in type (1 Form C)



Schematic (Bottom view)



mm inch

 * Intervals between terminals is measured at A surface level.

mm inch

2. Micro-ISO Plug-in type (1 Form A)



* Intervals between terminals is measured at A surface level.

3. Micro-ISO PC board type (1 Form C)



* Dimensions (thickness and width) of terminal specified in this catalog is measured before pre-soldering. Intervals between terminals is measured at A surface level.

4. Micro-ISO PC board type (1 Form A)



Schematic (Bottom view)

87 30

Including diode type, including resistor type also available

87 Π Π

86



* Dimensions (thickness and width) of terminal specified in this catalog is measured before pre-soldering. Intervals between terminals is measured at A surface level.