Pressure decay sensor

■ 100 % pneumatic



Also available in ATEX version for use in potentially explosive atmospheres in accordance with 94/9/EC Directive



Pressure decay sensor

Symbol

Characteristics			
Operating pressure	bar	2 → 8	
Flow at 6 bars	NI/min	200	
Tripping point	b	0.3	
with 6 bar supply			
Connection		Sub-base page 54-55	
Operating temperature	°C	-5 → +50	


Mechanical life Weight Connections


Without flow restrictor

operations

≥10⁷

25






Principle of operation

Fitted in-line between the cylinder and the control valve, the sensor will give an output when the pressure in this line is exhausted and the cylinder is at end of stroke.


For the correct usage of sensors on a falling pressure, it is recommended that the practical cylinder load is limited to 60% of the theoretical force.

Evolution of pressure within a double-acting cylinder



Dimensions

81 504 025





ATEX version products are available in the following catologues: Pneumatic products for explosive atmospheres or on our website www.crouzet.com

