
Powerpole® Connectors - PP75: up to 120 Amps



PP75 series Powerpole® housings can be used for wire-to-wire, wire-to-board, and wire-to-busbar applications. Wire sizes from #16 AWG (1.3 mm²) to #6 (13.3 mm²) offer power capabilities up to 120 amps per pole. Locking housings offer the capability to secure Powerpole® housings to each other and to mounting pads. Housings made from chemical resistant (CR) resin withstand industrial solvents better than standard housings.

- Large Wire Range Accommodates up to #6 (10mm²) Wire Reducing bushings allow as small as #16 (1.5 mm²) wire to be used
- Wire, PCB, and Busbar Contacts Allows one connection system to meet multiple needs
- Mini-Powerclaw PCB Contacts Minimize PCB Footprint Removes the PP75 housing from the board side

[47.9] 1 88

> [81.3] 3.20

PP75 ORDERING INFORMATION |

PP75 Standard Housings

The second smallest Powerpole® housing can be used with wire contacts up to 6 AWG [10mm²] as well as PCB and busbar contacts.

Part Numbers				
. 1,000	100			
5916G7-BK	5916G7			
5916G6-BK	5916G6			
5916G4-BK	5916G4			
5916G5-BK	5916G5			
5916-BK	5916			
5916G15-BK	5916G15			
5916G14-BK	5916G14			
5916G16-BK	5916G16			
	1,000 5916G7-BK 5916G6-BK 5916G4-BK 5916G5-BK 5916-BK 5916G15-BK 5916G14-BK			

PP75 Chemical Resistant (CR) Housings

Has the same form and dimensions of the standard PP75 housing in a chemical resistant PBT/ PC blend housing. Suitable for use to -40°C.

Description	- Part Numbers -
Minimum Quantity	1,000
Red	P5916G7-BK
Black	P5916G4-BK
White	P5916G5-BK
Blue	P5916-BK

PP75 Locking Dovetail Housings

Offers dovetails for stacking housings that have a locking feature to prevent housings separating. Can mate to standard and chemical resistant housings, but cannot be stacked with them.

Description	Part Numbers			
Minimum Quantity	1,000	100		
Red	75LOKRED-BK	75LOKRED		
Green	75LOKGRN-BK	75LOKGRN		
Black	75LOKBLK-BK	75LOKBLK		
White	75LOKWHT-BK	75LOKWHT		
Blue	75LOKBLU-BK	75LOKBLU		
Gray	75LOKGRA-BK	75LOKGRA		

Mated Length

🕲 A 📾

[15.9] 0.62


Front View


[15.9]

0.62

V0 = Standard Material ID Located Here







© 2017 Anderson Power Products, Inc. All rights reserved. APP®, Anderson Power Products®, A®, Powerpole®, SPEC Pak® and the APP Logo are registered trademarks of Anderson Power Products. Inc.



- 30 -


[17.0]

0.67

PP75 Premate Ground Housings

Offers a first-mate, last-break connection when stacked together with PP75 housings. Stacks together with PP75 standard and chemical resistant housings. Housings are mechanically keyed to prevent cross mating with power positions.

Description	Part Numbers				
Minimum Quantity	1,000	100			
Green	5927G6-BK	5927G6			



[30.0]

1.18

[11.1]

0.44

A

[7.2]

0.28



P

[7.1]

0.28

PP75 Silver Plated Wire Contacts

Silver plated contacts offer the best electrical performance and durability up to 10,000 mating cycles. See reducing bushings in accessory section for smaller wires.

					Dimens	sions
		Mating	Loose	Piece	- /	۹ -
AWG	mm²	Force	Part Nu	mbers	inches	mm
Minimum (Quantity		1,000	100		
6	13.3	Low	1307-BK	1307	0.22	5.59
6	13.3	High	5900-BK	5900	0.22	5.59
8	8.4	High	5952-BK	5952	0.19	4.83
12 to 10	3.3 to 5.3	Low	5953-BK	5953	0.14	3.56
12 to 10	3.3 to 5.3	High	5915-BK	5915	0.14	3.56

PP75 Premate Ground Wire Contacts

Silver plated contacts for use with the PP75 Premate Ground Housing. Rated to 10,000 mating cycles.

					Dimensions	
			Loose F	liece	- A	-
Туре	AWG	mm²	Part Nun	nbers	inches	mm
Minimum Q	uantity		1,000	100		
Individual	6	13.3	1875G1-BK	1875G1	0.22	5.59
Individual	8	8.4	1875G2-BK	1875G2	0.19	4.83
Individual	12 to 10	3.3 to 5.3	1875G3-BK	1875G3	0.14	3.56

PP75 Silver Plated Busbar Contacts

Provide a quick disconnect input or output busbar connection. Busbar contacts are for mating with wire contacts only. Part number 75BBS includes lock nuts. Locknuts must be ordered separately for B01915P1.


		Mating			
Туре	Thread	Force	P	art Numbers	;
Minimum (Quantity		1,000	20	10
Busbar	#10-24	High	B01915P1	-	75BBS
Lock Nut	#10-24	-	H1216P8	110G54	-


55A Right Angle Standard Powerclaw PCB Contacts

Standard Powerclaw contacts are for use inside a PP75 housing and provide a color coded right angle connection to the PCB.

Description		Part Numbers	[5.2] 0.20 ¬	[17.0]		PP75 Housing
Minimum Quantity	500	100		0.67		
Tin Plated	PC5930T-BK	PC5930T				
Silver Plated	PC5930S-BK	PC5930S	See PCB contact drawing on website for further detail.	/		Standard Powerclaw Contact
			Secon	d housing and contac	ct	

in two pole version only.







- 31 -

55A Right Angle Mini Powerclaw PCB Contacts


Right angle Mini Powerclaw contacts can be used on the PCB edge without a PP75 housing on the PCB side. A self polarizing design only allow PP75 wire housings to mate to PCB contacts one way.


	Loose Piece				
Description	Part Numbers				
Minimum Quantity	1,000	100			
Tin Plated	PC5934T-BK	PC5934T			
Silver Plated	PC5934S-BK	PC5934S			


55A Vertical Mini Powerclaw PCB Contacts

Vertical Mini Powerclaw contacts save space by not requiring a PP75 housing on the PCB side. The guide housing is required for 2 pole applications to provide a polarized connection. (See PP75 accessories).

Description	Loose Piece Part Numbers			
Minimum Quantity .	1,500 100			
Tin Plated	PC5933T-BK	PC5933T		
Silver Plated	PC5933S-BK	PC5933S		









See PCB contact drawing on website for further detail.

PP75 TEMPERATURE CHARTS | Temperature rise charts are based on a 25°C ambient temperature.







NOTE: Powerclaw charts are based on #8 AWG equivalent copper foil on board side, mated to #6 AWG conductor on wire side.

- 32 -

| PP75 SPECIFICATIONS |

Electrical			Mechanica	al		
Current Rating Amperes ¹	UL 1977	CSA	Wire Size Ra	nge	AV	NG
Wire to Wire (6 AWG)	120	70	Wire Contact	ts with Bushings	16	to 6
Wire to PCB (6-AWG)	55	50		-		
Wire to Busbar (6 AWG)	75		Max. Wire Ins	sulation Diameter	in.	
					0.4	437
Voltage Rating AC/DC						
UL 1977	600		Operating Te	mperature ²	°F	
			Standard & O	Ground	-4	° to 221°
PCB Connector Recommende	d Voltage 3		Chemical Re	esistant*	-40	0 to 221°
per IEC 60950-1 Table 2L Pollu	ution Degree ²		*Chemical res	istant material not ava	ilable for P	CB guide housings
Mini Vert. Contact Adjacent Po	les 220					
Mini Horiz. Contact Adjacent P	oles 200		Mating Cycle	s No Load by Plating	Si	lver (Ag)
Standard Contact Adjacent Pol	les 635		Wire and PC	B Contacts	10	0,000
Dielectric Withstanding Voltag	je		Avg. Mating /	Unmating Force	Lt	of.
Volts AC	2,200			Low Force Contacts	5	
			Wire to Wire	High Force Contacts	7	
Avg. Mated Contact Resistance	e Milliohms ¹		Standard Po	werclaw to Wire	7	
Wire Contact with 1 1/4" of #6	AWG 0.200		Mini Powercl	aw to Wire	4	
PCB Contact to Contact	0.500					
			PCB Specific	ations		
UL Hot Plug Current Rating A	mperes - 250 cycle	s at 120V DC ⁶	Mounting Sty	/le	Pla	ated Through Hole
Wire- wire	50A		Max PCB Th	ickness- in. [mm]	St	andard: 0.15 [0.381
PCB- wire (Vertical Mini Power	claw) 40A				Mi	ni: 0.25 [0.635
			Recommend	ed Traces	#8	AWG Cross Section
UL Ground Short Time Curren	it Test - 75A Prema	te Ground				
1530 Amps, #6 AWG Wire	6 Seconds	s	Min. Contact	/ Spring Retention For	orce Lb	of.
Materials			Wire Housing	g	50)
Housing	Delveerherete			e / Clearance Distan		
Standard Plastic Resin	Polycarbonate			werclaw Adjacent Pole		260
Chem. Resistant Resin	Polycarbonate			werclaw Adjacent Pole		087
Contact Retention Spring	Stainless Steel		Mini Horz. Po	owerclaw Adjacent Pol	es 0.0	079
Housing Flammability Rating			Mechanical S	shock 5		
UL94	V-0		MIL-STD-202		21	3 Condition A
Glow Wire	960°C (GWFI)	/ 800°C (GWIT)				
			Vibration Hig	h Frequency ⁵		
Contact			MIL-STD-202		20	4 Condition A
Base	Copper Alloy					
Wire Plating	Silver					-
PCB Plating	Sn or Ag over I	Ni	Connector			Creepage / Clearance
	C C		Series	Configurations		per IEC 60950-1
Contact Termination Methods	j.					0.07
Crimp ⁴	Wire Contacts			Single Pole	Unmated	2.97 mm
Hand Solder	Wire and PCB	Contacts	PP75	-	Mated	2.97 mm
Solder Dip*	PCB Contacts				Unmated	2.97 mm
Wave Solder*	PCB Contacts			Stacked Powerpole®	Mated	2.97 mm
					mateu	2.57 11111

mm² 1.3 to 13.3

mm 11.100

°C -20° to 105° -40° to 105°

Tin (Sn) 1,500

Ν 222

mm 6.6 2.2 2.0

50g's

10g's

Material Group

Illa

Wrench / Socket

Touch Safety with Wire Contacts IEC 60529 IP10

NOTE 1: See IEC 60664-1 for working voltage.

NOTE 2: Amp ratings are stated per position and based on all positions being fully loaded.

Busbar Contacts

¹ Based on: 105°C rated or better cable of the largest size, Properly calibrated APP recommended tooling, and a 25°C ambient temperature. UL rating not to exceed the maximum operating temperature. CSA rating below a 30°C temperature rise.

² Limited by the thermal properties of the connector plastic housing.

³ Without use of spacers to increase creepage and clearance distances.

⁴ Use APP recommended tooling only. Alternate tools may adversely affect the performance of our connectors along with UL and CSA recognition.

REACH

ΔΡΙ

⁵ Tested with contact part number 5900.

⁶ Based on 2 housings blocked together.





| Powerpole® PP75 Accessories |

Strain Relief Grommets

Use for strain relief in the back side of a PP75 housing. Wire gauge given for reference only, use grommet ID and wire OD to determine suitability in the end application.

		Dimensions	
Description	- Part Numbers -	inches	s mm
Minimum Quantity	100		
#6 AWG, Black	114411P2	0.35	8.89
#8 AWG, Black	114411P1	0.25	6.35
#10 - 12 AWG, Black	114411P3	0.17	4.32

Mounting Wing for Standard or CR Housings

Mounting wings can be used to secure dovetailed Powerpole[®] 75 series housings by passing fasteners through the wings in either a horizontal or vertical orientation. Useful for sheet metal panels, printed circuit boards, and many other mounting surfaces. Fasteners not included.


Description	Part Numbers			
Minimum Quantity	1,000	100		
Blue, Round Hole	1399G20-BK	1399G20		
Blue, Oval Hole	1399G7-BK	1399G7		


Mounting Wing for Locking Housings

Mounting wings can be used to secure Powerpole[®] 75 series housings with locking dovetails by passing fasteners through the wings in either a horizontal or vertical orientation. Useful for sheet metal panels, printed circuit boards, and many other mounting surfaces. Fasteners not included.

Description	Part Numbers			
Minimum Quantity	1,000	100		
Blue, Oval Hole	75LOKWNGBLU-BK	75LOKWNGBLU		
Blue, Round Hole	75LOKWNGBLU-R-BK	75LOKWNGBLU-R		










- Mounting Wing Top




Left Side View - Both Versions Right Side View


Round Hole

Surface Mount for Locking Housings

Use to secure Powerpole® 75 series housings with locking dovetails to a flat surface. Useful for sheet metal panels, printed circuit boards, and many other mounting surfaces. Fasteners not included.

Description	Part Numbers				
Minimum Quantity	1,000	100			
Blue	75LOKSMTBLU-BK	75LOKSMTBLU			







Side View

Spacer

Use to separate housings under high power to minimize power capability derating due to heat rise. They are recommended for squaring off a block of Powerpole® 75 housings to enable mounting accessories or retaining pins to be used. Combining long and short spacers opposite each other in a mated block adds keying features, or use two short spacers to avoid interference.

Description	Part Numbers			
Minimum Quantity	1000	100		
Red, Short	1399G23-BK	1399G23		
Red. Lona	1399G21-BK	1399G21		





Short


Long

- 34 -

Guide Housings for Vertical Mini Powerclaw Contacts

Prevents polarity being reversed when a two pole PP75 block is mated to vertical mini Powerclaw contacts. Fastening hardware not included.

Description	Part Numbers			
Minimum Quantity	1,000	100		
Black Guide Housing	PC-HSG-PP-BK	PC-HSG-PP		



Mounting Clamp

Mounting clamps can be used for fastening a block of Powerpole® 75 series housings to a panel. Connector blocks must be a complete square for the clamps to work properly. Fastening hardware not included.


Description	- Part Numbers -			
Minimum Quantity	50 sets of 2			
2 or 4 Pole	1463G1			
3 or 6 Pole	1463G2			

Mounting Clamp Panel 3 Pole ole

Retaining Pins

Retaining pins are used to keep stacked Powerpole® 75 series housings from separating. Retaining pins are inserted in the circular opening between two housings stacked side by side. Dimension B is +/- 0.015 in or 0.38 mm.

			Dimensions			
			- A -		- E	3 -
Description	Part Nu	mbers	inches	mm	inches	mm
Minimum Quantity .	1,000	100				
1 Block High	111812P7	110G19	0.196 / 0.207	4.98 / 5.26	0.560	14.220
2 Block High	111812P6	110G18	0.196 / 0.207	4.98 / 5.26	1.000	25.400



PCB Mounting Staples

Reducing Bushings

Contact Barrel Size Wire Size

Minimum Quantity


#6 AWG [13.3 mm²] #12- 10 AWG [3.3- 5.3 mm²]


#6 AWG [13.3 mm²] #16- 14 AWG [1.3- 2.1 mm²] 5913-BK

#6 AWG [13.3 mm²] #8 AWG [8.4 mm²]

Reduce strain on solder joints during mating and unmating. Staples bend over the underside of the PCB board to lock the housings in place. Staples are an interference fit with housings.

	Number of Stacked Powerpoles		
Part Numbers	НхW		
Minimum Quantity	100		
PCSTAPLE-2	1 x 2		





Fasten the staple by bending the leads on the bottom of the board.

Slide staple over housings and into the holes in the board.

Dimensions

Inches

0.45

0.47

0.47

- ID -

inches mm

4.57

3.56

2.29

0.18

0.14

0.09

- Part Numbers

1,000

5912-BK

-

100


5912


5910

5913

3,000

5910-BK





-----For environmentally sealed connector shells to hold Powerpole®

Use with contact part number 5900-BK or 1307-BK to allow a smaller wire to be used with the connector. Electrical capability is derated with smaller wire.

15-180 connectors, see SPEC Pak® product series on our website, www.andersonpower.com



35

Powerpole[®] - Tooling Information

Wire	Size	Reeled Part Numbers		Reeled Co	ntact Crimp Tool		
AWG	mm²	Tin Plating	Silver Plating	APP Applicator	+ APP Press		
	PP15 /	45 Flat W	iping Power	& Ground			
#16 / 20	1.3 / 0.52	262G1	262G2				
#16 / 20	1.3 / 0.52	269G2	N/A				
#12 / 16	3.3 / 1.3	261G1	N/A	TD0101			
#10 / 14	5.3 / 2.1	261G2	261G3	TDOTOT	115V= TE0101		
#12 / 16	3.3 / 1.3	269G1	N/A		230V = TE0102		
#10 / 14	5.3 / 2.1	269G3	N/A		2300 - 120102		
#10 / 14	5.3 / 2.1	200G1L	200G3L				
#10 / 14	5.3 / 2.1	201G1H	N/A	TD0102			
#10 / 14	5.3 / 2.1	1830G1	1830G2				

* APP applicators are mechanical feed style and do not require an air feed kit.

Wire	Size	Loose Piece Part Numbers Loose Piece Contact Crimp Tool					Tool			
AWG	mm²	Tin Plating	Silver Plating	Hand Tool	Pneumatic Bench r Tool		⊦ Locator	Number of Crimps		
PP15 / 45 Flat Wiping Power & Ground										
#16 / 20	1.3 / 0.52	N/A	1332		1367G1					
#12 / 16	3.3 / 1.3	N/A	1331	1309G2	1307G1					
#16 / 20	1.3 / 0.52	262G1-LPBK	262G2-LPBK	or 1309G8						
#16 / 20	1.3 / 0.52	269G2-LPBK	N/A							
#12 / 16	3.3 / 1.3	261G1-LPBK	N/A							
#10 / 14	5.3 / 2.1	261G2-LPBK	261G3-LPBK	1309G3 or				O're el e		
#12 / 16	3.3 / 1.3	269G1-LPBK	N/A	1309G8	N/A	N/A	N/A	Single		
#10 / 14	5.3 / 2.1	269G3-LPBK	N/A							
#10 / 14	5.3 / 2.1	200G1L-LPBK	200G3L-LPBK	1309G6						
#10 / 14	5.3 / 2.1	201G1H-LPBK	N/A	or						
310 / 14	5.3 / 2.1	1830G1-LPBK	1830G2-LPBK	1309G8						
	1		PF	P75						
#6	13.3		1307			1389G6				
	1010		5900			1388G6 1389G21 1389G6				
#8	8.4		1875G1							
		N/A	5952	1309G4	1387G1		Single			
#10 / 12	52/22	IN/A	1875G2	130304	-	34 I 367 G I	1307 9 1	13890	1389G21	Single
#10/12	5.575.5		5953					101	100007	400007
			5915 1875G3			1388G7	1389G21			
				120			1000021			
1/0	53.5		1323G2	120						
#1	42.4		1323G1			1388G3				
#2	33.6	N/A	1319	1368	1387G1		1389G4	Single		
#4	21.2		1319 1319G4	Series		1388G4		Single		
#4	13.3		1319G4 1319G6				-04			
#0	13.5			180						
3/0	85		1328G2							
2/0	53.5		1328G1			1303G12				
1/0	53.5		132861							
#1	42.4	N/A	1347	1368	1387G2	1303G13	1304G32	Double		
#2	33.6		1383	Series						
#4	21.1		1384							
#6	13.3		1348		1387G1	1388G4	1389G3	Single		

1. NOTE: See website for the most current information.

2. NOTE: Insertion / Extraction fool for PP15/45 contacts = 111038G2

