

T50RTM250HSM4



Article Number: 126-03501

Fir Tree Push Mount Ties, 8.0" Long, 0.25" - 0.28" Mounting Hole, PA66HS, Black, 1,000/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number T50RTM250HSM4

Type T50RTM25

Color Black (BK)

Features and Benefits

- Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation.
- Initial fir tree serves as a locating feature for assistance in blind assembly applications.
- Disc feature provides anti-rattle protection in high vibration applications.

Product Description Fir tree mounts with ties cables provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force, and slides along the cable tie for the proper orientation. This is sold as an assembly with the cable tie.

Short Description Fir Tree Push Mount Ties, 8.0" Long, 0.25" - 0.28" Mounting Hole, PA66HS, Black, 1,000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 50.0 lbs

Minimum Tensile Strength (Metric) 225 N

Length L (Imperial) 8.0 "

Length L (Metric) 213.1 mm

Fixation Method Fir Tree

Identification Plate Position none

Releasable Closure Yes

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.18 "

Width W (Metric) 4.6 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 2.0 mm

Bundle Diameter Max. (Imperial) 2.0 "

Bundle Diameter Max. (Metric) 50.0 mm

Panel Thickness Max. (Imperial) 0.28 "

Panel Thickness Max. (Metric) 7.00 mm

Panel Thickness Min. (Imperial) 0.05 "

Panel Thickness Min. (Metric) 1.32 mm

Mounting Hole Diameter D Min. (Imperial) 0.25 "

Mounting Hole Diameter D Max. (Imperial) 0.26 "

Mounting Hole Diameter D Max. (Metric) 6.6 mm

(Metric) 6.5 mm

Mounting Hole Diameter D Min. (Metric)

Logistics and Packaging

Quantity Per bag
Package Quantity (Metric) 1000
Carton Quantity 5000

Material and Specifications

Material Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut PA66HS
Operating Temperature -40°F to +221°F (-40°C to +105°C)
ROHS Compliant Yes